

# VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]  
> Cat.#s

> Current System AUD Prices



SSAC8W	Rotor seal 8 port 2-pos W-valve	1/16 x .4mm 75C/5000psi liq H
SSAC8WE	Rotor seal 8 port 2-pos W-valve	1/16 x .4mm 225C/400psi gas E
SSAC8WT	Rotor seal 8 port 2-pos valve	1/16 x .4mm 350C/300psi gas T
SSACI4UW.2	Rotor seal 4 port 2-pos int vol UW-valve	1/16 x .75mm 75C/5000psi liq .2ul H
SSACI4UW.5	Rotor seal 4 port 2-pos int vol UW-valve	1/16 x .75mm 75C/5000psi liq .5ul H
SSACI4UW1	Rotor seal 4 port 2-pos int vol UW-valve	1/16 x .75mm 75C/5000psi liq 1ul H
SSACI4UW2	Rotor seal 4 port 2-pos int vol UW-valve	1/16 x .75mm 75C/5000psi liq 2ul H
SSACI4UWE.2	Rotor seal 4 port 2-pos int vol UW-valve	1/16 x .75mm 175C/1000psi liq .2ul E
SSACI4UWE.5	Rotor seal 4 port 2-pos int vol UW-valve	1/16 x .75mm 175C/1000psi liq .5ul E
SSACI4UWE1	Rotor seal 4 port 2-pos int vol UW-valve	1/16 x .75mm 175C/1000psi liq 1ul E
SSACI4UWE2	Rotor seal 4 port 2-pos int vol UW-valve	1/16 x .75mm 175C/1000psi liq 2ul N60/E
SSACI4W.06	Rotor seal 4 port 2-pos int vol W-valve	1/16 x .4mm 75C/5000psi liq .06ul H
SSACI4W.1	Rotor seal 4 port 2-pos int vol W-valve	1/16 x .4mm 75C/5000psi liq .1ul H
SSACI4W.2	Rotor seal 4 port 2-pos int vol W-valve	1/16 x .4mm 75C/5000psi liq .2ul H
SSACI4W.5	Rotor seal 4 port 2-pos int vol W-valve	1/16 x .4mm 75C/5000psi liq .5ul H
SSACI4WE.06	Rotor seal 4 port 2-pos int vol W-valve	1/16 x .4mm 175C/1000psi liq .06ul E
SSACI4WE.1	Rotor seal 4 port 2-pos int vol W-valve	1/16 x .4mm 175C/1000psi liq .1ul E
SSACI4WE.2	Rotor seal 4 port 2-pos int vol W-valve	1/16 x .4mm 175C/1000psi liq .2ul E
SSACI4WE.5	Rotor seal 4 port 2-pos int vol W-valve	1/16 x .4mm 175C/1000psi liq .5ul E
SSACSC10MWE	Rotor seal 10 mpos common outlet MW valve	1/16 x 1mm 200C/200psi gas N60/E
SSACSC12MWE	Rotor seal 12 mpos common outlet MW valve	1/16 x 1mm 200C/200psi gas N60/E
SSACSC16MWE	Rotor seal 16 mpos common outlet MW valve	1/16 x 1mm 200C/200psi gas N60/E
SSACSC6MWE	Rotor seal 6 mpos common outlet MW valve	1/16 x 1mm 200C/200psi gas N60/E
SSACSD10MWE	Rotor seal 10 mpos dead-end path MW-valve	1/16 x .75mm 200C/400psi gas E
SSACSD10UW	Rotor seal 10 mpos dead-end path UW-valve	1/16 x .4mm 75C/5000psi liq E
SSACSD12MWE	Rotor seal 12 mpos dead-end path MW-valve	1/16 x .75mm 200C/400psi gas E
SSACSD16MWE	Rotor seal 16 mpos dead-end path MW-valve	1/16 x .75mm 200C/400psi gas E
SSACSD4UW	Rotor seal 4 mpos dead-end path UW-valve	1/16 x .4mm 75C/5000psi liq E
SSACSD6MWE	Rotor seal 6 mpos dead-end path MW-valve	1/16 x .75mm 200C/400psi gas E
SSACSD6UW	Rotor seal 6 mpos dead-end path UW-valve	1/16 x .4mm 75C/5000psi liq E
SSACSF10MWE	Rotor seal 10 mpos flow-through MW-valve	1/16 x 1mm 200C/200psi gas E
SSACSF12MWE	Rotor seal 12 mpos flow-through MW-valve	1/16 x 1mm 200C/200psi gas E
SSACSF16MWE	Rotor seal 16 mpos flow-through MW-valve	1/16 x 1mm 200C/200psi gas E
SSACSF6MWE	Rotor seal 6 mpos flow-through MW-valve	1/16 x 1mm 200C/200psi gas E
SSACST10MWE	Rotor seal 10 mpos trapping path MW-valve	1/16 x .75mm 200C/200psi gas E
SSACST12MWE	Rotor seal 12 mpos trapping path MW-valve	1/16 x .75mm 200C/200psi gas E
SSACST16MWE	Rotor seal 16 mpos trapping path MW-valve	1/16 x .75mm 200C/200psi gas E
SSACST4UW	Rotor seal 4 mpos trapping-path UW-valve	1/16 x .4mm 75C/5000psi liq E
SSACST6MWE	Rotor seal 6 mpos trapping path MW-valve	1/16 x .75mm 200C/200psi gas E
SSACST6UW	Rotor seal 6 mpos trapping-path UW-valve	1/16 x .4mm 75C/5000psi liq E
SSACSTF10MWE	Rotor seal 10 mpos trap/flow path MW-valve	1/16 x .75mm 200C/200psi gas E
SSACSTF12MWE	Rotor seal 12 mpos trap/flow path MW-valve	1/16 x .75mm 200C/200psi gas E
SSACSTF16MWE	Rotor seal 16 mpos trap/flow path MW-valve	1/16 x .75mm 200C/200psi gas E
SSACSTF6MWE	Rotor seal 6 mpos trap/flow path MW-valve	1/16 x .75mm 200C/200psi gas E
SSAI4UWE.2	Rotor seal 4 port 2-pos int vol UW-valve	1/8 x .75mm 175C/1000psi liq .2ul E
SSAI4UWE.5	Rotor seal 4 port 2-pos int vol UW-valve	1/8 x .75mm 175C/1000psi liq .5ul E
SSAI4UWE1	Rotor seal 4 port 2-pos int vol UW-valve	1/8 x .75mm 175C/1000psi liq 1ul E
SSAI4UWE2	Rotor seal 4 port 2-pos int vol UW-valve	1/8 x .75mm 175C/1000psi liq 2ul E
SSAL10UW	Rotor seal 10 port 2-pos UW-valve	1/8 x 1.0mm 75C/5000psi liq H
SSAL4UW	Rotor seal 4 port 2-pos UW-valve	1/8 x 1.7mm 75C/5000psi liq H
SSAL6UW	Rotor seal 6 port 2-pos UW-valve	1/8 x 1.7mm 75C/5000psi liq H
SSAL8UW	Rotor seal 8 port 2-pos UW-valve	1/8 x 1.3mm 75C/5000psi liq H
SSAN10WE	Rotor seal 10 port 2-pos W-valve	1/32 x .25mm 225C/400psi gas E
SSAN10WT	Rotor seal 10 port 2-pos W-valve	1/32 x .25mm 300C/300psi gas T
SSAN4WE	Rotor seal 4 port 2-pos W-valve	1/32 x .25mm 225C/400psi gas E
SSAN4WT	Rotor seal 4 port 2-pos W-valve	1/32 x .25mm 350C/300psi gas T
SSAN6WE	Rotor seal 6 port 2-pos W-valve	1/32 x .25mm 250C/400psi gas E
SSAN6WT	Rotor seal 6 port 2-pos W-valve	1/32 x .25mm 350C/300psi gas T
SSAN8WE	Rotor seal 8 port 2-pos W-valve	1/32 x .25mm 225C/400psi gas E
SSAN8WT	Rotor seal 8 port 2-pos W-valve	1/32 x .25mm 350C/300psi gas T
SSANI4WE.06	Rotor seal 4 port 2-pos int vol W-valve	1/32 x .25mm 175C/1000psi liq .06ul E