

VICIValco-Cheminert PRODUCT LIST 2012

(Ctrl F)
> Cat.#s

> Current System AUD Prices



SSANI4WE.1	Rotor seal 4 port 2-pos int vol W-valve	1/32 x .25mm 175C/1000psi liq .1ul E
SSANI4WE.2	Rotor seal 4 port 2-pos int vol W-valve	1/32 x .25mm 175C/1000psi liq .2ul E
SSANI4WE.5	Rotor seal 4 port 2-pos int vol W-valve	1/32 x .25mm 175C/1000psi liq .5 ul E
SSASC10MWE	Rotor seal 10 mpos common outlet MW valve	1/8 x 1mm 200C/200psi gas E
SSASC12MWE	Rotor seal 12 mpos common outlet MW valve	1/8 x 1mm 200C/200psi gas E
SSASC16MWE	Rotor seal 16 mpos common outlet MW valve	1/8 x 1mm 200C/200psi gas E
SSASC6MWE	Rotor seal 6 mpos common outlet MW valve	1/8 x 1mm 200C/200psi gas E
SSASD10MWE	Rotor seal 10 mpos dead-end path MW-valve	1/8 x 1mm 200C/200psi gas E
SSASD12MWE	Rotor seal 12 mpos dead-end path MW-valve	1/8 x 1mm 200C/200psi gas E
SSASD16MWE	Rotor seal 16 mpos dead-end path MW-valve	1/8 x 1mm 200C/200psi gas E
SSASD4UW	Rotor seal 4 mpos dead-end path UW-valve	1/8 x .75mm 75C/5000psi liq E
SSASD6MWE	Rotor seal 6 mpos dead-end path MW-valve	1/8 x 1mm 200C/400psi gas E
SSASD6UW	Rotor seal 6 mpos dead-end path UW-valve	1/8 x .75mm 75C/5000psi liq E
SSASD8UW	Rotor seal 8 mpos dead-end path UW-valve	1/8 x .75mm 75C/5000psi liq E
SSASF10MWE	Rotor seal 10 mpos flow-through MW-valve	1/8 x 1mm 200C/200psi gas E
SSASF12MWE	Rotor seal 12 mpos flow-through MW-valve	1/8 x 1mm 200C/200psi gas E
SSASF16MWE	Rotor seal 16 mpos flow-through MW-valve	1/8 x 1mm 200C/200psi gas E
SSASF6MWE	Rotor seal 6 mpos flow-through MW-valve	1/8 x 1mm 200C/200psi gas E
SSAST10MWE	Rotor seal 10 mpos trapping path MW-valve	1/8 x 1mm 200C/200psi gas E
SSAST12MWE	Rotor seal 12 mpos trapping path MW-valve	1/8 x 1mm 200C/200psi gas E
SSAST16MWE	Rotor seal 16 mpos trapping path MW-valve	1/8 x 1mm 200C/200psi gas E
SSAST6MWE	Rotor seal 6 mpos trapping path MW-valve	1/8 x 1mm 200C/200psi gas E
SSASTF10MWE	Rotor seal 10 mpos trap/flow path MWvalve	1/8 x 1mm 200C/200psi gas E
SSASTF12MWE	Rotor seal 12 mpos trap/flow path MWvalve	1/8 x 1mm 200C/200psi gas E
SSASTF16MWE	Rotor seal 16 mpos trap/flow path MWvalve	1/8 x 1mm 200C/200psi gas E
SSASTF6MWE	Rotor seal 6 mpos trap/flow path MW-valve	1/8 x 1mm 200C/200psi gas E
SSAVL4MWE2	Rotor seal 4 port 2 pos MW-valve	1/4 x 4mm 75C/100psi gas E2
SSAVL6MWE2	Rotor seal 6 port 2 pos MW-valve	1/4 x 4mm 75C/100psi gas E2
SSAVL8MWE2	Rotor seal 8 port 2 pos MW-valve	1/4 x 4mm 75C/100psi gas E2
SSAVLSC4MWE2	Rotor seal 4 mpos common outlet MW valve	1/4 x 4mm 75C/100psi gas E2
SSAVLSC6MWE2	Rotor seal 6 mpos common outlet MW valve	1/4 x 4mm 75C/100psi gas E2
SSAVLSC8MWE2	Rotor seal 8 mpos common outlet MW valve	1/4 x 4mm 75C/100psi gas E2
SSAVLSD10MWE2	Rotor seal 10 mpos dead-end path MW-valve	1/4 x 4mm 75C/100psi gas E2
SSAVLSD4MWE2	Rotor seal 4 mpos dead-end path MW-valve	1/4 x 4mm 75C/100psi gas E2
SSAVLSD6MWE2	Rotor seal 6 mpos dead-end path MW-valve	1/4 x 4mm 75C/100psi gas E2
SSAVLSD8MWE2	Rotor seal 8 mpos dead-end path MW-valve	1/4 x 4mm 75C/100psi gas E2
SSAVLSF4MWE2	Rotor seal 4 mpos flow-through MW-valve	1/4 x 4mm 75C/100psi gas E2
SSAVLSF6MWE2	Rotor seal 6 mpos flow-through MW-valve	1/4 x 4mm 75C/100psi gas E2
SSAVLSF8MWE2	Rotor seal 8 mpos flow-through MW-valve	1/4 x 4mm 75C/100psi gas E2
SVI-110	Serial valve interface 110Vac	Non-CE !!!
SVI-220	Serial valve interface 220Vac	Non-CE !!!
SWH4	Socket wrench handle 1/4in	for 1/16in nuts
T100C10-10	Tube-kit 1/16in .010in /.25mm	100 cm long 316SS 10/pkg
T100C10-100	Tube-kit 1/16in .010in /.25mm	100 cm long 316SS 100/pkg
T100C10-50	Tube-kit 1/16in .010in /.25mm	100 cm long 316SS 50/pkg
T100C10D	Tube-kit 1/16in .010in /.25mm	100 cm long 316SS 2/pkg
T100C20-10	Tube-kit 1/16in .020in /.50mm	100 cm long 316SS 10/pkg
T100C20-100	Tube-kit 1/16in .020in /.50mm	100 cm long 316SS 100/pkg
T100C20-50	Tube-kit 1/16in .020in /.50mm	100 cm long 316SS 50/pkg
T100C20D	Tube-kit 1/16in .020in /.50mm	100 cm long 316SS 2/pkg
T100C30-10	Tube-kit 1/16in .030in /.75mm	100 cm long 316SS 10/pkg
T100C30-100	Tube-kit 1/16in .030in /.75mm	100 cm long 316SS 100/pkg
T100C30-50	Tube-kit 1/16in .030in /.75mm	100 cm long 316SS 50/pkg
T100C30D	Tube-kit 1/16in .030in /.75mm	100 cm long 316SS 2/pkg
T100C40-10	Tube-kit 1/16in .040in /1.0mm	100 cm long 316SS 10/pkg
T100C40-100	Tube-kit 1/16in .040in /1.0mm	100 cm long 316SS 100/pkg
T100C40-50	Tube-kit 1/16in .040in /1.0mm	100 cm long 316SS 50/pkg
T100C40D	Tube-kit 1/16in .040in /1.0mm	100 cm long 316SS 2/pkg
T100N10-10	Tube-kit 1/32in .010in /.25mm	100 cm long 316SS 10/pkg
T100N10-100	Tube-kit 1/32in .010in /.25mm	100 cm long 316SS 100/pkg
T100N10-50	Tube-kit 1/32in .010in /.25mm	100 cm long 316SS 50/pkg