

VICIValco-Cheminert PRODUCT LIST 2012

(Ctrl F)
> Cat.#s

> Current System AUD Prices



T100N10D	Tube-kit 1/32in .010in /.25mm	100 cm long 316SS 2/pkg
T100N20-10	Tube-kit 1/32in .020in /.50mm	100 cm long 316SS 10/pkg
T100N20-100	Tube-kit 1/32in .020in /.50mm	100 cm long 316SS 100/pkg
T100N20-50	Tube-kit 1/32in .020in /.50mm	100 cm long 316SS 50/pkg
T100N20D	Tube-kit 1/32in .020in /.50mm	100 cm long 316SS 2/pkg
T10C10-10	Tube-kit 1/16in .010in /.25mm	10 cm long 316SS 10/pkg
T10C10-100	Tube-kit 1/16in .010in /.25mm	10 cm long 316SS 100/pkg
T10C10-50	Tube-kit 1/16in .010in /.25mm	10 cm long 316SS 50/pkg
T10C10D	Tube-kit 1/16in .010in /.25mm	10 cm long 316SS 2/pkg
T10C20-10	Tube-kit 1/16in .020in /.50mm	10 cm long 316SS 10/pkg
T10C20-100	Tube-kit 1/16in .020in /.50mm	10 cm long 316SS 100/pkg
T10C20-50	Tube-kit 1/16in .020in /.50mm	10 cm long 316SS 50/pkg
T10C20D	Tube-kit 1/16in .020in /.50mm	10 cm long 316SS 2/pkg
T10C30-10	Tube-kit 1/16in .030in /.75mm	10 cm long 316SS 10/pkg
T10C30-100	Tube-kit 1/16in .030in /.75mm	10 cm long 316SS 100/pkg
T10C30-50	Tube-kit 1/16in .030in /.75mm	10 cm long 316SS 50/pkg
T10C30D	Tube-kit 1/16in .030in /.75mm	10 cm long 316SS 2/pkg
T10C40-10	Tube-kit 1/16in .040in /1.0mm	10 cm long 316SS 10/pkg
T10C40-100	Tube-kit 1/16in .040in /1.0mm	10 cm long 316SS 100/pkg
T10C40-50	Tube-kit 1/16in .040in /1.0mm	10 cm long 316SS 50/pkg
T10C40D	Tube-kit 1/16in .040in /1.0mm	10 cm long 316SS 2/pkg
T10C5-10	Tube-kit 1/16in .005in /.12mm	10 cm long 316SS 10/pkg
T10C5-100	Tube-kit 1/16in .005in /.12mm	10 cm long 316SS 100/pkg
T10C5-50	Tube-kit 1/16in .005in /.12mm	10 cm long 316SS 50/pkg
T10C5D	Tube-kit 1/16in .005in /.12mm	10 cm long 316SS 2/pkg
T10N10-10	Tube-kit 1/32in .010in /.25mm	10 cm long 316SS 10/pkg
T10N10-100	Tube-kit 1/32in .010in /.25mm	10 cm long 316SS 100/pkg
T10N10-50	Tube-kit 1/32in .010in /.25mm	10 cm long 316SS 50/pkg
T10N10D	Tube-kit 1/32in .010in /.25mm	10 cm long 316SS 2/pkg
T10N20-10	Tube-kit 1/32in .020in /.50mm	10 cm long 316SS 10/pkg
T10N20-100	Tube-kit 1/32in .020in /.50mm	10 cm long 316SS 100/pkg
T10N20-50	Tube-kit 1/32in .020in /.50mm	10 cm long 316SS 50/pkg
T10N20D	Tube-kit 1/32in .020in /.50mm	10 cm long 316SS 2/pkg
T10N5-10	Tube-kit 1/32in .005in /.12mm	10 cm long 316SS 10/pkg
T10N5-100	Tube-kit 1/32in .005in /.12mm	10 cm long 316SS 100/pkg
T10N5-50	Tube-kit 1/32in .005in /.12mm	10 cm long 316SS 50/pkg
T10N5D	Tube-kit 1/32in .005in /.12mm	10 cm long 316SS 2/pkg
T20C10-10	Tube-kit 1/16in .010in /.25mm	20 cm long 316SS 10/pkg
T20C10-100	Tube-kit 1/16in .010in /.25mm	20 cm long 316SS 100/pkg
T20C10-50	Tube-kit 1/16in .010in /.25mm	20 cm long 316SS 50/pkg
T20C10D	Tube-kit 1/16in .010in /.25mm	20 cm long 316SS 2/pkg
T20C20-10	Tube-kit 1/16in .020in /.50mm	20 cm long 316SS 10/pkg
T20C20-100	Tube-kit 1/16in .020in /.50mm	20 cm long 316SS 100/pkg
T20C20-50	Tube-kit 1/16in .020in /.50mm	20 cm long 316SS 50/pkg
T20C20D	Tube-kit 1/16in .020in /.50mm	20 cm long 316SS 2/pkg
T20C30-10	Tube-kit 1/16in .030in /.75mm	20 cm long 316SS 10/pkg
T20C30-100	Tube-kit 1/16in .030in /.75mm	20 cm long 316SS 100/pkg
T20C30-50	Tube-kit 1/16in .030in /.75mm	20 cm long 316SS 50/pkg
T20C30D	Tube-kit 1/16in .030in /.75mm	20 cm long 316SS 2/pkg
T20C40-10	Tube-kit 1/16in .040in /1.0mm	20 cm long 316SS 10/pkg
T20C40-100	Tube-kit 1/16in .040in /1.0mm	20 cm long 316SS 100/pkg
T20C40-50	Tube-kit 1/16in .040in /1.0mm	20 cm long 316SS 50/pkg
T20C40D	Tube-kit 1/16in .040in /1.0mm	20 cm long 316SS 2/pkg
T20C5-10	Tube-kit 1/16in .005in /.12mm	20 cm long 316SS 10/pkg
T20C5-100	Tube-kit 1/16in .005in /.12mm	20 cm long 316SS 100/pkg
T20C5-50	Tube-kit 1/16in .005in /.12mm	20 cm long 316SS 50/pkg
T20C5D	Tube-kit 1/16in .005in /.12mm	20 cm long 316SS 2/pkg
T20N10-10	Tube-kit 1/32in .010in /.25mm	20 cm long 316SS 10/pkg
T20N10-100	Tube-kit 1/32in .010in /.25mm	20 cm long 316SS 100/pkg
T20N10-50	Tube-kit 1/32in .010in /.25mm	20 cm long 316SS 50/pkg
T20N10D	Tube-kit 1/32in .010in /.25mm	20 cm long 316SS 2/pkg