

VICIValco-Cheminert PRODUCT LIST 2012

(Ctrl F)
> Cat.#s

> Current System AUD Prices



T20N20-10	Tube-kit 1/32in .020in /.50mm	20 cm long 316SS 10/pkg
T20N20-100	Tube-kit 1/32in .020in /.50mm	20 cm long 316SS 100/pkg
T20N20-50	Tube-kit 1/32in .020in /.50mm	20 cm long 316SS 50/pkg
T20N20D	Tube-kit 1/32in .020in /.50mm	20 cm long 316SS 2/pkg
T20N5-10	Tube-kit 1/32in .005in /.12mm	20 cm long 316SS 10/pkg
T20N5-100	Tube-kit 1/32in .005in /.12mm	20 cm long 316SS 100/pkg
T20N5-50	Tube-kit 1/32in .005in /.12mm	20 cm long 316SS 50/pkg
T20N5D	Tube-kit 1/32in .005in /.12mm	20 cm long 316SS 2/pkg
T30C10-10	Tube-kit 1/16in .010in /.25mm	30 cm long 316SS 10/pkg
T30C10-100	Tube-kit 1/16in .010in /.25mm	30 cm long 316SS 100/pkg
T30C10-50	Tube-kit 1/16in .010in /.25mm	30 cm long 316SS 50/pkg
T30C10D	Tube-kit 1/16in .010in /.25mm	30 cm long 316SS 2/pkg
T30C20-10	Tube-kit 1/16in .020in /.50mm	30 cm long 316SS 10/pkg
T30C20-100	Tube-kit 1/16in .020in /.50mm	30 cm long 316SS 100/pkg
T30C20-50	Tube-kit 1/16in .020in /.50mm	30 cm long 316SS 50/pkg
T30C20D	Tube-kit 1/16in .020in /.50mm	30 cm long 316SS 2/pkg
T30C30-10	Tube-kit 1/16in .030in /.75mm	30 cm long 316SS 10/pkg
T30C30-100	Tube-kit 1/16in .030in /.75mm	30 cm long 316SS 100/pkg
T30C30-50	Tube-kit 1/16in .030in /.75mm	30 cm long 316SS 50/pkg
T30C30D	Tube-kit 1/16in .030in /.75mm	30 cm long 316SS 2/pkg
T30C40-10	Tube-kit 1/16in .040in /1.0mm	30 cm long 316SS 10/pkg
T30C40-100	Tube-kit 1/16in .040in /1.0mm	30 cm long 316SS 100/pkg
T30C40-50	Tube-kit 1/16in .040in /1.0mm	30 cm long 316SS 50/pkg
T30C40D	Tube-kit 1/16in .040in /1.0mm	30 cm long 316SS 2/pkg
T30C5-10	Tube-kit 1/16in .005in /.12mm	30 cm long 316SS 10/pkg
T30C5-100	Tube-kit 1/16in .005in /.12mm	30 cm long 316SS 100/pkg
T30C5-50	Tube-kit 1/16in .005in /.12mm	30 cm long 316SS 50/pkg
T30C5D	Tube-kit 1/16in .005in /.12mm	30 cm long 316SS 2/pkg
T30N10-10	Tube-kit 1/32in .010in /.25mm	30 cm long 316SS 10/pkg
T30N10-100	Tube-kit 1/32in .010in /.25mm	30 cm long 316SS 100/pkg
T30N10-50	Tube-kit 1/32in .010in /.25mm	30 cm long 316SS 50/pkg
T30N10D	Tube-kit 1/32in .010in /.25mm	30 cm long 316SS 2/pkg
T30N20-10	Tube-kit 1/32in .020in /.50mm	30 cm long 316SS 10/pkg
T30N20-100	Tube-kit 1/32in .020in /.50mm	30 cm long 316SS 100/pkg
T30N20-50	Tube-kit 1/32in .020in /.50mm	30 cm long 316SS 50/pkg
T30N20D	Tube-kit 1/32in .020in /.50mm	30 cm long 316SS 2/pkg
T30N5-10	Tube-kit 1/32in .005in /.12mm	30 cm long 316SS 10/pkg
T30N5-100	Tube-kit 1/32in .005in /.12mm	30 cm long 316SS 100/pkg
T30N5-50	Tube-kit 1/32in .005in /.12mm	30 cm long 316SS 50/pkg
T30N5D	Tube-kit 1/32in .005in /.12mm	30 cm long 316SS 2/pkg
T50C10-10	Tube-kit 1/16in .010in /.25mm	50 cm long 316SS 10/pkg
T50C10-100	Tube-kit 1/16in .010in /.25mm	50 cm long 316SS 100/pkg
T50C10-50	Tube-kit 1/16in .010in /.25mm	50 cm long 316SS 50/pkg
T50C10D	Tube-kit 1/16in .010in /.25mm	50 cm long 316SS 2/pkg
T50C20-10	Tube-kit 1/16in .020in /.50mm	50 cm long 316SS 10/pkg
T50C20-100	Tube-kit 1/16in .020in /.50mm	50 cm long 316SS 100/pkg
T50C20-50	Tube-kit 1/16in .020in /.50mm	50 cm long 316SS 50/pkg
T50C20D	Tube-kit 1/16in .020in /.50mm	50 cm long 316SS 2/pkg
T50C30-10	Tube-kit 1/16in .030in /.75mm	50 cm long 316SS 10/pkg
T50C30-100	Tube-kit 1/16in .030in /.75mm	50 cm long 316SS 100/pkg
T50C30-50	Tube-kit 1/16in .030in /.75mm	50 cm long 316SS 50/pkg
T50C30D	Tube-kit 1/16in .030in /.75mm	50 cm long 316SS 2/pkg
T50C40-10	Tube-kit 1/16in .040in /1.0mm	50 cm long 316SS 10/pkg
T50C40-100	Tube-kit 1/16in .040in /1.0mm	50 cm long 316SS 100/pkg
T50C40-50	Tube-kit 1/16in .040in /1.0mm	50 cm long 316SS 50/pkg
T50C40D	Tube-kit 1/16in .040in /1.0mm	50 cm long 316SS 2/pkg
T50C5-10	Tube-kit 1/16in .005in /.12mm	50 cm long 316SS 10/pkg
T50C5-100	Tube-kit 1/16in .005in /.12mm	50 cm long 316SS 100/pkg
T50C5-50	Tube-kit 1/16in .005in /.12mm	50 cm long 316SS 50/pkg
T50C5D	Tube-kit 1/16in .005in /.12mm	50 cm long 316SS 2/pkg
T50N10-10	Tube-kit 1/32in .010in /.25mm	50 cm long 316SS 10/pkg