

VICIValco-Cheminert PRODUCT LIST 2012

[Ctrl F]
> Cat.#s

> Current System AUD Prices



TTZ130-25M	Tubing 1/16in OD .030in / .75mm ID	ETFE 25m/pkg
TTZ130-5M	Tubing 1/16in OD .030in / .75mm ID	ETFE 5m/pkg
TTZ260-10M	Tubing 1/8in OD .060in / 1.52mm ID	ETFE 10m/pkg
TTZ260-25M	Tubing 1/8in OD .060in / 1.52mm ID	ETFE 25m/pkg
TTZ260-5M	Tubing 1/8in OD .060in / 1.52mm ID	ETFE 5m/pkg
V-EMPMCR-HP1100	Remote cable VICI micro E mpos. actuator	4/6 pos to HP1100 G1351A interface board
V-EMPMCR-HP1100-10	Remote cable VICI micro E mpos. actuator	8/10 pos to HP1100 G1351A interface board
V-EMPMCR-HP6890	BCD cable VICI micro E mpos. actuator	(26 pin connector) to HP 6890/7890
V-EMPMCR-HP6890N	BCD cable VICI micro E mpos. actuator	(26 pin connector) to HP 6890N/7890N
V-EMPMCR-WA2690	Remote cable VICI micro E mpos. actuator	4/6pos to Waters 2690 Separation Module
V-EMPMCR-WA2690-1C	Remote cable VICI micro E mpos. actuator	10pos to Waters 2690 Separation Module
VISF.5FPK	Syringe fillport for 1/32in connection fingertight	for .75in /19mm long needle 26Gauge OD PEEK
VISF-1	Syringe fillport for 1/16in connection	for .75in /19mm long needle 22Gauge OD
VISF-2	Syringe fillport for 1/16in connection	for 2.0in /51mm long needle 22Gauge OD
VISF-A	Syringe fillport for 1/8in fittings	for 2.0in /51mm long needle 22Gauge OD
VISL-1	Liner replacement for VISF-1 or C-VISF-1L	PTFE
VISL-1H	Liner replacement for C-VISF-1H	PTFE
VISL-2	Liner replacement for VISF-2 or VISF-A	PTFE
V-RA-24VDC-HP6890	Relay assy. for 2pos micro actuator	to HP6890/7890 24VDC
V-RA-24VDC-VA3800	Relay assy. for 2pos micro actuator	to VA3800 24VDC
V-RA-5VDC-HP1100	Relay assy. for 2pos micro actuator	to HP1100 external event 5VDC from micr act.
V-RA-5VDC-WA2690	Relay assy. for 2pos micro actuator	to WA2690 external event 5VDC from micro act.
VSH	Valve spanner handle for mpos valve	
V-SV-D32-110VAC	3-way manifold solenoid valve assy.	110Va CE
V-SV-D32-220VAC	3-way manifold solenoid valve assy.	220Vac CE
V-SV-D32-24VUC	3-way manifold solenoid valve assy.	24VacVdc CE
V-SV-S42-120VAC	4-way solenoid air valve	120Vac CE
V-SV-S42-220VAC	4-way solenoid air valve	220Vac CE
V-SV-S42-24VUC	4-way solenoid air valve	24VacVdc CE
WMMA	Close mount hdw. manual W/UW	2-pos 3468 port valves
WMMA10	Close mount hdw. manual	valves with unthreaded mounting holes
WMMASO	Manual W-knob for use with standoff	2-pos W-type valves
XLZN1-10	Nut 1/16in 25mm long SS 10/pkg	
XLZN2-10	Nut 1/8in 27mm long SS 10/pkg	
Z10M1	Manifold 1/16in 10 inlets 1 outlet	inlet .25mm/outlet .75mm bore SS
Z10M1PK	Manifold 1/16in 10 inlets 1 outlet	inlet .25mm/outlet .75mm bore PEEK
Z10M2	Manifold 1/8in 10 inlets 1 outlet	inlet 2mm/outlet 2mm bore SS
Z12M1	Manifold 1/16in 12 inlets 1 outlet	inlet .25mm/outlet .75mm bore SS
Z12M1PK	Manifold 1/16in 12 inlets 1 outlet	inlet .25mm/outlet .75mm bore PEEK
Z12M2	Manifold 1/8in 12 inlets 1 outlet	inlet 2mm/outlet 2mm bore SS
Z14M1	Manifold 1/16in 14 inlets 1 outlet	inlet .25mm/outlet .75mm bore SS
Z14M1PK	Manifold 1/16in 14 inlets 1 outlet	inlet .25mm/outlet .75mm bore PEEK
Z16M1PK	Manifold 1/16in 16 inlets 1 outlet	inlet .25mm/outlet .75mm bore PEEK
Z4M1	Manifold 1/16in 4 inlets 1 outlet	inlet .25mm/outlet .75mm bore SS
Z4M1PK	Manifold 1/16in 4 inlets 1 outlet	inlet .25mm/outlet .75mm bore PEEK
Z4M2	Manifold 1/8in 4 inlets 1 outlet	inlet 2mm/outlet 2mm bore SS
Z6M1	Manifold 1/16in 6 inlets 1 outlet	inlet .25mm/outlet .75mm bore SS
Z6M1PK	Manifold 1/16in 6 inlets 1 outlet	inlet .25mm/outlet .75mm bore PEEK
Z6M2	Manifold 1/8in 6 inlets 1 outlet	inlet 2mm/outlet 2mm bore SS
Z8M1	Manifold 1/16in 8 inlets 1 outlet	inlet .25mm/outlet .75mm bore SS
Z8M1PK	Manifold 1/16in 8 inlets 1 outlet	inlet .25mm/outlet .75mm bore PEEK
Z8M2	Manifold 1/8in 8 inlets 1 outlet	inlet 2mm/outlet 2mm bore SS
ZAOR11	Internal adaptor 1/16in to 10-32 thread	O-ring seal SS
ZAOR12	Internal adaptor 1/16in to 5/16-24 thread	O-ring seal SS
ZAOR22	Internal adaptor 1/8in to 5/16-24 thread	O-ring seal SS
ZBAA1	Aerosol adaptor bulkhead union 1/16in SS	Bore 0.75 mm
ZBNV1	Micrometering needle valve bulkhead 2-225 ml/min	1/16in int 2um screenlubricated 225CSS/Viton
ZBNV1-D	Micrometering needle valve bulkhead 2-225 ml/min	1/16in int 2um screen225Cnon-lubricatedSS/Viton
ZBNV1F	Micrometering needle valve bulkhead 2-175 ml/min	1/16in int 2um screenlubricated225CSS/Viton
ZBNV1F-D	Micrometering needle valve bulkhead 2-175 ml/min	1/16in int 2um screen225Cnon-lubricatedSS/Viton
ZBNV1F-KZ	Micrometering needle valve bulkhead 2-175 ml/min	1/16in int 2um screen315Cnon-lubricatSS/Kalrez