



# VICI Valco-Cheminert PRODUCT LIST 2012

ZLA-1	Female luer adapter	to 1/16in fittings
ZLA-2	Female luer adapter	to 1/8in fittings
ZLCA1PK	Cheminert adaptor 1/4-28 to 10-32 ZDV	0.5mm bore PEEK
ZLTA41	Tube adaptor 1/4in x 1/16in 2.075in (52.70 mm) long	1/16in bore SS
ZN.5	Nut 1/32in standard	SS
ZN.5-10	Nut 1/32in standard SS 10/pkg	
ZN.5FPK	Nut 1/32 fingertight 10.7mm long	PEEK
ZN.5FPK-10	Nut 1/32in fingertight 10.7 mm long	PEEK 10/pkg
ZN1	Nut 1/16in standard	SS SS
ZN1-10	Nut 1/16in standard SS 10/pkg	
ZN1FPK	Nut 1/16in fingertight 22.4mm long	PEEK
ZN1FPK-10	Nut 1/16in fingertight 22.4mm long	PEEK 10/pkg
ZN1PK-10	Nut 1/16in hex 11.4mm long	PEEK 10/pkg
ZN1Q	Nut 1/16in length .43in	SS
ZN2-10	Nut 1/8in standard SS 10/pkg	
ZN2PK-10	Nut 1/8in hex 15.7mm long	PEEK 10/pkg
ZN4-10	Nut 1/4in standard SS 10/pkg	
ZN1FKF-5	Nut 1/16in No Twist fingertight PEEK	with CTFE ferrule 5/pkg
ZN1FPK-5	Nut 1/16in No Twist fingertight PEEK	with PEEK ferrule 5/pkg
ZN1FPKG-5	Nut 1/16in No Twist fingertight PEEK	with glass-filled PEEK ferrule 5/pkg
ZN1KF-5	Nut 1/16in No Twist hex short PEEK	with CTFE ferrule 5/pkg
ZN1PK-5	Nut 1/16in No Twist hex short PEEK	with PEEK ferrule 5/pkg
ZN1PKG-5	Nut 1/16in No Twist hex short PEEK	with glass-filled PEEK ferrule 5/pkg
ZNFT	Tightening Tool for PEEK hex-head	1/16in nuts blue
ZP.5	Plug 1/32in	SS
ZP.5FPK	Plug 1/32in fingertight PEEK	
ZP.5H	Plug 1/32in high pressure	SS
ZP1	Plug 1/16in	SS
ZP1FPK	Plug 1/16in fingertight PEEK	
ZP1H	Plug 1/16in high pressure	SS
ZP2	Plug 1/8in	SS
ZP2H	Plug 1/8in high pressure	SS
ZP2PK	Plug 1/8in hex PEEK	
ZP4	Plug 1/4in	SS
ZRF1.5KF-5	Internal reducing ferrule 1/16in x 1/32in	CTFE 5/pkg
ZRF1.5PK-5	Internal reducing ferrule 1/16in x 1/32in	PEEK 5/pkg
ZRF1.5TFG-5	Internal reducing ferrule 1/16in x 1/32in	PTFE Glass-filled 25% 5/pkg
ZRF1.5V1-5	Internal reducing ferrule 1/16in x 1/32in	Polyimide Virgin 5/pkg
ZRF1.5V-5	Internal reducing ferrule 1/16in x 1/32in	Polyimide Valcon 5/pkg
ZRF2.5KF-5	Internal reducing ferrule 1/8in x 1/32in	CTFE 5/pkg
ZRF2.5PK-5	Internal reducing ferrule 1/8in x 1/32in	PEEK 5/pkg
ZRF2.5TFG-5	Internal reducing ferrule 1/8in x 1/32in	PTFE Glass-filled 25% 5/pkg
ZRF2.5V1-5	Internal reducing ferrule 1/8in x 1/32in	Polyimide Virgin 5/pkg
ZRF2.5V-5	Internal reducing ferrule 1/8in x 1/32in	Polyimide Valcon 5/pkg
ZRF21KF-5	Internal reducing ferrule 1/8in x 1/16in	CTFE 5/pkg
ZRF21PK-5	Internal reducing ferrule 1/8in x 1/16in	PEEK 5/pkg
ZRF21TFG-5	Internal reducing ferrule 1/8in x 1/16in	PTFE Glass-filled 25% 5/pkg
ZRF21V1-5	Internal reducing ferrule 1/8in x 1/16in	Polyimide Virgin 5/pkg
ZRF21V-5	Internal reducing ferrule 1/8in x 1/16in	Polyimide Valcon 5/pkg
ZRF41KF-5	Internal reducing ferrule 1/4in x 1/16in	CTFE 5/pkg
ZRF41PK-5	Internal reducing ferrule 1/4in x 1/16in	PEEK 5/pkg
ZRF41TFG-5	Internal reducing ferrule 1/4in x 1/16in	PTFE Glass-filled 25% 5/pkg
ZRF41V1-5	Internal reducing ferrule 1/4in x 1/16in	Polyimide Virgin 5/pkg
ZRF41V-5	Internal reducing ferrule 1/4in x 1/16in	Polyimide Valcon 5/pkg
ZRF42KF-5	Internal reducing ferrule 1/4in x 1/8in	CTFE 5/pkg
ZRF42PK-5	Internal reducing ferrule 1/4in x 1/8in	PEEK 5/pkg
ZRF42TFG-5	Internal reducing ferrule 1/4in x 1/8in	PTFE Glass-filled 25% 5/pkg
ZRF42V1-5	Internal reducing ferrule 1/4in x 1/8in	Polyimide Virgin 5/pkg
ZRF42V-5	Internal reducing ferrule 1/4in x 1/8in	Polyimide Valcon 5/pkg
ZRU1.5	Reducing union 1/16in x 1/32in	.25mm bore SS
ZRU1.5FPK	Reducing union 1/16in x 1/32in	.25mm bore PEEK