



# VICI Valco-Cheminert PRODUCT LIST 2012

ZU.5XC	Union 1/32in	.15mm bore SS
ZU1	Union 1/16in	.75mm bore SS
ZU1C	Union 1/16in	.25mm bore SS
ZU1CFPK	Union 1/16in fingertight	.25mm bore PEEK
ZU1CPK	Union 1/16in hex	.25mm bore PEEK
ZU1FPK	Union 1/16in fingertight	.75mm bore PEEK
ZU1FPK.5	Filter 1/16in fingertight 0.5 micron filter Ti	.5mm bore PEEK
ZU1L	Union 1/16in	1mm bore SS
ZU1M	Union 1/16in	.5mm bore SS
ZU1MFPK	Union 1/16in fingertight	.5mm bore PEEK
ZU1MPK	Union 1/16in hex	.5mm bore PEEK
ZU1PK	Union 1/16in hex	.75mm bore PEEK
ZU1T	Union 1/16in	1/16in through bore SS
ZU1TFPK	Union 1/16in fingertight	1/16in through bore PEEK
ZU1TPK	Union 1/16in hex	1/16in trough bore PEEK
ZU1XC	Union 1/16in	.15mm bore SS
ZU2	Union 1/8in	.75mm bore 316SS
ZU2L	Union 1/8in	2mm bore 316SS
ZU2LPK	Union 1/8in hex	2mm bore PEEK
ZU2PK	Union 1/8in hex	.75mm bore PEEK
ZU2T	Union 1/8in	1/8in through bore SS
ZU2TPK	Union 1/8in hex	1/8in trough bore PEEK
ZU4	Union 1/4in	.75mm bore SS
ZU4L	Union 1/4in	4.6mm bore SS
ZU4T	Union 1/4in	1/4in through bore SS
ZUF1	Filter union 1/16in	.75mm bore pressed 2 um frit SS
ZUF2	Filter union 1/8in	.75mm bore pressed 2 um frit SS
ZUF4	Filter union 1/4in	4.6mm bore pressed 2 um frit SS
ZUFLKF	Cheminert female luer adapter to 10-32	0.75mm bore CTFE
ZUFLPK	Cheminert female luer adapter to 10-32	0.75mm bore PEEK
ZUFR.5	Filter union 1/32in	.25mm bore removable 2 um screen SS
ZUFR.5F	Filter union 1/32in	.25mm bore removable 2 um frit 316SS
ZUFR1	Filter union 1/16in	.50mm bore removable 2 um screen SS
ZUFR1C	Filter union 1/16in	.25mm bore removable 2 um screen SS
ZUFR1CF	Filter union 1/16in	.25mm bore removable 2 um frit 316SS
ZUFR1F	Filter union 1/16in	.5mm bore removable 2um frit 316SS
ZUFR2	Filter 1/8in	2mm bore removable 2 um screen SS
ZUFR2F	Filter union 1/8in	2mm bore removable 2 um frit 316SS
ZVISF-1PE	Syringe fillport for 1/16in high throughput HPE	for minimum 35mm long needle 22Gauge OD
ZVISF-1PEH	Syringe fillport for 1/16in high throughput HPE	for minimum 35mm long needle 22Gauge OD
ZVISF-1PFA	Fillport ZDV for 1/16in PEEK with PFA bushing	for minimum 35mm long needle 22 Gauge
ZVISF-1PFAH	Fillport ZDV for 1/16in PEEK with PFA bushing HP	for minimum 35mm long needle 22 Gauge
ZX.5	Cross 1/32in .25mm bore SS	
ZX.5FPK	Cross 1/32in fingertight	.25mm bore PEEK
ZX.5L	Cross 1/32in .50mm bore SS	
ZX.5LFPK	Cross 1/32in fingertight	.5mm bore PEEK
ZX1	Cross 1/16in .75mm bore SS	
ZX1C	Cross 1/16in .25mm bore SS	
ZX1CFPK	Cross 1/16in fingertight	.25mm bore PEEK
ZX1FPK	Cross 1/16in fingertight	.75mm bore PEEK
ZX1L	Cross 1/16in 1.0mm bore SS	
ZX1LFPK	Cross 1/16in fingertight	1mm bore PEEK
ZX1M	Cross 1/16in .50mm bore SS	
ZX1MFPK	Cross 1/16in fingertight	.5mm bore PEEK
ZX2	Cross 1/8in .75mm bore SS	
ZX2L	Cross 1/8in 2.0mm bore SS	
ZX2LPK	Cross 1/8in hex	2mm bore PEEK
ZX2PK	Cross 1/8in hex	.75mm bore PEEK
ZX4	Cross 1/4in 1.0mm bore SS	
ZX4L	Cross 1/4in 4.6mm bore SS	
ZXLTA41	Tube adaptor 1/4in x 1/16in 2.800in (71.12 mm) long	1/16in bore SS