



VICI-Jour PRODUCT LIST 2012

| | | | | |
|---------------|---|-----|----|----|
| JR-TSS130-M10 | Tubing Premium SS 1/16in OD x 0.75 mm ID 10 m/pkg | pkg | 10 | m |
| JR-TSS130-M3 | Tubing Premium SS 1/16in OD x 0.75 mm ID 3 m/pkg | pkg | 3 | m |
| JR-TSS140-M10 | Tubing Premium SS 1/16in OD x 1.00 mm ID 10 m/pkg | pkg | 10 | m |
| JR-TSS140-M3 | Tubing Premium SS 1/16in OD x 1.00 mm ID 3 m/pkg | pkg | 3 | m |
| JR-TSS230-M10 | Tubing Premium SS 1/8in OD x 0.75 mm ID 10 m/pkg | pkg | 10 | m |
| JR-TSS230-M3 | Tubing Premium SS 1/8in OD x 0.75 mm ID 3 m/pkg | pkg | 3 | m |
| JR-TSS240-M10 | Tubing Premium SS 1/8in OD x 1.00 mm ID 10 m/pkg | pkg | 10 | m |
| JR-TSS240-M3 | Tubing Premium SS 1/8in OD x 1.00 mm ID 3 m/pkg | pkg | 3 | m |
| JR-TSS260-M10 | Tubing Premium SS 1/8in OD x 1.52 mm ID 10 m/pkg | pkg | 10 | m |
| JR-TSS260-M3 | Tubing Premium SS 1/8in OD x 1.52 mm ID 3 m/pkg | pkg | 3 | m |
| JR-TSS267-M10 | Tubing Premium SS 1/8in OD x 1.70 mm ID 10 m/pkg | pkg | 10 | m |
| JR-TSS267-M3 | Tubing Premium SS 1/8in OD x 1.70 mm ID 3 m/pkg | pkg | 3 | m |
| JR-TSS285-M10 | Tubing Premium SS 1/8in OD x 2.16 mm ID 10 m/pkg | pkg | 10 | m |
| JR-TSS285-M3 | Tubing Premium SS 1/8in OD x 2.16 mm ID 3 m/pkg | pkg | 3 | m |
| JR-55010-5 | Color-It fingertight adapter blue 5/pkg | pkg | 5 | pc |
| JR-55011-5 | Color-It fingertight adapter yellow 5/pkg | pkg | 5 | pc |
| JR-55012-5 | Color-It fingertight adapter green 5/pkg | pkg | 5 | pc |
| JR-55013-5 | Color-It fingertight adapter black 5/pkg | pkg | 5 | pc |
| JR-55014-5 | Color-It fingertight adapter white 5/pkg | pkg | 5 | pc |
| JR-55015-5 | Color-It fingertight adapter red 5/pkg | pkg | 5 | pc |
| JR-55016-12 | Color-It fingertight adapter multi-color assorted 2 pcs. each color 12/pkg | pkg | 12 | pc |
| JR-5502-5 | Fitting PEEK one-piece 10-32 5/pkg | pkg | 5 | pc |
| JR-55080-10 | Adapter PP fingertight sleeve natural 10/pkg | pkg | 10 | pc |
| JR-55080-5 | Adapter PP fingertight sleeve natural 5/pkg | pkg | 5 | pc |
| JR-55081-10 | Adapter PP fingertight sleeve white 10/pkg | pkg | 10 | pc |
| JR-55081-5 | Adapter PP fingertight sleeve white 5/pkg | pkg | 5 | pc |
| JR-55082-10 | Adapter PP fingertight sleeve dark grey 10/pkg | pkg | 10 | pc |
| JR-55082-5 | Adapter PP fingertight sleeve dark grey 5/pkg | pkg | 5 | pc |
| JR-55083-10 | Adapter PP fingertight sleeve black 10/pkg | pkg | 10 | pc |
| JR-55083-5 | Adapter PP fingertight sleeve black 5/pkg | pkg | 5 | pc |
| JR-55084-10 | Adapter PP fingertight sleeve lavender 10/pkg | pkg | 10 | pc |
| JR-55084-5 | Adapter PP fingertight sleeve lavender 5/pkg | pkg | 5 | pc |
| JR-55085-10 | Adapter PP fingertight sleeve red 10/pkg | pkg | 10 | pc |
| JR-55085-5 | Adapter PP fingertight sleeve red 5/pkg | pkg | 5 | pc |
| JR-55086-10 | Adapter PP fingertight sleeve yellow 10/pkg | pkg | 10 | pc |
| JR-55086-5 | Adapter PP fingertight sleeve yellow 5/pkg | pkg | 5 | pc |
| JR-55087-10 | Adapter PP fingertight sleeve orange 10/pkg | pkg | 10 | pc |
| JR-55087-5 | Adapter PP fingertight sleeve orange 5/pkg | pkg | 5 | pc |
| JR-55088-10 | Adapter PP fingertight sleeve brown 10/pkg | pkg | 10 | pc |
| JR-55088-5 | Adapter PP fingertight sleeve brown 5/pkg | pkg | 5 | pc |
| JR-55089-10 | Adapter PP fingertight sleeve green 10/pkg | pkg | 10 | pc |
| JR-55089-5 | Adapter PP fingertight sleeve green 5/pkg | pkg | 5 | pc |
| JR-5508X-12 | Adapter PP fingertight sleeve 6 colors assorted 2 pcs. each 12/pkg | pkg | 12 | pc |
| JR-5508X-24 | Adapter PP fingertight sleeve assorted 2 pcs. per color 24/pkg | pkg | 24 | pc |
| JR-55090-10 | Adapter PP fingertight sleeve blue 10/pkg | pkg | 10 | pc |
| JR-55090-5 | Adapter PP fingertight sleeve blue 5/pkg | pkg | 5 | pc |
| JR-55091-10 | Adapter PP fingertight sleeve purple 10/pkg | pkg | 10 | pc |
| JR-55091-5 | Adapter PP fingertight sleeve purple 5/pkg | pkg | 5 | pc |
| JR-55100-5 | Fitting PEEK one-piece hex-head short 10-32 5/pkg | pkg | 5 | pc |
| JR-55110-5 | Fitting PEEK one-piece hex-head long 10-32 5/pkg | pkg | 5 | pc |
| JR-5520-10 | Fitting PEEK HT 1/16in one-piece hex-head short 10-32 10'000 psi 10/pkg incl. | pkg | 10 | pc |
| JR-5525-10 | Fitting PEEK HT 1/32in one-piece hex-head short 6-40 9000 psi 10/pkg incl. CN | pkg | 10 | pc |
| JR-58000-5 | Fitting PPS hex-head one-piece black 10-32 5/pkg | pkg | 5 | pc |
| JR-CNFT | Tightening Tool for PEEK hex-head 1/32in nuts green | pc | | |
| JR-ZNFT | Tightening Tool for PEEK hex-head 1/16in nuts blue | pc | | |
| JR-55020-5 | Fitting PEEK one-piece natural 10-32 5/pkg | pkg | 5 | pc |
| JR-55021-5 | Fitting PEEK one-piece black 10-32 5/pkg | pkg | 5 | pc |