



VICI-Jour PRODUCT LIST 2012

> Current System AUD Prices

JR-10FR1K	Frit SS 1in diam. x 0.060in thickn. 10 um	pc		
JR-10FR2	Frit SS 1/8in diam. x 0.040in thickn. 10 um	pc		
JR-10FR4	Frit SS 1/4in diam. x 0.040in thickn. 10 um	pc		
JR-10FR6	Frit SS 3/8in diam. x 0.040in thickn. 10 um	pc		
JR-10FR8	Frit SS 1/2in diam. x 0.040in thickn. 10 um	pc		
JR-10FR8TI	Frit Ti 1/2in diam. x 0.040in thickn. 10 um	pc		
JR-1FR1	Frit SS 1/16in diam. x 0.030in thickn. 1 um	pc		
JR-1FR2	Frit SS 1/8in diam. x 0.030in thickn. 1 um	pc		
JR-2FR1	Frit SS 1/16in diam. x 0.030in thickn. 2 um	pc		
JR-2FR1K	Frit SS 1in diam. x 0.060in thickn. 2 um	pc		
JR-2FR1KTI	Frit Ti 1in diam. x 0.060in thickn. 2 um	pc		
JR-2FR1TI	Frit Ti 1/16in diam. x 0.040in thickn. 2 um	pc		
JR-2FR2	Frit SS 1/8in diam. x 0.040in thickn. 2 um	pc		
JR-2FR2TI	Frit Ti 1/8in diam. x 0.040in thickn. 2 um	pc		
JR-2FR4	Frit SS 1/4in diam. x 0.040in thickn. 2 um	pc		
JR-2FR4TI	Frit Ti 1/4in diam. x 0.040in thickn. 2 um	pc		
JR-2FR6	Frit SS 3/8in diam. x 0.040in thickn. 2 um	pc		
JR-2FR6TI	Frit Ti 3/8in diam. x 0.040in thickn. 2 um	pc		
JR-2FR8	Frit SS 1/2in diam. x 0.040in thickn. 2 um	pc		
JR-2FR8TI	Frit Ti 1/2in diam. x 0.040in thickn. 2 um	pc		
JR-1100-05P	Frit SS 4.6 mm diam. 0.5 um PEEK-encased 0.25 x 0.062in thick	pc		
JR-1100-2P	Frit SS 4.6 mm diam. 2 um PEEK-encased 0.25 x 0.062in thick	pc		
JR-1101-05P	Frit SS 3.9 mm diam. 0.5 um PEEK-encased 0.25 x 0.062in thick	pc		
JR-1101-2P	Frit SS 3.9 mm diam. 2 um PEEK-encased 0.25 x 0.062in thick	pc		
JR-1102-05P	Frit SS 3.2 mm diam. 0.5 um PEEK-encased 0.25 x 0.062in thick	pc		
JR-1102-2P	Frit SS 3.2 mm diam. 2 um PEEK-encased 0.25 x 0.062in thick	pc		
JR-1103-05P	Frit SS 3.2 mm diam. 0.5 um PEEK-encased 0.25 x 0.032in thick	pc		
JR-1103-2P	Frit SS 3.2 mm diam. 2 um PEEK-encased 0.25 x 0.032in thick	pc		
JR-1104-05P	Frit SS 2.0 mm diam. 0.5 um PEEK-encased 0.25in x 0.062in thickn.	pc		
JR-1104-2P	Frit SS 2.0 mm diam. 2 um PEEK-encased 0.25 x 0.062in thick	pc		
JR-1110-05P	Frit SS 0.038 diam. 0.5 um PEEK-encased 0.115in x 0.028in thick	pc		
JR-1110-2P	Frit SS 0.038 diam. 2 um PEEK-encased 0.115in x 0.028in thick	pc		
JR-1110-5P	Frit SS 0.038 diam. 5 um PEEK-encased 0.115in x 0.028in thick	pc		
JR-1111-05P	Frit SS 0.077 diam. 0.5 um PEEK-encased 0.115in x 0.028in thick	pc		
JR-1111-10P	Frit SS 0.077 diam. 10 um PEEK-encased 0.115in x 0.028in thick	pc		
JR-1111-10P-5	Frit SS 0.077 diam. 10 um PEEK-encased 0.115in x 0.028in thick	pkg	5	pc
JR-1111-2P	Frit SS 0.077 diam. 2 um PEEK-encased 0.115in x 0.028in thick	pc		
JR-1111-5P	Frit SS 0.077 diam. 5 um PEEK-encased 0.115in x 0.028in thick	pc		
JR-1125-05P	Frit Ti 4.6 mm diam. 0.5 um PEEK-encased 0.25in x 0.062in thick	pc		
JR-1125-10P	Frit Ti 4.6 mm diam. 10 um PEEK-encased 0.25in x 0.062in thick	pc		
JR-1125-2P	Frit Ti 4.6 mm diam. 2 um PEEK-encased 0.25in x 0.062in thick	pc		
JR-1125-5P	Frit Ti 4.6 mm diam. 5 um PEEK-encased 0.25in x 0.062in thick	pc		
JR-1127-05P	Frit Ti 3.2 mm diam. 0.5 um PEEK-encased 0.125 x 0.062in thick	pc		
JR-1127-2P	Frit Ti 3.2 mm diam. 2 um PEEK-encased 0.125 x 0.062in thick	pc		
JR-1128-5P	Frit Ti 2.6 mm diam. 5 um PEEK-encased 0.2in x 0.062in thick	pc		
JR-1150-10P	Frit PE 2.5 mm diam. 10 um PEEK-encased 0.2in x 0.059in thick	pc		
JR-1151-10P	Frit PE 4.9 mm diam. 10 um PEEK-encased 0.25in x 0.059in thick	pc		
JR-4071	Plug Nylon column endstopper white 10-32	pc		
JR-4072	Plug Nylon column endstopper black 10-32	pc		
JR-4073	Plug Nylon column endstopper red 10-32	pc		
JR-4074	Plug Nylon column endstopper green 10-32	pc		
JR-4075	Plug Nylon column endstopper blue 10-32	pc		
JR-4081	Plug Nylon column endstopper white 10-32	pc		
JR-4082	Plug Nylon column endstopper black 10-32	pc		
JR-4083	Plug Nylon column endstopper red 10-32	pc		
JR-4084	Plug Nylon column endstopper green 10-32	pc		
JR-4085	Plug Nylon column endstopper blue 10-32	pc		