

SRIGC PRODUCTS LIST 2014

(Ctrl F)
> Cat.#s

> Current System AUD Prices



MFR PART NO	MFR PART NO	PRODUCT NAME AND DESCRIPTION
GAS CHROMATOGRAPH	0110-0003	110 CHASSIS, 115V
	0110-0003-2	110 CHASSIS, 230V
	0310-1003	310 GC MAINFRAME, 1 CHANNEL USB 2.0 CHASSIS, 115V
	0310-1003-2	310 GC MAINFRAME, 1 CHANNEL USB 2.0 CHASSIS, 230V
	0310-6003	310 GC MAINFRAME, 6 CHANNEL USB CHASSIS, 115V
	0310-6003-2	310 GC MAINFRAME, 6 CHANNEL USB CHASSIS, 230V
	0410-1000	410 RACK GC MAINFRAME, 1 CHANNEL USB 2.0 CHASSIS, 115V
	0410-1000-2	410 RACK GC MAINFRAME, 1 CHANNEL USB 2.0 CHASSIS, 230V
	0410-6000	410 RACK GC MAINFRAME, 6 CHANNEL USB CHASSIS, 115V
	0410-6000-2	410 RACK GC MAINFRAME, 6 CHANNEL USB CHASSIS, 230V
	8610-1003	8610C GC MAINFRAME, 1 CHANNEL USB 2.0 CHASSIS, 115V
	8610-1003-2	8610C GC MAINFRAME, 1 CHANNEL USB 2.0 CHASSIS, 230V
	8610-2003	8610V GC MAINFRAME, 1 CHANNEL USB 2.0 CHASSIS, 115V (VERTICAL INJ.)
	8610-2003-2	8610V GC MAINFRAME, 1 CHANNEL USB 2.0 CHASSIS, 230V (VERTICAL INJ.)
	8610-6003	8610C GC MAINFRAME, 6 CHANNEL USB CHASSIS, 115V
	8610-6003-2	8610C GC MAINFRAME, 6 CHANNEL USB CHASSIS, 230V
	8610-1004	8610D GC MAINFRAME w/ DUAL COLUMN OVENS, 1 CH USB 2.0, 115V
	8610-1004-2	8610D GC MAINFRAME w/ DUAL COLUMN OVENS, 1 CH USB 2.0L, 230V
	8610-6004	8610D GC MAINFRAME w/ DUAL COLUMN OVENS, 6 CH USB, 115V
	8610-6004-2	8610D GC MAINFRAME w/ DUAL COLUMN OVENS, 6 CH USB, 230V
	8610-7003	8610V GC MAINFRAME, 6 CHANNEL USB 2.0 CHASSIS, 115V (VERTICAL INJ.)
	8610-7003-2	8610V GC MAINFRAME, 6 CHANNEL USB 2.0 CHASSIS, 230V (VERTICAL INJ.)

PRECONFIGURED GC SYSTEMS	0110-0100	110 CHASSIS, VOC SCREENING DYNAMIC THERMAL STRIPPER, CCD, 115V
	0110-0100-2	110 CHASSIS, VOC SCREENING DYNAMIC THERMAL STRIPPER, CCD, 230V
	0310-0004	310 EDUCATIONAL FID GC, 115V USB 2.0 CHASSIS
	0310-0045	310 SOIL GAS GC SYSTEM
	0310-1000	310 EDUCATIONAL TCD GC, 115V USB 2.0 CHASSIS
	0310-1006	310 GASLESS EDUCATIONAL CCD GC, USB 2.0 CHASSIS
	0310-1117	310 GASLESS EXPLOSIVES GC, TID
	0410-0065	410 RACK MOUNT MUDLOGGING GC SYSTEM (FID-FID), 115VAC
	0410-0065-2	410 RACK MOUNT MUDLOGGING GC SYSTEM (FID-FID), 230VAC
	8610-0025	8610C METHOD 25 GC (METHANE/NON-METHANE HYDROCARB)
	8610-0035	8610C DGA GC, HID
	8610-0036	8610C DGA GC, TCD - HID
	8610-0040	8610C GREENHOUSE GAS GC SYSTEM
	8610-0050	8610C BTEX GAS CHROMATOGRAPH, METHOD 5030 COMPLIANT
	8610-0051	8610C BTEX GAS CHROMATOGRAPH, METHOD 5030/5035 COMPLIANT
	8610-0059	8610C ENVIRONMENTAL GC (PID-FID/DELCD-P&T)
	8610-0061	8610C GEOPROBE GC (PID-FID/DELCD)
	8610-0062	8610C GEOPROBE GC (FID/DELCD)
	8610-0065	8610C MUDLOGGING GC (FID-FID)
	8610-0066	8610C FAST MUDLOGGING GC, 115VAC
	8610-0070	8610C MULTIPLE GAS GC I (TCD)
	8610-0071	8610C MULTIPLE GAS GC I (TCD-FID-METH)
	8610-0072	8610C MULTIPLE GAS GC I (TCD-HID)
	8610-0073	8610C MULTIPLE GAS GC I + SULFUR ANALYZER
	8610-0080	8610C PCB GC SYSTEM
	8610-0114	8610C METHOD TO-14 AIR MONITORING GC
	8610-0270	8610C MULTIPLE GAS GC II (TCD)
	8610-0271	8610C MULTIPLE GAS GC II (TCD-FID-METH)
	8610-0272	8610C MULTIPLE GAS GC II (TCD-HID)
	8610-0273	8610C MULTIPLE GAS GC II + SULFUR ANALYZER
	8610-0370	8610C MULTIPLE GAS GC III (TCD)
	8610-0371	8610C MULTIPLE GAS GC III (TCD-FID-METH)
	8610-0372	8610C MULTIPLE GAS GC III (TCD-HID)
	8610-0373	8610C MULTIPLE GAS GC III + SULFUR ANALYZER
	8610-1025	8610C EPA METHOD 25 GC, 115VAC
	8610-1117	8610C EXPLOSIVES GC (TID)
	8610-1500	8610C CFC GAS CHROMATOGRAPH WITH TCD
	8610-1510	8610C CFC GAS CHROMATOGRAPH WITH FID
	8610-3070	8610C BTU GAS ANALYZER GC, TCD
	8610-5400	8610C CAPILLARY FID GC
	8610-5405	8610C NARROW BORE CAPILLARY FID GC