

SRIGC PRODUCTS LIST 2014

(Ctrl F)
> Cat.#s

> Current System AUD Prices



	8610-5500	8610D TUNEABLE COLUMN SELECTIVITY GC
	8610-5675	8610C CRYOSULFUR GC SYSTEM
	8610-5700	8610C SPME GC
	8610-5800	8610C HRVOC GC SYSTEM, 115VAC
	8610-5810	8610C HRVOC GC SYSTEM, 115VAC, ADD PID, 6 CH.
	8610-6584	8610C BIODIESEL GC SYSTEM, ASTM D-6584, 115VAC
	8610-6555	8610C SULFUR IN NATURAL GAS GC SYSTEM, 115VAC
	8610-VUPG	UPGRADE PRECONFIGURED GC MODEL TO VERTICAL CHASSIS 8610V GC

DETECTORS

CCD	0110-2007	CCD MOUNTED ON MODEL 110 CHASSIS
	8670-2007	REPLACEMENT CCD DETECTOR ELEMENT
	8690-2007	CCD DETECTOR

FID-DELCD	8670-0150	FID CERAMIC IGNITOR ELEMENT
	8670-0155	FID COLLECTOR ELECTRODE CABLE WITH BNC CONNECTOR
	8670-1024	FID DETECTOR BODY
	8670-1025	FID DETECTOR BODY FOR METHANIZER
	8670-1029	DELCD HEATER / COLLECTOR ASSEMBLY
	0110-2026	FID-DELCD MOUNTED ON MODEL 110 CHASSIS
	8690-2026	FID-DELCD DETECTOR ASSEMBLY (FID-DELCD)

DELCD	0110-1026	DELCD MOUNTED ON MODEL 110 CHASSIS
	8670-1029	DELCD HEATER / COLLECTOR ASSEMBLY
	8690-1026	DELCD DETECTOR

RGD	0110-0009	RGD MOUNTED ON MODEL 110 CHASSIS
	8690-0009	RGD DETECTOR (WITH EMPTY REACTOR)
	8670-0009	REPLACEMENT RGD REACTION TUBE, UNPACKED, WITH FRITS
	8690-0011	BLANK REACTION TUBE W/FRITS

ECD	0110-0020	ECD MOUNTED ON MODEL 110 CHASSIS
	8690-0020	ECD DETECTOR

FID	0110-0010	FID MOUNTED ON MODEL 110 CHASSIS
	0110-1080	FID-FPD MOUNTED ON MODEL 110 CHASSIS
	0110-4010	FID-PID MOUNTED ON MODEL 110 CHASSIS
	0110-2026	FID-DELCD MOUNTED ON 110 CHASSIS
	8670-0150	FID IGNITOR
	8670-0154	FID COLLECTOR ELECTRODE (REPL. 8610C)
	8670-0155	FID COLLECTOR ELECTRODE CABLE (REPL. 8610C)
	8670-1023	FID DETECTOR INLET BULKHEAD FITTING
	8670-1024	FID DETECTOR BODY
	8670-1025	FID DETECTOR BODY FOR METHANIZER
	8690-0010	FID DETECTOR
	8690-0081	METHANIZER ACCESSORY MOUNTED TO EXISTING VALVE OVEN
	8690-0082	METHANIZER ACCESSORY, IN JET
	8670-1081	REPLACEMENT METHANIZER TUBE, 6" x 1/8" S.S.
	8670-1082	REPLACEMENT METHANIZER JET
	8690-1115	FID / NPD CONVERTIBLE DETECTOR
	8690-2026	FID/DELCD DETECTOR
	8690-8294	METHANIZER/OXIDIZER UNIT, FOR METHOD 25-3

NPD	8670-0120	NPD BEAD (REPLACEMENT ONLY)
	8670-1026	NPD DETECTOR BODY
	0110-0015	NPD MOUNTED ON MODEL 110 CHASSIS
	8690-0015	NPD DETECTOR
	8690-1015	NPD CONVERSION KIT FOR FID
	8690-1115	FID / NPD CONVERTIBLE DETECTOR
	8690-2615	NPD-DELCD SERIES DETECTOR

PID	8670-1240	PID CELL ASSEMBLY
	8670-1242	PID LAMP 10.6eV w/ SEAL, 106-TYPE (SMALL, NEW STYLE)
	8670-1243	PID LAMP 10.2eV w/ SEAL, 103C-TYPE (LARGE, OLD STYLE)
	8670-1244	PID LAMP SEAL, TEFLON®, PACK OF 10
	8670-1245	PID 45VDC BATTERY (REPLACEMENT)
	8670-1246	PID HV POWER SUPPLY TRANSFORMER, 8610 A, B MODEL