

# SRIGC PRODUCTS LIST 2014

(Ctrl F)  
> Cat.#s



> Current System AUD Prices

	8670-0025	HEATED INJECTOR HARDWARE, COMPLETE, WITHOUT EPC
	8670-0026	HEATED INJECTION PORT CARRIER INLET
	8670-0034	HEATED SPLIT INJECTOR BODY
	8670-0072	NARROW BORE SPME INJECTOR SLEEVE (FOR HTD. INJ.)
	8670-1034	SILCOSTEEL LINER FOR SPLIT/SPLITLESS INJECTOR
	8670-1353	SILICONE SEPTA, MOLDED PLUG, FOR ON-COLUMN INJECTOR (PACK OF 25)
	8670-1354	SILICONE SEPTA, STAMPED DISK, FOR HEATED INJECTOR (PACK OF 25)
	8670-9090	SEPTUM NUT w/ GUIDE FOR 26GA. NEEDLE
	8670-9093	0.53mm CAPILLARY COLUMN ADAPTER
	8670-9094	INJECTOR BODY
	8670-9095	SEPTUM NUT W/ GUIDE FOR 20GA. NEEDLE
	8670-9096	SEPTUM NUT W/ GUIDE FOR 20GA. NEEDLE, FOR HEATED INJECTOR
	8670-9304	HEATED TRANSFER LINE ADDITION, FOR NEW BUILD GC, RT. SIDE
	8670-9305	HEATED TRANSFER LINE MOD. w/ PLUG
	8670-9550	SYRINGE 10 uL
	8690-0023	ADDITIONAL ON-COLUMN INJECTOR, EPC CIRCUIT
	8690-0025	HEATED INJECTION PORT UPGRADE
	8690-0034	SPLIT/SPLITLESS INJECTOR UPGRADE, AUTO. VENT
	8690-0035	GAS PHASE SPLITTER
	8690-0037	ON-COLUMN PTV INJECTOR UPGRADE
	8690-0045	HEATED STATIC HEADSPACE INJECTOR
	8690-0046	HEATED STATIC HEADSPACE INJECTOR UPGRADE, TO EXISTING VALVE, VALVE OVEN
	8690-2022	ADDITIONAL EPC CONTROL ZONE (NO INJECTOR)
	8690-2023	ADDITIONAL INJECTION PORT WITHOUT EPC CONTROL/CARRIER
	8690-7034	HEATED SPLIT/SPLITLESS INJECTOR UPGRADE WITH PTV
	8690-8034	HEATED SPLIT/SPLITLESS INJECTOR UPGRADE WITH PTV, VALVE
<b>PURGE &amp; TRAP</b>	8670-1173	NEEDLE, 115 MM, FOR METHOD 5035 SPARGE HEAD
	8670-1174	NEEDLE, 50 MM, FOR METHOD 5035 SPARGE HEAD
	8670-1300	BLANK TRAP
	8670-1305	TENAX GR TRAP
	8670-1315	CARBOSIEVE II TRAP
	8670-1320	CARBOPACK B TRAP
	8670-1324	POLISHING FILTER, 3"
	8670-1330	TEFLON TEST TUBE SEALS (1 PAIR), FOR P&T
	8670-1335	SPARGE TEST TUBES (10 PACK)
	8670-1350	PURGE & TRAP SPARGING HEAD w/ GAS INJ. PORT
	8670-1351	SPARGE HEAD, 5030 INTERCHANGEABLE, REPLACEMENT
	8670-1352	SPARGE HEAD, 5035 INTERCHANGEABLE, REPLACEMENT
	8670-1450	TRAP HEATER ASSEMBLY WITH T-COUPLE
	8670-5052	UPGRADE METHOD 5030 P&T TO 5035 COMPLIANT (NEW BUILD ONLY)
	8670-5860	ONLINE SAMPLER / SPARGER FOR HRVOC GC
	8670-9556	1/16" S.S. TUBE FOR P&T SPARGE GAS
	8680-0052	METHOD 5035 COMPLIANT VOA VIAL SPARGE ACCESSORY
	8690-0051	AUTOMATED PURGE AND TRAP CONCENTRATOR, METHOD 5030
	8690-0052	AUTOMATED PURGE AND TRAP CONCENTRATOR, METHOD 5030/35
	8690-0053	10 SAMPLE PURGE AND TRAP AUTOSAMPLER, w/4 RELAY BD
	8690-0054	10 SAMPLE METHOD 5035 PURGE-AND-TRAP SAMPLER
	8690-0064	4 PORT LIQUID SAMPLING VALVE, MANUAL ACTUATOR
	8690-0075	ON-LINE LIQUID SAMPLER FOR PURGE-AND-TRAP
	8690-0084	HEATED / FAST COOLING ADSORBENT TRAP FOR EXISTING GAS VALVE
	8690-0086	PELTIER CRYOCOOLING w/ ELECTRONICS FOR TRAP
	8690-0090	PELTIER CRYOCOOLING TRAP, FOR GAS SAMPLING VALVE
	8690-0097	TRAP PACKING ACCESSORY
	8690-1051	METHOD TO-14 AIR CONCENTRATOR, VAC PUMP, 1 TRAP
	8690-1052	METHOD TO-14 AIR CONCENTRATOR, 2 TRAP, w/TUBE DESORBER
	8690-1055	METHOD TO-14 AIR CONCENTRATOR, VAC PUMP, 2 TRAPS
	8690-1084	HEATED/FAST COOLING 1/4" TRAP, FOR EXISTING GAS SAMPLING VALVE
	8690-2084	DUAL HEATED TRAPS FOR EXISTING GAS VALVES
	8690-2253	10 STATION PURGE-AND-TRAP AUTOSAMPLER 230V, 4 REL BD
	8690-5052	UPGRADE 5030 P&T TO METHOD 5030/5035 COMPLIANT (NEW BUILD ONLY)
<b>THERMAL DESORBERS</b>	8670-0062	VALCO T ROTOR HIGH TEMP.
	8670-1501	DESORBER BULKHEAD
	8670-1502	GAS DELIVERY LINE WITH CONNECTOR, THERMAL DESORBER
	8670-1590	3/8" GRAPHITE FERRULE FOR TSD (EACH)
	8690-1087	THERMAL DESORBER SAMPLE TUBE (PK. OF 10)