

SRIGC PRODUCTS LIST 2014

(Ctrl F)
> Cat.#s

> Current System AUD Prices



	8690-1088	THERMAL SOIL DESORBER, MANUAL ACTUATOR
VALVES	8670-0060	VALCO E ROTOR MID TEMP.
	8670-0061	VALCO P ROTOR LOW TEMP.
	8670-0062	VALCO T ROTOR HIGH TEMP.
	8670-0063	10 PORT VALVE HEAD, GAS SAMPLING
	8670-0064	ELECTRIC VALVE ACTUATOR, FOR 10 PORT GAS SAMPLING VALVE
	8670-0066	CIRCUIT BOARD KIT, FOR ELECTRIC ACTUATOR, 115VAC
	8670-8000	SAMPLE LOOP (SPECIFY VOLUME BETWEEN 0.5mL and 3.0mL)
	8690-0060	10 PORT GAS SAMPLING VALVE, MULTIGAS 3 PLUMBING, WITH SOLENOID
	8690-0061	10 PORT GAS SAMPLING VALVE, PNEUMATIC ACTUATOR
	8690-0062	4 PORT LIQUID SAMPLING VALVE, ELECTRIC ACTUATOR
	8690-0063	10 PORT GAS SAMPLING VALVE, MANUAL ACTUATOR
	8690-0064	4 PORT LIQUID SAMPLING VALVE, MANUAL ACTUATOR
	8690-0065	10 PORT GAS SAMPLING VALVE, ELECTRIC ACTUATOR
	8690-0066	10 INPUT HEATED STREAM SELECTOR W/ TRANSFER LINE
	8690-0067	BLOCK HEATER w/ CARTRIDGE FOR GAS VALVE
	8690-0069	SOLENOID-CONTROLLED GAS VALVE
	8690-0072	SPLIT VENT VALVE
	8690-0073	VACUUM PUMP INTERFACE, DATA SYSTEM CONTROLLED
	8690-0074	THERMOSTATTED VALVE OVEN, HIGH TEMP. (300°C MAX.)
	8690-0077	22 PORT, 10 STREAM SELECTOR VALVE, AUTOMATED, STD. ALONE
	8690-0078	22 PORT, 10 STREAM SELECTOR VALVE, ELECTRIC ACTUATOR, PLUMBED
	8690-0079	22 PORT, 10 STREAM SELECTOR VALVE, ELECTRIC ACTUATOR, UNPLUMBED
	8690-0083	CRYOTRAP LOOP, AUTOMATED CONTROL
	8690-0084	HEATED / FAST COOLING TRAP AND PLUMBING
	8690-0087	DGA-TOGA PERMEATION LOOP ACCESSORY
	8690-0088	THERMOSTATTED VALVE OVEN
	8690-0089	UNHEATED INSULATED VALVE OVEN
	8690-0091	THERMOSTATTED VALVE OVEN, NARROW, FOR 8610D GC

INJECTOR ACCESSORIES	8670-0025	HEATED INJECTOR HARDWARE, COMPLETE, WITHOUT EPC
	8690-0075	ON-LINE LIQUID SAMPLER
	8670-2368	INJECTION PORT COUPLER TO LIQUID AUTOSAMPLER CAROUSEL
	8670-8000	SAMPLE LOOP (0.5 to 3.0cc, SPECIFY)

DATA SYSTEMS	8600-9000	DATA SYSTEM HOST NOTEBOOK PC w/ PTR.
	8600-9010	DATA SYSTEM HOST DESKTOP PC w/ PTR.
	8600-9050	MULTIMEDIA DATA SYSTEM HOST DESKTOP PC W/ PTR.
USB DATA SYSTEM	8600-1050	PEAKSIMPLE 1 CH. USB DATA SYSTEM KIT, 115VAC, MODEL 333
	8600-1051	4 RELAY KIT FOR MODEL 333
	8600-1250	PEAKSIMPLE 1 CH. USB DATA SYSTEM KIT, 230VAC, MODEL 333
	8600-4060	4 RELAY BOARD FOR GC RETROFIT SERIAL INTERFACE, 8610C
	8600-4061	4 RELAY BOARD FOR GC RETROFIT, WITH EXTERNAL JACK (CURRENT 8610C)
	8600-5655	1 CH. DATA SYSTEM WITH H2 / HC SENSOR INSTALLED
	8600-6055	PEAKSIMPLE 6 CH. USB DATA SYSTEM KIT, 115V MODEL 302
	8600-6056	AC SWITCHED OUTLET FOR USB DATA SYSTEM
	8600-6255	PEAKSIMPLE 6 CH. USB DATA SYSTEM KIT, 230V MODEL 302
	8660-4653	UPGRADE 4 CH. DATA SYSTEM TO 6 CH. USB VERSION (IN EXISTING GC/LC)
	8660-6053	UPGRADE 1 CH. DATA SYSTEM TO 6 CH. USB VERSION (IN EXISTING GC/LC)
	8660-6055	UPGRADE 1 CH. USB DATA SYSTEM TO 6 CH. USB VERSION (IN NEW GC/LC)
	8670-0232	SERIAL CABLE, RS-232 (DB-9 CONNECTORS), 6'
	8670-1052	64 BIT WINDOWS 7 COMPATIBLE PIC CHIP FOR EARLY MODEL 333
	8670-1058	POWER SUPPLY FOR MODEL 333, 115VAC TO 15VDC
	8670-1058-2	POWER SUPPLY FOR MODEL 333, 230VAC TO 15VDC
	8670-USB2	USB 2.0 A TO B CABLE, 6'

PACKED COLUMNS	8600-PK1A	3' x 1/8" S.S. SILICA GEL PACKED COLUMN
	8600-PK1B	6' x 1/8" S.S. SILICA GEL PACKED COLUMN
	8600-PK2A	3' x 1/8" S.S. MOLECULAR SIEVE 5A PACKED COLUMN
	8600-PK2B	6' x 1/8" S.S. MOLECULAR SIEVE 5A PACKED COLUMN
	8600-PK3A	3' x 1/8" S.S. MOLECULAR SIEVE 13X PACKED COLUMN
	8600-PK3B	6' x 1/8" S.S. MOLECULAR SIEVE 13X PACKED COLUMN
	8600-PKC3	CTR3 DOUBLE PACKED COLUMN, FOR ARGON
	8600-PKC4	CTR1 DOUBLE PACKED COLUMN
	8600-PKC5	24' x 1/8" S.S. AT-1000/CARBOPACK B CFC PACKED COLUMN