

SRIGC PRODUCTS LIST 2014

(Ctrl F)
> Cat.#s

> Current System AUD Prices



	8600-PKDA	3' x 1/8" S.S. HAYESEP D PACKED COLUMN
	8600-PKDB	6' x 1/8" S.S. HAYESEP D PACKED COLUMN
	8600-PKQA	3' x 1/8" S.S. PORAPAK Q PACKED COLUMN
	8600-PKQA-T	3' x 1/8" TEFLON® PORAPAK Q PACKED COLUMN
	8600-PKQB	6' x 1/8" S.S. PORAPAK Q PACKED COLUMN
	8600-PKQB-T	6' x 1/8" TEFLON® PORAPAK Q PACKED COLUMN
	8600-PKSC	6' x 1/8" S.S. SHINCARBON ST 80/100 PACKED COLUMN (2M)
	8600-PKTA	3' x 1/8" S.S. HAYESEP T PACKED COLUMN
	8600-PKTB	6' x 1/8" S.S. HAYESEP T PACKED COLUMN

CAPILLARY COLUMNS	8600-WB1A	15M x 0.53MM I.D. 5.0U MXT-1 CAPILLARY COLUMN (DB-1 NON-POLAR)
	8600-WB1B	30M x 0.53MM I.D. 5.0U MXT-1 CAPILLARY COLUMN
	8600-WB1C	60M x 0.53MM I.D. 5.0U MXT-1 CAPILLARY COLUMN
	8600-WB5A	15M x 0.53MM I.D. 1.0U MXT-5 CAPILLARY COLUMN (DB-5 MED. POLARITY)
	8600-WB5B	30M x 0.53MM I.D. 1.0U MXT-5 CAPILLARY COLUMN
	8600-WB5C	60M x 0.53MM I.D. 1.0U MXT-5 CAPILLARY COLUMN
	8600-WBBD	15M x 0.53MM I.D. 0.15U MXT-500 CAPILLARY COLUMN (FOR GLYC. IN BIODIESEL)
	8600-WBBG	15M x 0.53MM I.D. 1.0U MXT-BIODIESEL CAPILLARY COLUMN
	8600-WBVA	15M x 0.53MM I.D. 5.0U MXT-VOL CAPILLARY COLUMN (FOR VOLATILES)
	8600-WBVB	30M x 0.53MM I.D. 5.0U MXT-VOL CAPILLARY COLUMN
	8600-WBVC	60M x 0.53MM I.D. 5.0U MXT-VOL CAPILLARY COLUMN
	8600-WBXA	15M x 0.53MM I.D. 1.0U MXT-WAX CAPILLARY COLUMN (POLAR)
	8600-WBXB	30M x 0.53MM I.D. 1.0U MXT-WAX CAPILLARY COLUMN
	8600-WBXC	60M x 0.53MM I.D. 1.0U MXT-WAX CAPILLARY COLUMN
	8600-WQPA	15M x 0.53MM I.D. 20.0U RT-QPLOT CAPILLARY COLUMN
	8600-WQPB	30M x 0.53MM I.D. 20.0U RT-QPLOT CAPILLARY COLUMN

ACCESSORIES	0510-0081	METHANIZER ACCESSORY, FOR NON-SRI GC / AFTERMARKET, 90-240 VAC
	8600-C346	GAS LINE INSTALLATION KIT CGA346
	8600-C350	GAS LINE INSTALLATION KIT CGA350
	8600-C380	GAS LINE INSTALLATION KIT CGA380
	8600-C580	GAS LINE INSTALLATION KIT CGA580
	8600-C590	GAS LINE INSTALLATION KIT CGA590
	8600-MAIN	GC MAINTENANCE KIT, SPECIFY 8610C OR 310, 115V OR 230V
	8660-0060	FAST MUDLOGGER MODIFICATION
	8660-0082	METHANIZER RETROFIT KIT, IN JET VERSION
	8670-1081	METHANIZER TUBE REPLACEMENT- 6" x 1/8"
	8670-1082	METHANIZER TUBE REPLACEMENT- 2" x 1/8" - FOR NEW 8610C GC
	8670-1083	METHANIZER TUBE, IN JET, UNPACKED
	8670-1122	VOLTAGE TRANSFORMER, STEP UP/STEP DOWN, 115VAC-230VAC
	8670-1340	OXYGEN TRAP FILTER
	8670-1341	HYDROCARBON TRAP FILTER
	8670-3500	AUTOSAMPLER MOUNTING SYSTEM, FOR HTA
	8670-5850	SAMPLE STREAM DRYER
	8670-9008	MAINTENANCE KIT, HYDROGEN GENERATOR (MINUS CELL)
	8670-9304	HEATED TRANSFER LINE ADDITION, FOR NEW BUILD GC, RT. SIDE
	8670-9305	HEATED TRANSFER LINE MOD. w/ PLUG
	8670-9554	SRI TUBING CUTTER FOR COPPER TUBING
	8680-0052	METHOD 5035 COMPLIANT VOA VIAL SPARGE ACCESSORY
	8680-0352	SPARE DESSICANT CANISTER
	8680-5050	HOT WAND ACCESSORY, ADJUSTABLE, 115V
	8690-0070	INTERNAL WHISPER-QUIET AIR COMPRESSOR, 115V
	8690-0071	PERISTALTIC PUMP, REPLACEMENT
	8690-0073	VACUUM PUMP INTERFACE, AUTOMATED
	8690-0081	METHANIZER ACCESSORY BUILT ONTO EXISTING VALVE OVEN
	8690-0082	METHANIZER ACCESSORY, IN JET
	8690-0086	PELTIER COOLING WITH ELECTRONICS, FOR EXISTING TRAP
	8690-0087	DGA-TOGA PERMEATION LOOP ACCESSORY
	8690-0090	PELTIER COOLED TRAP, FOR GAS SAMPLING VALVE
	8690-0092	ENRICHMENT COIL ACCESSORY
	8690-0093	ONLINE MEMBRANE SAMPLER W/ SPARGER FOR COOLING TOWER WATER
	8690-0094	OXIDIZER ACCESSORY
	8690-0095	REUSEABLE SHIPPING CONTAINER
	8690-2270	INTERNAL WHISPER-QUIET AIR COMPRESSOR, 230V
	8690-5510	DIGITAL MULTIMETER, GENERAL PURPOSE
	8690-5600	H2 / HC LEAK DETECTOR, AC POWERED, WITH DIGITAL VOLTMETER
	8690-5655	H2 / HC LEAK DETECTOR, BUILT INTO 1 CH. DATA SYSTEM