

# SRIGC PRODUCTS LIST 2014

(Ctrl F)  
> Cat.#s



> Current System

	8690-9305	HEATED TRANSFER LINE WITH THERMOCOUPLE, 115VAC
	8690-LPGH	LPG HEATED EXPANSION CHAMBER / HOMOGENIZER

<b>PARTS</b>	8660-6055	UPGRADE 1 CHANNEL DATA SYSTEM TO 6 CHANNEL VERSION (IN NEW GC)
	8670-CB02	CIRCUIT BREAKER, 2 A (115VAC)
	8670-CB05	CIRCUIT BREAKER, 5 A (230VAC)
	8670-CB10	CIRCUIT BREAKER, 10A (115VAC)
	8670-GRE1	GRAPHITE ELECTRODE ROPE, WITH CONNECTORS, FOR HYDROGEN GENERATOR
	8670-KBF1	KYNAR BAR FITTING, WATER, FOR HYDROGEN GENERATOR (REPLACES NYLON)
	8670-0007	TCD CELL w/ FILAMENTS, HEATING ELEMENT, SRI MODEL
	8670-0011	TCD GAIN SWITCH
	8670-0017	TID DETECTOR BEAD
	8670-0025	HEATED INJECTOR HARDWARE, COMPLETE, WITHOUT EPC
	8670-0026	HEATED INJECTION PORT CARRIER INLET
	8670-0030	HID COLLECTOR ELECTRODE ASSEMBLY
	8670-0031	HID DETECTOR BODY
	8670-0034	HEATED SPLIT INJECTOR BODY
	8670-0060	VALCO E ROTOR MID TEMP.
	8670-0061	VALCO P ROTOR LOW TEMP.
	8670-0062	VALCO T ROTOR HIGH TEMP.
	8670-0063	10 PORT VALVE HEAD, GAS SAMPLING
	8670-0064	ELECTRIC VALVE ACTUATOR, FOR 10 PORT GAS SAMPLING VALVE
	8670-0066	CIRCUIT BOARD KIT, FOR ELECTRIC ACTUATOR, 115VAC
	8670-0068	SYRINGE NEEDLE, REPLACEMENT, FOR LIQUID AUTOSAMPLER
	8670-0070	AIR COMPRESSOR, REPLACEMENT, 115VAC
	8670-0071	PERISTALTIC PUMP TUBING, REPLACEMENT
	8670-0072	NARROW BORE SPME INJECTOR SLEEVE (FOR HTD. INJ.)
	8670-0073	VACUUM PUMP INTERFACE, SELF INSTALL KIT
	8670-0074	VACUUM PUMP, REPLACEMENT
	8670-0080	PHOTOMULTIPLIER (PMT) TUBE
	8670-0081	FPD DETECTOR BODY
	8670-0082	SULPHUR WAVELENGTH FILTER
	8670-0083	PHOSPHORUS WAVELENGTH FILTER
	8670-0084	FPD FILTER ASSEMBLY WITH BUILT-IN SULFUR FILTER
	8670-0085	FPD FILTER ASSEMBLY WITH BUILT-IN PHOSPHORUS FILTER
	8670-0086	FPD PMT SOCKET ASSEMBLY
	8670-0120	NPD BEAD (REPLACEMENT ONLY)
	8670-0150	FID IGNITOR / ELCD HEATER
	8670-0154	FID COLLECTOR ELECTRODE (REPL. 8610C)
	8670-0155	FID COLLECTOR ELECTRODE CABLE (REPL. 8610C)
	8670-0232	SERIAL CABLE, RS-232 (DB-9 CONNECTORS), 6'
	8670-0353	CELL, HYDROGEN GENERATOR, REPLACEMENT (NEW)
	8670-0354	CELL, HYDROGEN GENERATOR, REPLACEMENT (REBUILT)
	8670-0355	H2-40 SAFETY UPGRADE KIT
	8670-0356	H2-50 SAFETY UPGRADE KIT
	8670-0357	GLASS CYLINDER REPLACEMENT KIT, FOR H2 GENERATOR
	8670-0651	FAN MOTOR KIT, 8610C (SPECIFY 115VAC OR 230VAC)
	8670-0655	FAN MOTOR AND BLADE, 310/410 (SPECIFY 115VAC OR 230VAC)
	8670-1024	FID DETECTOR BODY
	8670-1025	FID DETECTOR BODY FOR METHANIZER
	8670-1026	NPD DETECTOR BODY
	8670-1028	DELCD COOLING FAN, FOR RED LID
	8670-1029	DELCD HEATER / COLLECTOR ASSEMBLY
	8670-1034	SILCOSTEEL LINER FOR SPLIT/SPLITLESS INJECTOR
	8670-1052	64 BIT WINDOWS 7 COMPATIBLE PIC CHIP FOR EARLY MODEL 333
	8670-1081	METHANIZER TUBE REPLACEMENT- 6" x 1/8"
	8670-1082	METHANIZER IN-JET TUBE REPLACEMENT- 2" x 1/8"
	8670-1083	METHANIZER TUBE, IN JET, UNPACKED
	8670-1084	HEATED/FAST COOLING 1/4" TRAP, FOR EXISTING GAS SAMPLING VALVE
	8670-114A	DIFFERENTIAL AMPLIFIER IC, INA114AP
	8670-117P	DIFFERENTIAL AMPLIFIER IC, INA117P
	8670-1351	SPARGE HEAD, 5030 INTERCHANGEABLE, REPLACEMENT
	8670-1352	SPARGE HEAD, 5035 INTERCHANGEABLE, REPLACEMENT
	8670-1353	SILICONE SEPTA, MOLDED PLUG, FOR ON-COLUMN INJECTOR (PACK OF 25)
	8670-1354	SILICONE SEPTA, STAMPED DISK, FOR HEATED INJECTOR (PACK OF 25)
	8670-1357	PORTER PRESSURE REGULATOR w/ SENSOR
	8670-1400	OVEN HEATER / SOCKET SET, 110 OR 230V