

SRIGC PRODUCTS LIST 2014

(Ctrl F)
> Cat.#s



> Current System AUD Prices

8670-1401	OVEN HEATER ELEMENT, 8610A/B/9300A, REPLACEMENT
8670-1402	OVEN HEATER SOCKET FOR 8610A, B, 9300A GC's
8670-1403	OVEN HEATER ELEMENT FOR 8610C GC, 115V
8670-1404	OVEN HEATER ELEMENT FOR 8610C GC, 230V
8670-1405	OVEN HEATER ELEMENT FOR 310 GC, 230V
8670-1406	OVEN HEATER ELEMENT FOR 310 GC, 115V
8670-1410	CARTRIDGE HEATER, 100W, 1/4"x1 5/16", FOR DET. BLOCK, METH. (115V OR 230V)
8670-1411	CARTRIDGE HEATER, 100W, 3/8"x2 3/4", FOR ECD HEATER BLOCK (115V OR 230V)
8670-1412	CARTRIDGE HEATER, 40W, 1/4"x1 1/4", FOR 5030 P&T SAMPLER (115V OR 230V)
8670-1413	CARTRIDGE HEATER, 40W, 1/4"x1 1/4", FOR HID HEATER BLOCK (24VDC)
8670-1414	CARTRIDGE HEATER, 50W, 1/4"x1 1/4", FOR 510 METHANIZER HEATER (12VDC)
8670-1415	CARTRIDGE HEATER, 150W, 3/8"x2", FOR THERMAL DESORBER (115V OR 230V)
8670-1416	CARTRIDGE HEATER, 200W, 1/4"x1 1/2", FOR PELTIER, BIOD. DET. BLK. (115V OR 230V)
8670-1418	1/4" TO 1/8" VESPEL REDUCING FERRULE, PACK OF 10
8670-1419	1/4" TO 1/8" TEFLON® REDUCING FERRULE, PACK OF 10
8670-1450	TRAP HEATER ASSEMBLY WITH T-COUPLE
8670-1460	TYPE K THERMOCOUPLE, 36"
8670-1506	1/16" S.S. FERRULE SET, PACK OF 10
8670-1590	3/8" GRAPHITE FERRULE FOR TSD
8670-1800	1/8" BRASS NUT, PACK OF 10
8670-1806	1/8" S.S. FERRULE SET, PACK OF 10
8670-1814	1/4" TO 1/8" REDUCING FITTING, FOR CTR COLUMN, ETC.
8670-1815	1/4" TO 1/8" REDUCING FITTING, WITH 1/16" GAS LINE ENTRY
8670-1818	1/8" GRAPHITE STRAIGHT FERRULE, PACK OF 10
8670-1853	GRAPHITE REDUCING FERRULE, 1/8" - 0.8mm, PACK OF 10
8670-1855	1/4" GRAPHITE STRAIGHT FERRULE, PACK OF 10
8670-1828	GRAPHITE REDUCING FERRULE, 1/8" - 0.5MM, PACK OF 10
8670-2085	DFPD-FID DETECTOR BODY
8670-2270	AIR COMPRESSOR, REPLACEMENT, 230VAC
8670-2368	INJECTION PORT COUPLER TO LIQUID AUTOSAMPLER CAROUSEL
8670-5600	PROBE, REPLACEMENT, FOR HC/H2 LEAK DETECTOR
8670-6000	DIGITAL FLOW CONTROLLER
8670-6020	PRESSURE SENSOR WITH CONNECTOR FOR EPC
8670-6021	TANK PRES. REGULATOR w/ CGA FITTING
8670-6022	NORGREN GAS PRESSURE REGULATOR
8670-6023	NORGREN PRESSURE REGULATOR w/ SENSOR
8670-6024	WATTS GAS PRESSURE REGULATOR
8670-6025	WATTS PRESSURE REGULATOR w/ SENSOR
8670-6026	GAUGE FOR REGULATOR
8670-6500	OVEN CIRCULATING FAN w/ SQUIREL CAGE
8670-6550	GREY OVEN COOLING FAN, WITH COOLING FAN MUFFIN
8670-6554	HEATSINK FAN
8670-6575	CHASSIS FAN, 24VDC, FOR 8610C/310
8670-6576	CHASSIS FAN, 115VAC, FOR 8610C/310
8670-6600	COLUMN OVEN LID, 8610B
8670-9001	GC MAINTENANCE KIT, 8610C 115V
8670-9002	GC MAINTENANCE KIT, 8610C 230V
8670-9003	GC MAINTENANCE KIT, 8610B 115V
8670-9004	GC MAINTENANCE KIT, 8610B 230V
8670-9005	GC MAINTENANCE KIT, 310 115V
8670-9006	GC MAINTENANCE KIT, 310 230V
8670-9093	0.53mm CAPILLARY COLUMN ADAPTER
8670-9304	HEATED TRANSFER LINE ADDITION, FOR NEW BUILD GC, RT. SIDE
8670-9305	HEATED TRANSFER LINE MOD. w/ PLUG
8670-9555	TUBING COPPER 1/8", 50' ROLL
8670-USB2	USB 2.0 A TO B CABLE, 6'
8690-0064	4 PORT LIQUID SAMPLING VALVE, MANUAL ACTUATOR
8690-0071	PERISTALTIC PUMP, REPLACEMENT
8690-0072	SPLIT VENT VALVE
8690-0073	VACUUM PUMP INTERFACE, DATA SYSTEM CONTROLLED
8690-0081	METHANIZER ACCESSORY BUILT ONTO EXISTING VALVE OVEN
8690-0082	METHANIZER ACCESSORY, IN JET
8690-0086	PELTIER COOLING w/ ELECTRONICS FOR TRAP
8690-0090	PELTIER COOLED TRAP, FOR GAS SAMPLING VALVE
8690-0095	REUSEABLE SHIPPING CONTAINER
8690-0096	DGA-TOGA EXTRACTOR ASSEMBLY
8690-0151	NAFION MEMBRANE REPLACEMENT FOR HYDROGEN GEN.

where "SUPPLIER" = restek, vicivalco, vicijour, srigcs, valueplastics (MAIN Suppliers ONLY > Latest Prices

SEARCH [cat#] Write Down Cat#

Go To www.chromtech.net.au/flip/catalogs/ THEN add "/index.php" to URL

134 [Ctrl "F"] to SEARCH for Item > Description/Cat# etc

06/2014