

SRIGC PRODUCTS LIST 2014

(Ctrl F)
> Cat.#s



> Current System AUD Prices

	8690-0152	NAFION TUBING, DRYER, FOR HYDROGEN GENERATOR
	8690-0153	WATER FILTER, FOR HYDROGEN GENERATOR
	8690-1070	REPLACEMENT AIR FILTER
	8690-7000	OP-AMP CHIP, LF356 (REPLACES OP-80A)
	8690-7100	SCR - TRIAC CIRCUIT BOARD

PRODUCT LIST	0110-0003	110 CHASSIS, 115V
	0110-0003-2	110 CHASSIS, 230V
	0110-0006	ASD MOUNTED ON MODEL 110 CHASSIS
	0110-0007	TCD MOUNTED ON MODEL 110 CHASSIS
	0110-0009	RGD MOUNTED ON MODEL 110 CHASSIS
	0110-0010	FID MOUNTED ON MODEL 110 CHASSIS
	0110-0015	NPD MOUNTED ON MODEL 110 CHASSIS
	0110-0017	TID MOUNTED ON MODEL 110 CHASSIS
	0110-0020	ECD MOUNTED ON MODEL 110 CHASSIS
	0110-0030	HID MOUNTED ON MODEL 110 CHASSIS
	0110-0040	PID MOUNTED ON MODEL 110 CHASSIS
	0110-0080	FPD MOUNTED ON MODEL 110 CHASSIS
	0110-0085	SIMULTANEOUS S/P FPD MOUNTED ON MODEL 110 CHASSIS
	0110-0100	110 CHASSIS, DYNAMIC THERMAL STRIPPER
	0110-1026	DELCD MOUNTED ON MODEL 110 CHASSIS
	0110-1080	FPD-FID MOUNTED ON MODEL 110 CHASSIS
	0110-2007	CCD MOUNTED ON MODEL 110 CHASSIS
	0110-2026	FID-DELCD MOUNTED ON MODEL 110 CHASSIS
	0110-2426	PID-FID-DELCD MOUNTED ON MODEL 110 CHASSIS
	0110-4010	PID-FID MOUNTED ON MODEL 110 CHASSIS
	0310-0004	310 EDUCATIONAL FID GC, USB 2.0 CHASSIS, 115V
	0310-0045	310 SOIL GAS GC SYSTEM
	0310-1000	310 EDUCATIONAL TCD GC, USB 2.0 CHASSIS, 115V
	0310-1003	310 GC MAINFRAME, 1 CHANNEL USB 2.0 CHASSIS, 115V
	0310-1003-2	310 GC MAINFRAME, 1 CHANNEL USB 2.0 CHASSIS, 230V
	0310-1006	310 GASLESS EDUCATIONAL CCD GC, SERIAL CHASSIS, 115V
	0310-1007	310 GASLESS INDOOR AIR QUALITY GC (CCD)
	0310-1008	310 GASLESS INDOOR AIR QUALITY GC (CCD-PID)
	0310-1117	310 GASLESS EXPLOSIVES GC, TID
	0310-6003	310 GC MAINFRAME, 6 CHANNEL USB CHASSIS, 115V
	0310-6003-2	310 GC MAINFRAME, 6 CHANNEL USB CHASSIS, 230V
	0410-0065	410 RACK MOUNT MUDLOGGING GC SYSTEM (FID-FID)
	0410-0065-2	410 RACK MOUNT MUDLOGGING GC SYSTEM (FID-FID)
	0410-1000	410 RACK GC MAINFRAME, 1 CHANNEL USB 2.0 CHASSIS, 115V
	0410-1000-2	410 RACK GC MAINFRAME, 1 CHANNEL USB 2.0 CHASSIS, 230V
	0410-6000	410 RACK GC MAINFRAME, 6 CHANNEL USB CHASSIS, 115V
	0410-6000-2	410 RACK GC MAINFRAME, 6 CHANNEL USB CHASSIS, 230V
	0510-0081	METHANIZER ACCESSORY FOR NON-SRI GC / AFTERMARKET, 90-240 VAC
	0510-1081	REPLACEMENT METHANIZER TUBE FOR MODEL 510
	8600-1050	PEAKSIMPLE 1 CH. USB DATA SYSTEM KIT, 115VAC, MODEL 333
	8600-1051	4 RELAY KIT FOR MODEL 333
	8600-1250	PEAKSIMPLE 1 CH. USB DATA SYSTEM KIT, 230VAC, MODEL 333
	8600-2022	SINGLE-GAS EPC OPTION FOR MODEL 333 UNITS
	8600-4060	4 RELAY BOARD FOR GC RETROFIT, 8610C/310
	8600-4061	4 RELAY BOARD FOR GC RETROFIT, WITH EXTERNAL JACK (CURRENT 8610C)
	8600-5655	1 CH. DATA SYSTEM WITH H2 / HC SENSOR INSTALLED
	8660-6053	UPGRADE 1 CH. DATA SYSTEM TO 6 CH. USB VERSION (IN EXISTING GC/LC)
	8600-6055	PEAKSIMPLE 6 CH. USB DATA SYSTEM KIT, 115V MODEL 302
	8600-6056	SWITCHED AC OUTLET FOR USB DATA SYSTEM
	8600-6255	PEAKSIMPLE 6 CH. USB DATA SYSTEM KIT, 230V MODEL 302
	8600-9000	DATA SYSTEM HOST NOTEBOOK PC w/ PTR.
	8600-9010	DATA SYSTEM HOST DESKTOP PC w/ PTR.
	8600-9050	MULTIMEDIA DATA SYSTEM HOST DESKTOP PC W/ PTR.
	8600-C346	GAS LINE INSTALLATION KIT CGA346
	8600-C350	GAS LINE INSTALLATION KIT CGA350
	8600-C380	GAS LINE INSTALLATION KIT CGA380
	8600-C580	GAS LINE INSTALLATION KIT CGA580
	8600-C590	GAS LINE INSTALLATION KIT CGA590
	8600-PK1A	3' x 1/8" S.S. SILICA GEL PACKED COLUMN
	8600-PK1B	6' x 1/8" S.S. SILICA GEL PACKED COLUMN
	8600-PK2A	3' x 1/8" S.S. MOLECULAR SIEVE 5A PACKED COLUMN