

SRIGC PRODUCTS LIST 2014

[Ctrl F]
> Cat.#s

> Current System AUD Prices



8600-PK2B	6' x 1/8" S.S. MOLECULAR SIEVE 5A PACKED COLUMN
8600-PK3A	3' x 1/8" S.S. MOLECULAR SIEVE 13X PACKED COLUMN
8600-PK3B	6' x 1/8" S.S. MOLECULAR SIEVE 13X PACKED COLUMN
8600-PKC3	CTR3 DOUBLE PACKED COLUMN, FOR ARGON
8600-PKC4	CTR1 DOUBLE PACKED COLUMN
8600-PKC5	24' x 1/8" S.S. AT-1000/CARBOPACK B CFC PACKED COLUMN
8600-PKDA	3' x 1/8" S.S. HAYESEP D PACKED COLUMN
8600-PKDB	6' x 1/8" S.S. HAYESEP D PACKED COLUMN
8600-PKQA	3' x 1/8" S.S. PORAPAK Q PACKED COLUMN
8600-PKQA-T	3' x 1/8" TEFLON® PORAPAK Q PACKED COLUMN
8600-PKQB	6' x 1/8" S.S. PORAPAK Q PACKED COLUMN
8600-PKQB-T	6' x 1/8" TEFLON® PORAPAK Q PACKED COLUMN
8600-PKSC	6' x 1/8" S.S. SHINCARBON ST 80/100 PACKED COLUMN (2M)
8600-PKTA	3' x 1/8" S.S. HAYESEP T PACKED COLUMN
8600-PKTB	6' x 1/8" S.S. HAYESEP T PACKED COLUMN
8600-WB1A	15M x 0.53MM I.D. 5.0U MXT-1 CAPILLARY COLUMN (DB-1 NON-POLAR)
8600-WB1B	30M x 0.53MM I.D. 5.0U MXT-1 CAPILLARY COLUMN
8600-WB1C	60M x 0.53MM I.D. 5.0U MXT-1 CAPILLARY COLUMN
8600-WB5A	15M x 0.53MM I.D. 1.0U MXT-5 CAPILLARY COLUMN (DB-5 MED. POLARITY)
8600-WB5B	30M x 0.53MM I.D. 1.0U MXT-5 CAPILLARY COLUMN
8600-WB5C	60M x 0.53MM I.D. 1.0U MXT-5 CAPILLARY COLUMN
8600-WBBD	15M x 0.53MM I.D. 0.15U MXT-500 CAPILLARY COLUMN (FOR GLYC. IN BIODIESEL)
8600-WBBG	15M x 0.53MM I.D. MXT-BIODIESEL CAPILLARY COLUMN
8600-WBVA	15M x 0.53MM I.D. 5.0U MXT-VOL CAPILLARY COLUMN (FOR VOLATILES)
8600-WBVB	30M x 0.53MM I.D. 5.0U MXT-VOL CAPILLARY COLUMN
8600-WBVC	60M x 0.53MM I.D. 5.0U MXT-VOL CAPILLARY COLUMN
8600-WBXA	15M x 0.53MM I.D. 1.0U MXT-WAX CAPILLARY COLUMN (POLAR)
8600-WBXC	30M x 0.53MM I.D. 1.0U MXT-WAX CAPILLARY COLUMN
8600-WBXC	60M x 0.53MM I.D. 1.0U MXT-WAX CAPILLARY COLUMN
8600-WQPA	15M x 0.53MM I.D. 20.0U RT-QPLOT CAPILLARY COLUMN (19741)
8600-WQPB	30M x 0.53MM I.D. 20.0U RT-QPLOT CAPILLARY COLUMN (19742)
8610-0025	8610C METHOD 25 GC (CH4/NON-CH4 HC)
8610-0035	8610C DGA GC SYSTEM, HID
8610-0036	8610C DGA GC SYSTEM, TCD - HID
8610-0040	8610C GREENHOUSE GAS GC SYSTEM
8610-0050	8610C BTEX GAS CHROMATOGRAPH, METHOD 5030 COMPLIANT
8610-0051	8610C BTEX GAS CHROMATOGRAPH, METHOD 5030/5035 COMPLIANT
8610-0059	8610C ENVIRONMENTAL GC (PID-FID/DELCD-P&T)
8610-0061	8610C GEOPROBE GC (PID-FID/DELCD)
8610-0062	8610C GEOPROBE GC (FID/DELCD)
8610-0065	8610C MUDLOGGING GC (FID-FID)
8610-0066	8610C FAST MUDLOGGING GC, 115VAC
8610-0070	8610C MULTIPLE GAS ANALYZER GC - TCD
8610-0071	8610C MULTIPLE GAS ANALYZER TCD FID METH
8610-0072	8610C MULTIPLE GAS ANALYZER TCD HID
8610-0073	8610C MULTIPLE GAS + SULFUR ANALYZER
8610-0080	8610C PCB GC SYSTEM
8610-0114	8610C METHOD TO-14 AIR MONITORING GC
8610-0270	8610C MULTIPLE GAS GC II (TCD)
8610-0271	8610C MULTIPLE GAS GC II (TCD-FID-METH)
8610-0272	8610C MULTIPLE GAS GC II (TCD-HID)
8610-0273	8610C MULTIPLE GAS GC II + SULFUR ANALYZER
8610-0370	8610C MULTIPLE GAS GC III (TCD)
8610-0371	8610C MULTIPLE GAS GC III (TCD-FID-METH)
8610-0372	8610C MULTIPLE GAS GC III (TCD-HID)
8610-0373	8610C MULTIPLE GAS GC III + SULFUR ANALYZER
8610-1003	8610C GC MAINFRAME, 1 CHANNEL USB 2.0 CHASSIS, 115V
8610-1003-2	8610C GC MAINFRAME, 1 CHANNEL USB 2.0 CHASSIS, 230V
8610-1025	EPA METHOD 25 GC, 115V
8610-1117	8610C EXPLOSIVES GC (TID)
8610-1500	8610C CFC GAS CHROMATOGRAPH WITH TCD
8610-1510	8610C CFC GAS CHROMATOGRAPH WITH FID
8610-2003	8610V GC MAINFRAME, 1 CHANNEL USB 2.0 CHASSIS, 115V (VERTICAL INJ.)
8610-2003-2	8610V GC MAINFRAME, 1 CHANNEL USB 2.0 CHASSIS, 230V (VERTICAL INJ.)
8610-3070	8610C BTU GAS ANALYZER GC, TCD
8610-5400	8610C CAPILLARY FID GC
8610-5405	8610C NARROW BORE CAPILLARY FID GC