

SRIGC PRODUCTS LIST 2014

(Ctrl F)
> Cat.#s



> Current System AUD Prices

8610-5500	8610D TUNEABLE COLUMN SELECTIVITY GC
8610-5675	8610C CRYOSULFUR GC SYSTEM
8610-5700	8610C SPME GC
8610-5800	8610C HRVOC GC SYSTEM, 115VAC
8610-5810	8610C HRVOC GC SYSTEM, 115VAC, ADD PID, 6 CH.
8610-6003	8610C GC MAINFRAME, 6 CHANNEL USB CHASSIS, 115V
8610-6003-2	8610C GC MAINFRAME, 6 CHANNEL USB CHASSIS, 230V
8610-6004	8610D GC MAINFRAME w/ DUAL COLUMN OVENS, 6 CH USB, 115V
8610-6004-2	8610D GC MAINFRAME w/ DUAL COLUMN OVENS, 6 CH USB, 230V
8610-6584	8610C BIODIESEL GC SYSTEM, ASTM D-6584, 115VAC
8610-6555	SULFUR IN NATURAL GAS GC SYSTEM, 115VAC
8610-7003	8610V GC MAINFRAME, 6 CHANNEL USB 2.0 CHASSIS, 115V (VERTICAL INJ.)
8610-7003-2	8610V GC MAINFRAME, 6 CHANNEL USB 2.0 CHASSIS, 230V (VERTICAL INJ.)
8610-VUPG	UPGRADE PRECONFIGURED GC MODEL TO VERTICAL CHASSIS 8610V GC
8640-0001	LIQUID AUTOSAMPLER, 100 VIAL TRAY, COBRA (VERTICAL, FOR 8610V ONLY)
8640-0002	MOUNTING BRACKET KIT, FOR VERTICAL AUTOSAMPLER (8610V ONLY)
8640-0003	SYRINGE, FOR COBRA AUTOSAMPLER, 5 CM. NEEDLE
8640-0050	AUTOCALIBRATION SYSTEM, GAS
8640-1006	SINGLE BAY AUTOINJECTOR
8660-0060	FAST MUDLOGGER MODIFICATION
8660-0082	METHANIZER RETROFIT KIT, IN JET VERSION
8660-6053	UPGRADE 1 CH. DATA SYSTEM TO 6 CH. USB VERSION (IN EXISTING GC/LC)
8660-6055	UPGRADE 1 CH. USB DATA SYSTEM TO 6 CH. USB VERSION (IN NEW GC/LC)
8670-CB02	CIRCUIT BREAKER, 2 A (115VAC)
8670-CB05	CIRCUIT BREAKER, 5 A (230VAC)
8670-CB10	CIRCUIT BREAKER, 10 A (115VAC)
8670-GRE1	GRAPHITE ELECTRODE ROPE, WITH CONNECTORS, FOR HYDROGEN GENERATOR
8670-KBF1	KYNAR BAR FITTING, WATER, FOR HYDROGEN GENERATOR (REPLACES NYLON)
8670-USB2	USB 2.0 A TO B CABLE, 6'
8670-0007	TCD CELL w/ FILAMENTS, HEATING ELEMENT, SRI MODEL
8670-0009	REPLACEMENT RGD REACTION TUBE, UNPACKED, WITH FRITS
8670-0011	TCD GAIN SWITCH
8670-0017	TID DETECTOR BEAD
8670-0024	HEATED INJECTOR BODY
8670-0025	HEATED INJECTOR HARDWARE, COMPLETE, WITHOUT EPC
8670-0026	HEATED INJECTION PORT CARRIER INLET
8670-0030	HID COLLECTOR ELECTRODE ASSEMBLY
8670-0031	HID DETECTOR BODY
8670-0034	HEATED SPLIT INJECTOR BODY
8670-0060	VALCO E ROTOR MID TEMP.
8670-0061	VALCO P ROTOR LOW TEMP.
8670-0062	VALCO T ROTOR HIGH TEMP.
8670-0063	10 PORT VALVE HEAD, GAS SAMPLING
8670-0064	ELECTRIC VALVE ACTUATOR, FOR 10 PORT GAS SAMPLING VALVE
8670-0066	CIRCUIT BOARD KIT, FOR ELECTRIC ACTUATOR, 115VAC
8670-0068	SYRINGE NEEDLE, REPLACEMENT, FOR LIQUID AUTOSAMPLER
8670-0070	AIR COMPRESSOR, REPLACEMENT, 115VAC
8670-0071	PERISTALTIC PUMP TUBING, REPLACEMENT
8670-0072	NARROW BORE SPME INJECTOR SLEEVE (FOR HTD. INJ.)
8670-0073	VACUUM PUMP INTERFACE, SELF INSTALL KIT
8670-0074	VACUUM PUMP, REPLACEMENT
8670-0080	PHOTOMULTIPLIER (PMT) TUBE
8670-0081	FPD DETECTOR BODY
8670-0082	SULPHUR WAVELENGTH FILTER
8670-0083	PHOSPHORUS WAVELENGTH FILTER
8670-0084	FPD FILTER ASSEMBLY WITH BUILT-IN SULFUR FILTER
8670-0085	FPD FILTER ASSEMBLY WITH BUILT-IN PHOSPHORUS FILTER
8670-0120	NPD BEAD (REPLACEMENT ONLY)
8670-0150	FID IGNITOR
8670-0154	FID COLLECTOR ELECTRODE (REPL. 8610C)
8670-0155	FID COLLECTOR ELECTRODE CABLE (REPL. 8610C)
8670-0232	SERIAL CABLE, RS-232 (DB-9 CONNECTORS), 6'
8670-0351	NAFION MEMBRANE REPLACEMENT FOR 50ML HYDROGEN GEN.
8670-0353	CELL, HYDROGEN GENERATOR, REPLACEMENT (NEW)
8670-0354	CELL, HYDROGEN GENERATOR, REPLACEMENT (REBUILT)
8670-0357	GLASS CYLINDER REPLACEMENT KIT, FOR H2 GENERATOR
8670-0651	FAN MOTOR KIT, 8610C (SPECIFY 115VAC OR 230VAC)

where "SUPPLIER" = restek, vicijour, vicivalco, vicijour, srigrs, valueplastics (MAIN Suppliers ONLY > Latest Prices

SEARCH [cat#] Write Down Cat#