

# SRIGC PRODUCTS LIST 2014

(Ctrl F)  
> Cat.#s



> Current System AUD Prices

8670-0655	FAN MOTOR KIT, 310/410 (SPECIFY 115VAC OR 230VAC)
8670-6575	CHASSIS FAN, 24VDC, FOR 8610C/310
8670-1017	TID DETECTOR BODY
8670-1023	FID DETECTOR INLET BULKHEAD FITTING
8670-1024	FID DETECTOR BODY
8670-1025	FID DETECTOR BODY FOR METHANIZER
8670-1026	NPD DETECTOR BODY
8670-1028	DELCD COOLING FAN, FOR RED LID
8670-1029	DELCD HEATER / COLLECTOR ASSEMBLY
8670-1034	SILCOSTEEL LINER FOR SPLIT/SPLITLESS INJECTOR
8670-1052	64 BIT WINDOWS 7 COMPATIBLE PIC CHIP FOR EARLY MODEL 333
8670-1058	POWER SUPPLY FOR MODEL 333, 115VAC TO 15VDC
8670-1058-2	POWER SUPPLY FOR MODEL 333, 230VAC TO 15VDC
8670-1081	METHANIZER TUBE REPLACEMENT- 6" x 1/8"
8670-1082	METHANIZER IN-JET TUBE REPLACEMENT - 2" x 1/8"
8670-1083	METHANIZER TUBE, IN JET, UNPACKED
8670-1084	HEATED/FAST COOLING 1/4" TRAP, FOR EXISTING GAS SAMPLING VALVE
8670-1122	VOLTAGE TRANSFORMER, STEP UP/STEP DOWN, 115VAC-230VAC
8670-1173	NEEDLE, 115 MM, FOR METHOD 5035 SPARGE HEAD
8670-1174	NEEDLE, 50 MM, FOR METHOD 5035 SPARGE HEAD
8670-114A	DIFFERENTIAL AMPLIFIER IC, INA114AP
8670-117P	DIFFERENTIAL AMPLIFIER IC, INA117P
8670-1240	PID CELL ASSEMBLY
8670-1242	PID LAMP 10.6eV w/ SEAL, 106-TYPE (SMALL, NEW STYLE)
8670-1243	PID LAMP 10.2eV w/ SEAL, 103C-TYPE (LARGE, OLD STYLE)
8670-1244	PID LAMP SEAL, TEFLON®, PACK OF 10
8670-1245	PID 45VDC BATTERY (REPLACEMENT)
8670-1246	PID HV POWER SUPPLY TRANSFORMER, 8610 A, B MODEL
8670-1247	PID HV POWER SUPPLY CIRCUIT BOARD, 8610C, 310 MODEL
8670-1248	PID DETECTOR INLET BULKHEAD FITTING
8670-1300	BLANK TRAP
8670-1305	TENAX GR TRAP
8670-1315	CARBOSIEVE II TRAP
8670-1320	CARBOPACK B TRAP
8670-1324	POLISHING FILTER, 3"
8670-1330	TEFLON TEST TUBE SEALS (1 PAIR), FOR P&T
8670-1335	SPARGE TEST TUBES (10 PACK)
8670-1340	OXYGEN TRAP FILTER
8670-1341	HYDROCARBON TRAP FILTER
8670-1350	PURGE & TRAP SPARGING HEAD w/ GAS INJ. PORT
8670-1351	SPARGE HEAD, 5030 INTERCHANGEABLE, REPLACEMENT
8670-1352	SPARGE HEAD, 5035 INTERCHANGEABLE, REPLACEMENT
8670-1353	SILICONE SEPTA, MOLDED PLUG, FOR ON-COLUMN INJECTOR (PACK OF 25)
8670-1354	SILICONE SEPTA, STAMPED DISK, FOR HEATED INJECTOR (PACK OF 25)
8670-1356	PORTER GAS PRESSURE REGULATOR & FITTING
8670-1357	PORTER PRESSURE REGULATOR w/ SENSOR
8670-1400	OVEN HEATER / SOCKET SET, 110 or 230V
8670-1401	OVEN HEATER ELEMENT, 8610A/B/9300A, REPLACEMENT
8670-1402	OVEN HEATER SOCKET FOR 8610A, B, 9300A GC's
8670-1403	OVEN HEATER ELEMENT FOR 8610C GC, 115V
8670-1404	OVEN HEATER ELEMENT FOR 8610C GC, 230V
8670-1405	OVEN HEATER ELEMENT FOR 310 GC, 230V
8670-1406	OVEN HEATER ELEMENT FOR 310 GC, 115V
8670-1410	HEATER CARTRIDGE, 100W, 115V, 1/4"x1 5/16", FOR DET. BLOCK, METH. (115V OR 230V)
8670-1411	CARTRIDGE HEATER, 100W, 3/8"x2 3/4", FOR ECD HEATER BLOCK (115V OR 230V)
8670-1412	CARTRIDGE HEATER, 40W, 1/4"x1 1/4", FOR 5030 P&T SAMPLER (115V OR 230V)
8670-1413	CARTRIDGE HEATER, 40W, 1/4"x1 1/4", FOR HID HEATER BLOCK (24VDC)
8670-1414	CARTRIDGE HEATER, 50W, 1/4"x1 1/4", FOR 510 METHANIZER HEATER (12VDC)
8670-1415	CARTRIDGE HEATER, 150W, 3/8"x2", FOR THERMAL DESORBER (115V OR 230V)
8670-1416	CARTRIDGE HEATER, 200W, 1/4"x1 1/2", FOR PELTIER, BIOD. DET. BLK. (115V OR 230V)
8670-1418	1/4" TO 1/8" VESPEL REDUCING FERRULE, PACK OF 10
8670-1419	1/4" TO 1/8" TEFLON® REDUCING FERRULE, PACK OF 10
8670-1450	TRAP HEATER ASSEMBLY WITH T-COUPLE
8670-1460	TYPE K THERMOCOUPLE, 36"
8670-1501	DESORBER BULKHEAD
8670-1502	GAS DELIVERY LINE WITH CONNECTOR, THERMAL DESORBER
8670-1506	1/16" S.S. FERRULE SET, PACK OF 10