

SRIGC PRODUCTS LIST 2014

(Ctrl F)
> Cat.#s



> Current System AUD Prices

8670-1590	3/8" GRAPHITE FERRULE FOR TSD (EACH)
8670-1800	1/8" BRASS NUT, PACK OF 10
8670-1801	1/8" BRASS FERRULE SET, PACK OF 10
8670-1805	1/8" S.S. NUT, PACK OF 10
8670-1806	1/8" S.S. FERRULE SET, PACK OF 10
8670-1814	1/4" TO 1/8" REDUCING FITTING, FOR CTR COLUMN, ETC.
8670-1815	1/4" TO 1/8" REDUCING FITTING, WITH 1/16" GAS LINE ENTRY
8670-1818	1/8" GRAPHITE STRAIGHT FERRULES, PACK OF 10
8670-1828	GRAPHITE REDUCING FERRULE, 1/8" - 0.5MM, PACK OF 10
8670-1853	GRAPHITE REDUCING FERRULE, 1/8" - 0.8MM, PACK OF 10
8670-1855	1/4" GRAPHITE STRAIGHT FERRULE, PACK OF 10
8670-2007	REPLACEMENT CCD DETECTOR ELEMENT
8670-2085	DFFD-FID DETECTOR BODY
8670-2270	AIR COMPRESSOR, REPLACEMENT, 230VAC
8670-2368	INJECTION PORT COUPLER TO LIQUID AUTOSAMPLER CAROUSEL
8670-3500	AUTOSAMPLER MOUNTING SYSTEM, FOR HTA
8670-5052	UPGRADE 5030 P&T TO METHOD 5030/5035 COMPLIANT (NEW BUILD ONLY)
8670-5600	PROBE, REPLACEMENT, FOR HC/H2 LEAK DETECTOR
8670-5850	SAMPLE STREAM DRYER
8670-5860	ON-LINE SAMPLER / SPARGER FOR HRVOC
8670-6000	DIGITAL FLOW CONTROLLER
8670-6015	FLUISTOR (EPC MODULE) WITH CONNECTOR, CURRENT 8610C
8670-6016	EPC CIRCUIT BOARD
8670-6020	PRESSURE SENSOR WITH CONNECTOR, FOR EPC
8670-6021	TANK PRES. REGULATOR w/ CGA FITTING
8670-6022	NORGREN GAS PRESSURE REGULATOR
8670-6023	NORGREN PRESSURE REGULATOR w/ SENSOR
8670-6024	WATTS GAS PRESSURE REGULATOR
8670-6025	WATTS PRESSURE REGULATOR w/ SENSOR
8670-6026	GAUGE FOR REGULATOR
8670-6500	OVEN CIRCULATING FAN
8670-6550	GREY OVEN COOLING FAN, WITH COOLING MUFFIN FAN
8670-6554	HEATSINK FAN
8670-6575	CHASSIS FAN, 24VDC, FOR 8610C/310
8670-6576	CHASSIS FAN, 115VAC, FOR 8610C/310
8670-6600	COLUMN OVEN LID, 8610B
8670-8000	SAMPLE LOOP (SPECIFY VOLUME BETWEEN 0.5mL and 3.0mL)
8670-9001	GC MAINTENANCE KIT, 8610C 115V
8670-9002	GC MAINTENANCE KIT, 8610C 220 VAC
8670-9003	GC MAINTENANCE KIT, 8610B 115V
8670-9004	GC MAINTENANCE KIT, 8610B 230V
8670-9005	GC MAINTENANCE KIT, 310 115V
8670-9006	GC MAINTENANCE KIT, 310 230V
8670-9007	UPGRADE TCD TO CURRENT HIGH TEMPERATURE MODEL (HARDWARE ONLY)
8670-9008	MAINTENANCE KIT, HYDROGEN GENERATOR (MINUS CELL)
8670-9010	FID MAINTENANCE KIT
8670-9090	SEPTUM NUT w/ GUIDE FOR 26GA. NEEDLE
8670-9093	0.53mm CAPILLARY COLUMN ADAPTER
8670-9094	INJECTOR BODY
8670-9095	SEPTUM NUT W/ GUIDE FOR 20GA. NEEDLE
8670-9096	SEPTUM NUT W/ GUIDE FOR 20GA. NEEDLE, FOR HEATED INJECTOR
8670-9100	TCD CELL STAINLESS STEEL, GOWMAC-TYPE
8670-9110	O-RING FOR TCD FILAMENT, EACH (MIN. QTY 10)
8670-9120	TCD FILAMENT, TUNGSTEN-RHENIUM (SPECIFY COPPER OR VITON SEAL)
8670-9121	TCD FILAMENT, GOLD PLATED, SET OF FOUR (AuW 13-300)
8670-9122	O-RING, FOR TCD FILAMENT, PACK OF 10
8670-9123	NUT, TCD, FILAMENT RETAINING (WAS FILAMENT W/ CU SEAL)
8670-9124	COPPER SEAL, FOR TCD FILAMENT, PACK OF 10
8670-9125	TCD FILAMENT PROTECTION CIRCUIT (RETROFIT)
8670-9127	TCD CELL w/ FILAMENTS, SRI MODEL (EXCHANGE)
8670-9304	HEATED TRANSFER LINE ADDITION, FOR NEW BUILD GC, RT. SIDE
8670-9305	HEATED TRANSFER LINE MOD. w/ PLUG
8670-9306	HEATED TRANSFER LINE, CAPILLARY TUBING
8670-9550	SYRINGE 10 UL
8670-9554	SRI TUBING CUTTER FOR COPPER TUBING
8670-9555	TUBING COPPER 1/8", 50' ROLL
8670-9556	1/16" S.S. TUBE FOR P&T SPARGE GAS