

SRIGC PRODUCTS LIST 2014

(Ctrl F)
> Cat.#s



> Current System AUD Prices

8690-1026	DELCD DETECTOR
8690-1051	METHOD TO-14 AIR CONCENTRATOR, VAC PUMP, 1 TRAP
8690-1052	METHOD TO-14 AIR CONCENTRATOR, 2 TRAP, w/TUBE DESORBER
8690-1055	METHOD TO-14 AIR CONCENTRATOR, VAC PUMP, 2 TRAPS
8690-1068	ON-LINE SYRINGE SAMPLER (NO CAROUSEL)
8690-1070	REPLACEMENT AIR FILTER
8690-1080	FPD/FID DETECTOR WITH DUAL AMPLIFIERS
8690-1081	REPLACEMENT METHANIZER TUBE
8690-1087	THERMAL DESORBER SAMPLE TUBE (PK. OF 10)
8690-1088	THERMAL SOIL DESORBER, MANUAL ACTUATOR
8690-1115	FID / NPD CONVERTIBLE DETECTOR
8690-2007	CCD DETECTOR
8690-2022	ADDITIONAL EPC CONTROL ZONE (NO INJECTOR)
8690-2023	ADDITIONAL INJECTION PORT WITHOUT EPC CONTROL/CARRIER
8690-2026	FID-DELCD DETECTOR (FID-DELCD)
8690-2084	DUAL HEATED TRAPS FOR EXISTING VALVES
8690-2085	DFPD-FID DETECTOR (3 AMPLIFIERS)
8690-2253	10 STATION PURGE-AND-TRAP AUTOSAMPLER 230V, 4 REL BD
8690-2270	INTERNAL WHISPER-QUIET AIR COMPRESSOR, 230V
8690-2615	NPD-DELCD SERIES DETECTOR
8690-5052	UPGRADE PURGE & TRAP TO 5030/5035 COMPLIANT
8690-5510	DIGITAL MULTIMETER, GENERAL PURPOSE
8690-5600	H2 / HC LEAK DETECTOR, AC POWERED, WITH DIGITAL VOLTMETER
8690-5655	H2 / HC LEAK DETECTOR, BUILT INTO 1 CH. DATA SYSTEM
8690-7000	OP-AMP CHIP, LF356 (REPLACES OP-80A)
8690-7034	HEATED SPLIT/SPLITLESS INJECTOR UPGRADE WITH PTV
8690-7100	SCR - TRIAC CIRCUIT BOARD
8690-8034	HEATED SPLIT/SPLITLESS INJECTOR UPGRADE WITH PTV, VALVE
8690-8294	METHANIZER/OXIDIZER UNIT, FOR METHOD 25-3
8690-9305	HEATED TRANSFER LINE WITH THERMOCOUPLE, 115VAC
8690-LPGH	LPG HEATED EXPANSION CHAMBER / HOMOGENIZER