

10144 Rtx-1 Cap. Column
 10145 Rtx-1 Cap. Column
 10145-6850 Rtx-1 Cap. Column
 10147 Rtx-DHA-50 Cap. Column
 10148 Rtx-DHA-100 Cap. Column
 10149 Rtx-DHA-150 Cap. Column
 10150 Rtx-1 Cap. Column
 10150-124 Rtx-1 Cap. Column
 10150-28205 Rtx-1 Cap. Column
 10151 Rtx-1 Cap. Column
 10151-104 Rtx-1 Cap. Column
 10151-107 Rtx-1 Cap. Column
 10151-123 Rtx-1 Cap. Column
 10151-125 Rtx-1 Cap. Column
 10151-6850 Rtx-1 Cap. Column
 10152 Rtx-1 Cap. Column
 10152-104 Rtx-1 Cap. Column
 10152-107 Rtx-1 Cap. Column
 10152-123 Rtx-1 Cap. Column
 10152-126 Rtx-1 Cap. Column
 10152-6850 Rtx-1 Cap. Column
 10153 Rtx-1 Cap. Column
 10153-124 Rtx-1 Cap. Column
 10153-127 Rtx-1 Cap. Column
 10153-280 Rtx-1 Cap. Column
 10153-600 Rtx-1 Cap. Column
 10153-6850 Rtx-1 Cap. Column
 10154 Rtx-1 Cap. Column
 10154-101 Rtx-1 Cap. Column
 10154-106 Rtx-1 Cap. Column
 10154-112 Rtx-1 Cap. Column
 10154-125 Rtx-1 Cap. Column
 10154-12568 Rtx-1 Cap. Column
 10154-128 Rtx-1 Cap. Column
 10154-282 Rtx-1 Cap. Column
 10154-289 Rtx-1 Cap. Column
 10154-600 Rtx-1 Cap. Column
 10154-6850 Rtx-1 Cap. Column
 10155 Rtx-1 Cap. Column
 10155-051 Rtx-1 Cap. Column
 10155-101 Rtx-1 Cap. Column
 10155-102 Rtx-1 Cap. Column
 10155-106 Rtx-1 Cap. Column
 10155-10628 Rtx-1 Cap. Column
 10155-126 Rtx-1 Cap. Column
 10155-12660 Rtx-1 Cap. Column
 10155-12668 Rtx-1 Cap. Column
 10155-129 Rtx-1 Cap. Column
 10155-284 Rtx-1 Cap. Column
 10155-6850 Rtx-1 Cap. Column
 10156 Rtx-1 Cap. Column
 10156-105 Rtx-1 Cap. Column
 10156-10560 Rtx-1 Cap. Column
 10156-124 Rtx-1 Cap. Column
 10156-138 Rtx-1 Cap. Column
 10156-600 Rtx-1 Cap. Column
 10156-6850 Rtx-1 Cap. Column
 10157 Rtx-1 Cap. Column
 10157-051 Rtx-1 Cap. Column
 10157-105 Rtx-1 Cap. Column
 10157-125 Rtx-1 Cap. Column
 10157-128 Rtx-1 Cap. Column
 10157-600 Rtx-1 Cap. Column
 10157-6850 Rtx-1 Cap. Column
 10158 Rtx-1 Cap. Column
 10158-109 Rtx-1 Cap. Column

Page 6
 105m, 0.25mm ID, 0.50um
 105m, 0.32mm ID, 0.50um
 105m, 0.32mm ID, 0.50um on 6850 Cage
 50m, 0.20mm ID, 0.5um
 100m, 0.25mm ID, 0.5um
 150m, 0.25mm ID, 1.0um
 15m, 0.25mm ID, 1.00um
 15m, 0.25mm ID, 1.00um with 5m Integra-Guard Column
 15m, 0.25mm ID, 1.00um Recoil f.s. column into 5" diameter No Cage No guarant
 15m, 0.32mm ID, 1.00um
 3-5m, 0.32mm ID, 1.00um
 10m, 0.32mm ID, 1.00um
 1-10m, 1-5m, 0.32mm ID, 1.00um
 15m, 0.32mm ID, 1.0um w/5m 0.32mm Integra Guard
 15m, 0.32mm ID, 1.00um 5" HP6850 Cage
 15m, 0.53mm ID, 1.00um
 3 x 5m, 0.53mm ID, 1.00um
 10m, 0.53mm ID, 1.00um
 1x10m & 1x5m, 0.53mm ID, 1.00um
 15m, 0.53mm ID, 1.00um with 5m Integra-Guard Column
 15m, 0.53mm ID, 1.00um with 5" cage for HP 6850 GC
 30m, 0.25mm ID, 1.00um
 30m, 0.25mm ID, 1.00um with 5m Integra-Guard Column
 30m, 0.25mm ID, 1.00um with 10m Integra-Guard Column
 30m, 0.25mm ID, 1.0um 4" Star Cage
 30m, 0.25mm ID, 1.00um Pack of 6
 30m, 0.25mm ID, 1.00um 5" HP 6850 Cage
 30m, 0.32mm ID, 1.00um
 3-10m 0.32mm ID, 1.00um
 25m, 0.32mm ID, 1.00um
 20m, 0.32mm ID, 1.00um
 30m, 0.32mm ID, 1.00um with 5m Integra-Guard Column
 30m, 0.32mm ID, 1.00um w/5m 0.32mm Integra Guard 5" HP6850 Cage
 30m, 0.32mm ID, 1.00um with 10m Integra-Guard Column
 30m, 0.32mm ID, 1.00um w/5 inch inner diameter coil
 30m, 0.32mm ID, 1.0um 4.5" Coil - No Cage - No Guarantee for Breakage
 30m, 0.32mm ID, 1.00um Pack of 6
 30m, 0.32mm ID, 1.00um 5" Cage
 30m, 0.53mm ID, 1.00um
 30m, 0.53mm ID, 1.00um No Cage*NO GUARANTEE FOR BREAKAGE*
 3 x 10m, 0.53mm ID, 1.00um
 10m, 20m, 0.53mm ID, 1.00um
 30m, 0.53mm ID, 1.00um Break 30m into 25m column
 25m, 0.53mm, , 1.0um 3.5" coil
 30m, 0.53mm ID, 1.00um with 5m Integra-Guard Column
 30m, 0.53mm ID, 1.00um w/5m Integra Guard, Pack of 6
 30m, 0.53mm ID, 1.00um w/ 5m Integra-Guard Column For HP 6850 Cage
 30m, 0.53mm ID, 1.00um with 10m Integra-Guard Column
 30m, 0.53mm, 1.0um with 3.5" coil No Guarantee for Breakage
 30m, 0.53mm ID, 1.00um 5" Cage for HP6850
 60m, 0.25mm ID, 1.00um
 50m, 0.25mm ID, 1.00um
 50m, 0.25mm ID, 1.00um 6pk
 60m, 0.25mm ID, 1.0um w/5m 0.25mm guard
 45m & 15m, 0.25mm ID, 1.00um
 60m, 0.25mm ID, 1.00um Pack of 6
 60m, 0.25mm ID, 1.00um 5" Cage for HP6850's
 60m, 0.32mm ID, 1.00um
 60m, 0.32mm ID, 1.00um No Cage no guarantee for breakage
 50m, 0.32mm ID, 1.00um
 60m, 0.32mm ID, 1.00um with 5m Integra-Guard Column
 60m, 0.32mm ID, 1.00um with 10m Integra-Guard Column
 60m, 0.32mm ID, 1.00um Pack of 6
 60m, 0.32mm ID, 1.00um 5"/HP6850 Cage
 60m, 0.53mm ID, 1.00um
 50m & 10m, 0.53mm ID, 1.00um

(Ctrl F)
 > Cat.#s

> Current System AUD Prices

