

10238	Rtx-5 Cap. Column	30m, 0.25mm ID, 0.50um
10238-106	Rtx-5 Cap. Column	25m, 0.25mm ID, 0.50um
10238-124	Rtx-5 Cap. Column	30m, 0.25mm ID, 0.50um with 5m Integra-Guard Column
10238-127	Rtx-5 Cap. Column	30m, 0.25mm ID, 0.50um with 10m Integra-Guard Column
10238-303	Rtx-5 Cap. Column	30m, 0.25mm ID, 0.50um w/Presstighted 5m, 0.25mm Guard Column
10238-600	Rtx-5 Cap. Column	30m, 0.25mm ID, 0.50um Pack of 6
10238-6850	Rtx-5 Cap. Column	30m, 0.25mm ID, 0.50um 5" cage
10239	Rtx-5 Cap. Column	30m, 0.32mm ID, 0.50um
10239-106	Rtx-5 Cap. Column	25m, 0.32mm ID, 0.50um
10239-125	Rtx-5 Cap. Column	30m, 0.32mm ID, 0.50um with 5m Integra-Guard Column
10239-128	Rtx-5 Cap. Column	30m, 0.32mm ID, 0.50um with 10m Integra-Guard Column
10239-144	Rtx-5 Cap. Column	25m & 5m, 0.32mm ID, 0.50um
10239-365	Rtx-5 Cap. Column	30m, 0.32mm ID, 0.50um w/5m 0.32mm Siltek Guard Column & Siltek Presstight
10239-600	Rtx-5 Cap. Column	30m, 0.32mm ID, 0.50um 6pk
10239-6850	Rtx-5 Cap. Column	30m, 0.32mm ID, 0.50um 5" Cage for HP6850
10240	Rtx-5 Cap. Column	30m, 0.53mm ID, 0.50um
10240-126	Rtx-5 Cap. Column	30m, 0.53mm ID, 0.50um with 5m Integra-Guard Column
10240-129	Rtx-5 Cap. Column	30m, 0.53mm ID, 0.50um with 10m Integra-Guard Column
10240-1296850	Rtx-5 Cap. Column	30m, 0.53mm ID, 0.50um w/10m, 0.53mm guard 5" cage for HP 6850
10240-600	Rtx-5 Cap. Column	30m, 0.53mm ID, 0.50um 6pk
10240-6850	Rtx-5 Cap. Column	30m, 0.53mm ID, 0.5um 5" HP6850 Cage
10241	Rtx-5 Cap. Column	60m, 0.25mm ID, 0.50um
10242	Rtx-5 Cap. Column	60m, 0.32mm ID, 0.50um
10242-105	Rtx-5 Cap. Column	50m, 0.32mm ID, 0.50um
10242-125	Rtx-5 Cap. Column	60m, 0.32mm ID, 0.50um w/5m, 0.32mm ID Integra Guard
10242-128	Rtx-5 Cap. Column	60m, 0.32mm ID, 0.50um with 10m Integra Guard
10242-138	Rtx-5 Cap. Column	45m & 15m, 0.32mm ID, 0.50um
10242-6850	Rtx-5 Cap. Column	60m, 0.32mm ID, 0.50um 5" cage for HP 6850
10243	Rtx-5 Cap. Column	60m, 0.53mm ID, 0.50um
10243-105	Rtx-5 Cap. Column	50m, 0.53mm ID, 0.50um
10243-129	Rtx-5 Cap. Column	60m, 0.53mm ID, 0.5um w/10m Integra Guard
10244	Rtx-5 Cap. Column	105m, 0.25mm ID, 0.50um
10245	Rtx-5 Cap. Column	105m, 0.32mm ID, 0.50um
10250	Rtx-5 Cap. Column	15m, 0.25mm ID, 1.00um
10250-104	Rtx-5 Cap. Column	3 - 5m, 0.25mm ID, 1.00um
10250-124	Rtx-5 Cap. Column	15m 0.25mm ID, 1.00um with 5m Integra Guard Column
10250-127	Rtx-5 Cap. Column	15m, 0.25mm ID, 1.00um 10m, 0.25mm guard built in
10250-6850	Rtx-5 Cap. Column	15m, 0.25mm ID, 1.00um For HP 6850
10251	Rtx-5 Cap. Column	15m, 0.32mm ID, 1.00um
10251-125	Rtx-5 Cap. Column	15m, 0.32mm ID, 1.00um with 5m Integra-Guard Column
10251-128	Rtx-5 Cap. Column	15m, 0.32mm ID, 1.00um with 10m Integra-Guard Column
10251-305	Rtx-5 Cap. Column	15m, 0.32mm ID, 1.00um w/5m, 0.53mm IP Deact Presstight Guard Col.
10251-600	Rtx-5 Cap. Column	15m, 0.32mm ID, 1.00um Package of 6
10251-6850	Rtx-5 Cap. Column	15m, 0.32mm ID, 1.00um 5" HP6850 Cage
10252	Rtx-5 Cap. Column	15m, 0.53mm ID, 1.00um
10252-126	Rtx-5 Cap. Column	15m, 0.53mm ID, 1.00um with 5m Integra-Guard Column
10252-129	Rtx-5 Cap. Column	15m, 0.53mm ID, 1.00um with 10m Integra-Guard Column
10252-600	Rtx-5 Cap. Column	15m, 0.53mm ID, 1.00 Pack of 6
10252-6850	Rtx-5 Cap. Column	15m, 0.53mm ID, 1.00um Configured for 6850 GC
10253	Rtx-5 Cap. Column	30m, 0.25mm ID, 1.00um
10253-124	Rtx-5 Cap. Column	30m, 0.25mm ID, 1.00um with 5m Integra-Guard Column
10253-124600	Rtx-5 Cap. Column	30m, 0.25mm ID, 1.00um with 5m Integra Guard, 6pk
10253-127	Rtx-5 Cap. Column	30m, 0.25mm ID, 1.00um with 10m Integra-Guard Column
10253-303	Rtx-5 Cap. Column	30m, 0.25mm ID, 1.00um w/5m x 0.25mm ID Guard Column Presstight with glue
10253-600	Rtx-5 Cap. Column	30m, 0.25mm ID, 1.00um Package of 6
10253-6850	Rtx-5 Cap. Column	30m, 0.25mm ID, 1.00um 5" cage for HP 6850
10254	Rtx-5 Cap. Column	30m, 0.32mm ID, 1.00um
10254-031	Rtx-5 Cap. Column	30m, 0.32mm ID, 1.00um Cage column in customers cage.
10254-106	Rtx-5 Cap. Column	25m, 0.32mm ID, 1.00um
10254-125	Rtx-5 Cap. Column	30m, 0.32mm ID, 1.00um with 5m Integra-Guard Column
10254-128	Rtx-5 Cap. Column	30m, 0.32mm ID, 1.00um with 10m Integra-Guard Column
10254-289	Rtx-5 Cap. Column	30m, 0.32mm ID, 1.00um 4.5" Diameter, no cage
10254-303	Rtx-5 Cap. Column	30m, 0.32mm ID, 1.00um w/5m x 0.25mm ID Guard Column Presstight with glue
10254-304	Rtx-5 Cap. Column	30m, 0.32mm ID, 1.00um w/5m x 0.32mm ID Guard Column Presstight with glue
10254-305	Rtx-5 Cap. Column	30m, 0.32mm ID, 1.00um 5m x 0.53mm Guard Column w/Presstight
10254-600	Rtx-5 Cap. Column	30m, 0.32mm ID, 1.00um Package of 6

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



HROMalytic +61(0)3 9762 2034
ECHnology Pty Ltd

Australian Distributors
 Importers & Manufacturers
www.chromtech.net.au

Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

(Ctrl F)
> Cat.#s

> Current System AUD Prices

