

10254-6850	Rtx-5 Cap. Column
10255	Rtx-5 Cap. Column
10255-042	Rtx-5 Cap. Column
10255-126	Rtx-5 Cap. Column
10255-129	Rtx-5 Cap. Column
10255-305	Rtx-5 Cap. Column
10255-600	Rtx-5 Cap. Column
10255-6850	Rtx-5 Cap. Column
10256	Rtx-5 Cap. Column
10256-124	Rtx-5 Cap. Column
10256-127	Rtx-5 Cap. Column
10256-6850	Rtx-5 Cap. Column
10257	Rtx-5 Cap. Column
10257-105	Rtx-5 Cap. Column
10257-108	Rtx-5 Cap. Column
10257-125	Rtx-5 Cap. Column
10257-600	Rtx-5 Cap. Column
10257-6850	Rtx-5 Cap. Column
10258	Rtx-5 Cap. Column
10258-105	Rtx-5 Cap. Column
10259	Rtx-5 Cap. Column
10260	Rtx-5 Cap. Column
10260-324	Rtx-5 Cap. Column
10260-6850	Rtx-5 Cap. Column
10266	Rtx-5 Cap. Column
10266-125	Rtx-5 Cap. Column
10267	Rtx-5 Cap. Column
10267-096	Rtx-5 Cap. Column
10267-104	Rtx-5 Cap. Column
10267-126	Rtx-5 Cap. Column
10267-129	Rtx-5 Cap. Column
10267-282	Rtx-5 Cap. Column
10267-6850	Rtx-5 Cap. Column
10269	Rtx-5 Cap. Column
10269-125	Rtx-5 Cap. Column
10269-125685	Rtx-5 Cap. Column
10269-128	Rtx-5 Cap. Column
10269-6850	Rtx-5 Cap. Column
10270	Rtx-5 Cap. Column
10270-042	Rtx-5 Cap. Column
10270-106	Rtx-5 Cap. Column
10270-126	Rtx-5 Cap. Column
10270-126685	Rtx-5 Cap. Column
10270-129	Rtx-5 Cap. Column
10270-129685	Rtx-5 Cap. Column
10270-280	Rtx-5 Cap. Column
10270-305	Rtx-5 Cap. Column
10270-600	Rtx-5 Cap. Column
10270-6850	Rtx-5 Cap. Column
10272	Rtx-5 Cap. Column
10273	Rtx-5 Cap. Column
10273-126	Rtx-5 Cap. Column
10273-6850	Rtx-5 Cap. Column
10275	Rtx-5 Cap. Column
10277	Rtx-5 Cap. Column
10277-107	Rtx-5 Cap. Column
10277-126	Rtx-5 Cap. Column
10277-600	Rtx-5 Cap. Column
10279	Rtx-5 Cap. Column
10279-126	Rtx-5/Rtx-G27 Cap. Column
10279-126685	Rtx-5 Cap. Column
10279-129	Rtx-5 Cap. Column
10279-305	Rtx-5 Cap. Column
10279-600	Rtx-5 Cap. Column
10279-6850	Rtx-5 Cap. Column
10281	Rtx-5 Cap. Column

30m, 0.32mm ID, 1.00um on 6850 Ca
30m, 0.53mm ID, 1.00um
30m, 0.53mm ID, 1.00um on 5" Nordic...
30m, 0.53mm ID, 1.00um with 5m Integra-Guard Column
30m, 0.53mm ID, 1.00um with 10m Integra-Guard Column
30m, 0.53mm ID, 1.00um w/5m x 0.53mm ID Guard Column Presstight with glue
30m, 0.53mm ID, 1.00um Package of 6
30m, 0.53mmID, 1.00um 5" cage for HP 6850
60m, 0.25mm ID, 1.00um
60m, 0.25mmID, 1.00um 5m, 0.25mm Guard column built in
60m, 0.25mm ID, 1.00um w/10m 0.25mm Integra Guard
60m, 0.25mm ID, 1.00um 5" Cage for HP 6850 GCs
60m, 0.32mm ID, 1.00um
50m, 0.32mm ID, 1.00um
60m, 0.32mmID, 1.00um Break a 60m into 6 x 10m columns
60m, 0.32mm ID, 1.00um w/5m Integra Guard
60m, 0.32mm ID, 1.00um Pack of 6
60m, 0.32mm ID, 1.0um 5" HP6850 Cage
60m, 0.53mm ID, 1.00um
50m, 0.53mm ID, 1.00um
105m, 0.25mm ID, 1.00um
105m, 0.32mm ID, 1.00um
105m, 0.32mm ID, 1.00um 5m Guard Column w/Cap Vu-Union
105m, 0.32mm ID, 1.00um 5in cage for HP 6850
15m, 0.32mm ID, 1.50um
15m, 0.32mm ID, 1.50um with 5m Integra-Guard Column
15m, 0.53mm ID, 1.50um
15m, 0.53mmID, 1.50um Break into 2 6m columns
3-5m, 0.53mm ID, 1.50um
15m, 0.53mm ID, 1.50um with 5m Integra-Guard Column
15m, 0.53mm ID, 1.50um with 10m Integra-Guard Column
15m, 0.53mm, 1.50um 5in Cage, No Guarantee for breakage
15m, 0.53mm ID, 1.50um 5" Cage for HP 6850 GCs
30m, 0.32mm ID, 1.50um
30m, 0.32mm ID, 1.50um w/5m, 0.32mm ID Integra Guard
30m, 0.32mm ID, 1.50um w/5m, 0.32mmID Integra Guard on 5" cage for Agilent 6
30m, 0.32mm ID, 1.50um with 10m Integra-Guard Column
30m, 0.32mm ID, 1.50um 5" HP6850 Cage
30m, 0.53mm ID, 1.50um
30m, 0.53mmID, 1.50um cage column in 5" Nordion cage
25m, 0.53mm ID, 1.50um
30m, 0.53mm ID, 1.50um with 5m Integra-Guard Column
30m, 0.53mm ID, 1.50um w/ 5m Integra-Guard Column, 5" Cage on HP 6850
30m, 0.53mm ID, 1.50um with 10m Integra-Guard Column
30m, 0.53mm ID, 1.50um 10m, 0.53mm Integra guard built in 5" cage for HP 6850
30m, 0.53mm ID, 1.50um 4" cage no guarantee for breakage Includes Star cage
30m, 0.53mm ID, 1.50um w/5m x 0.53mm ID Guard Column Presstight with glue
30m, 0.53mm ID, 1.50um Package of 6
30m, 0.53mm ID, 1.50um 5" cage for HP 6850
60m, 0.32mm ID, 1.50um
60m, 0.53mm ID, 1.50um
60m, 0.53mm ID, 1.5um w/5m 0.53mm Integra Guard
60m, 0.53mm ID, 1.50um 5" Cage for HP6850
105m, 0.32mm ID, 1.50um
15m, 0.53mm ID, 5.00um
10m, 0.53mm ID, 5.00um
15m, 0.53mm ID, 5.00um w/5m 0.53mm Integra Guard
15m, 0.53mm ID, 5.00um Pack of 6
30m, 0.53mm ID, 5.00um
30m, 0.53mm ID, 5.00um w/5m Integra-Guard Column Rtx-G27 (Rtx-5)
30m, 0.53mm ID, 5.00um (G27) with 5m Integra-Guard Column 5" HP 6850 Cage
30m, 0.53mm ID, 5.00um with 10m Integra-Guard Column
30m, 0.53mm ID, 5.00um w/5m x 0.53mm ID Guard Column Presstight with glue
30m, 0.53mm ID, 5.00um Pack of 6
30m, 0.53mm ID, 5.0um with 5" cage for HP 6850 GC
15m, 0.32mm ID, 3.00um

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



HROMalytic +61(0)3 9762 2034
ECHnology Pty Ltd
 Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

Australian Distributors
 Importers & Manufacturers
www.chromtech.net.au

