

| | | |
|------------|--------------------|---|
| 10328 | Rtx-20 Cap. Column | 60m, 0.53mm ID, 0.25um |
| 10329 | Rtx-20 Cap. Column | 105m, 0.25mm ID, 0.25um |
| 10330 | Rtx-20 Cap. Column | 105m, 0.32mm ID, 0.25um |
| 10335 | Rtx-20 Cap. Column | 15m, 0.25mm ID, 0.50um |
| 10336 | Rtx-20 Cap. Column | 15m, 0.32mm ID, 0.50um |
| 10337 | Rtx-20 Cap. Column | 15m, 0.53mm ID, 0.50um |
| 10338 | Rtx-20 Cap. Column | 30m, 0.25mm ID, 0.50um |
| 10338-127 | Rtx-20 Cap. Column | 30m, 0.25mm ID, 0.50um 10m, 0.25mm ID Guard |
| 10339 | Rtx-20 Cap. Column | 30m, 0.32mm ID, 0.50um |
| 10339-6850 | Rtx-20 Cap. Column | 30m, 0.32mm ID, 0.50um For HP 6850 GCs |
| 10340 | Rtx-20 Cap. Column | 30m, 0.53mm ID, 0.50um |
| 10340-126 | Rtx-20 Cap. Column | 30m, 0.53mmID, 0.50um w/ 5m 0.53mm Guard column built in |
| 10341 | Rtx-20 Cap. Column | 60m, 0.25mm ID, 0.50um |
| 10342 | Rtx-20 Cap. Column | 60m, 0.32mm ID, 0.50um |
| 10343 | Rtx-20 Cap. Column | 60m, 0.53mm ID, 0.50um |
| 10344 | Rtx-20 Cap. Column | 105m, 0.25mm ID, 0.50um |
| 10345 | Rtx-20 Cap. Column | 105m, 0.32mm ID, 0.50um |
| 10350 | Rtx-20 Cap. Column | 15m, 0.25mm ID, 1.00um |
| 10350-127 | Rtx-20 Cap. Column | 15m, 0.25mm ID, 1.00um with 10m Integra-Guard Column |
| 10351 | Rtx-20 Cap. Column | 15m, 0.32mm ID, 1.00um |
| 10351-6850 | Rtx-20 Cap. Column | 15m, 0.32mm ID, 1.00um 5" Cage for HP6850 |
| 10352 | Rtx-20 Cap. Column | 15m, 0.53mm ID, 1.00um |
| 10353 | Rtx-20 Cap. Column | 30m, 0.25mm ID, 1.00um |
| 10353-600 | Rtx-20 Cap. Column | 30m, 0.25mm ID, 1.00um Pack of 6 |
| 10354 | Rtx-20 Cap. Column | 30m, 0.32mm ID, 1.00um |
| 10354-125 | Rtx-20 Cap. Column | 30m, 0.32mm ID, 1.00um w/5m 0.32mm Integra Guard |
| 10354-304 | Rtx-20 Cap. Column | 30m, 0.32mm ID, 1.00um w/5m x 0.32mm ID Guard Column Presstight with glue |
| 10354-6850 | Rtx-20 Cap. Column | 30m, 0.32mm ID, 1.00um 5" Cage for HP6850 |
| 10355 | Rtx-20 Cap. Column | 30m, 0.53mm ID, 1.00um |
| 10355-6850 | Rtx-20 Cap. Column | 30m, 0.53mm ID, 1.00um 5" Cage for HP6850 |
| 10356 | Rtx-20 Cap. Column | 60m, 0.25mm ID, 1.00um |
| 10357 | Rtx-20 Cap. Column | 60m, 0.32mm ID, 1.00um |
| 10357-600 | Rtx-20 Cap. Column | 60m, 0.32mm ID, 1.00um 6pk |
| 10357-6850 | Rtx-20 Cap. Column | 60m, 0.32mm ID, 1.00um 5" cage for HP 6850 |
| 10358 | Rtx-20 Cap. Column | 60m, 0.53mm ID, 1.00um |
| 10359 | Rtx-20 Cap. Column | 105m, 0.25mm ID, 1.00um |
| 10360 | Rtx-20 Cap. Column | 105m, 0.32mm ID, 1.00um |
| 10366 | Rtx-20 Cap. Column | 15m, 0.32mm ID, 1.50um |
| 10367 | Rtx-20 Cap. Column | 15m, 0.53mm ID, 1.50um |
| 10369 | Rtx-20 Cap. Column | 30m, 0.32mm ID, 1.50um |
| 10370 | Rtx-20 Cap. Column | 30m, 0.53mm ID, 1.50um |
| 10370-126 | Rtx-20 Cap. Column | 30m, 0.53mm ID, 1.50um w/5m 0.53mm Integra Guard |
| 10372 | Rtx-20 Cap. Column | 60m, 0.32mm ID, 1.50um |
| 10373 | Rtx-20 Cap. Column | 60m, 0.53mm ID, 1.50um |
| 10373-6850 | Rtx-20 Cap. Column | 60m, 0.53mm ID, 1.50um 5" Cage for HP 6850 |
| 10375 | Rtx-20 Cap. Column | 105m, 0.32mm ID, 1.50um |
| 10381 | Rtx-20 Cap. Column | 15m, 0.32mm ID, 3.00um |
| 10382 | Rtx-20 Cap. Column | 15m, 0.53mm ID, 3.00um |
| 10384 | Rtx-20 Cap. Column | 30m, 0.32mm ID, 3.00um |
| 10384-128 | Rtx-20 Cap. Column | 30m, 0.32mm ID, 3.00um w/10m Integra Guard |
| 10384-6850 | Rtx-20 Cap. Column | 30m, 0.32mm ID, 3.00um For HP 6850 GCs |
| 10385 | Rtx-20 Cap. Column | 30m, 0.53mm ID, 3.00um |
| 10385-126 | Rtx-20 Cap. Column | 30m, 0.53mm ID, 3.00um w/ 5m, 0.53mmID Integra Guard |
| 10385-6850 | Rtx-20 Cap. Column | 30m, 0.53mm ID, 3.00um 5in cage for HP 6850 |
| 10387 | Rtx-20 Cap. Column | 60m, 0.32mm ID, 3.00um |
| 10388 | Rtx-20 Cap. Column | 60m, 0.53mm ID, 3.00um |
| 10390 | Rtx-20 Cap. Column | 105m, 0.32mm ID, 3.00um |
| 10405 | Rtx-35 Cap. Column | 15m, 0.25mm ID, 0.10um |
| 10406 | Rtx-35 Cap. Column | 15m, 0.32mm ID, 0.10um |
| 10407 | Rtx-35 Cap. Column | 15m, 0.53mm ID, 0.10um |
| 10408 | Rtx-35 Cap. Column | 30m, 0.25mm ID, 0.10um |
| 10409 | Rtx-35 Cap. Column | 30m, 0.32mm ID, 0.10um |
| 10410 | Rtx-35 Cap. Column | 30m, 0.53mm ID, 0.10um |
| 10410-126 | Rtx-35 Cap. Column | 30m, 0.53mm ID, 0.10um with 5m Integra-Guard Column |
| 10411 | Rtx-35 Cap. Column | 60m, 0.25mm ID, 0.10um |
| 10412 | Rtx-35 Cap. Column | 60m, 0.32mm ID, 0.10um |

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

| | | |
|---|--|---|
|  HROMalytic +61(0)3 9762 2034 ECHnology Pty Ltd | | Australian Distributors Importers & Manufacturers www.chromtech.net.au |
| Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA | | |

[Ctrl F]
> Cat.#s

> Current System AUD Prices

