

10539-6850	Rtx-50 Cap. Column	30m, 0.32mm ID, 0.50um 5" Cage for
10540	Rtx-50 Cap. Column	30m, 0.53mm ID, 0.50um
10540-600	Rtx-50 Cap. Column	30m, 0.53mm ID, 0.50um Pack of 6
10541	Rtx-50 Cap. Column	60m, 0.25mm ID, 0.50um
10542	Rtx-50 Cap. Column	60m, 0.32mm ID, 0.50um
10543	Rtx-50 Cap. Column	60m, 0.53mm ID, 0.50um
10550	Rtx-50 Cap. Column	15m, 0.25mm ID, 1.00um
10551	Rtx-50 Cap. Column	15m, 0.32mm ID, 1.00um
10551-600	Rtx-50 Cap. Column	15m, 0.32mm ID, 1.00um Pack of 6
10552	Rtx-50 Cap. Column	15m, 0.53mm ID, 1.00um
10552-104	Rtx-50 Cap. Column	3 x 5m, 0.53mmID, 1.00um
10552-305	Rtx-50 Cap. Column	15m, 0.53mm ID, 1.00um w/5m 0.53mm PT Guard Column
10552-600	Rtx-50 Cap. Column	15m, 0.53mmID, 1.00um Pack of 6
10552-6850	Rtx-50 Cap. Column	15m, 0.53mm ID, 1.00um 5" HP6850 Cage
10553	Rtx-50 Cap. Column	30m, 0.25mm ID, 1.00um
10553-6850	Rtx-50 Cap. Column	30m, 0.25mm ID, 1.00um 5" cage for HP 6850
10554	Rtx-50 Cap. Column	30m, 0.32mm ID, 1.00um
10554-031	Rtx-50 Cap. Column	30m, 0.32mm ID, 1.00um Customer Supplied Cage
10554-106	Rtx-50 Cap. Column	25m, 0.32mm ID, 1.00um
10554-6850	Rtx-50 Cap. Column	30m, 0.32mm ID, 1.00um 5" Cage for HP 6850
10555	Rtx-50 Cap. Column	30m, 0.53mm ID, 1.00um
10555-111	Rtx-50 Cap. Column	2-15m, 0.53mm ID, 1.00um
10555-305	Rtx-50 Cap. Column	30m, 0.53mm ID, 1.00um w/5m x 0.53mm ID Guard Column Presstight with glue
10555-600	Rtx-50 Cap. Column	30m, 0.53mm ID, 1.00um Pack of 6
10555-6850	Rtx-50 Cap. Column	30m, 0.53mm ID, 1.00um 5" HP6850 Cage
10556	Rtx-50 Cap. Column	60m, 0.25mm ID, 1.00um
10556-303	Rtx-50 Cap. Column	60m, 0.25mm ID, 1.00um w/5m x 0.25mm ID Guard Column Presstight
10557	Rtx-50 Cap. Column	60m, 0.32mm ID, 1.00um
10558	Rtx-50 Cap. Column	60m, 0.53mm ID, 1.00um
10558-6850	Rtx-50 Cap. Column	60m, 0.53mm ID, 1.00um 5" cage for HP 6850
10567	Rtx-50 Cap. Column	15m, 0.53mm ID, 1.50um
10567-6850	Rtx-50 Cap. Column	15m, 0.53mm ID, 1.50um 5" HP 6850 Cage
10569	Rtx-50 Cap. Column	30m, 0.53mm ID, 0.83um Rtx-50 (608)
10570	Rtx-50 Cap. Column	30m, 0.53mm ID, 1.50um
10570-306	Rtx-50 Cap. Column	30m, 0.53mm ID, 1.50um w/10m 0.53mm Presstight Guard Column
10570-600	Rtx-50 Cap. Column	30m, 0.53mm ID, 1.50um Pack of 6
10573	Rtx-50 Cap. Column	60m, 0.53mm ID, 1.50um
10605	Stabilwax Cap. Column	15m, 0.25mm ID, 0.10um
10606	Stabilwax Cap. Column	15m, 0.32mm ID, 0.10um
10607	Stabilwax Cap. Column	15m, 0.53mm ID, 0.10um
10608	Stabilwax Cap. Column	30m, 0.25mm ID, 0.10um
10608-124	Stabilwax Cap. Column	30m, 0.25mm ID, 0.10um w/5m 0.25mm Integra Guard
10608-273	Stabilwax Cap. Column	30m, 0.25mm ID, 0.10um 3.5"OD w/o Cage
10609	Stabilwax Cap. Column	30m, 0.32mm ID, 0.10um
10609-128	Stabilwax Cap. Column	30m, 0.32mmID, 0.10um 10m, 0.32mm Guard column built in
10610	Stabilwax Cap. Column	30m, 0.53mm ID, 0.10um
10611	Stabilwax Cap. Column	60m, 0.25mm ID, 0.10um
10611-127	Stabilwax Cap. Column	60m, 0.25mm ID, 0.10um w/10m 0.25mm Integra Guard
10611-6850	Stabilwax Cap. Column	60m, 0.25mm ID, 0.10um 5" Cage
10612	Stabilwax Cap. Column	60m, 0.32mm ID, 0.10um
10613	Stabilwax Cap. Column	60m, 0.53mm ID, 0.10um
10620	Stabilwax Cap. Column	15m, 0.25mm ID, 0.25um
10620-124	Stabilwax Cap. Column	15m, 0.25mm ID, 0.25um with 5m Integra-Guard Column
10620-390	Stabilwax Cap. Column	15m, 0.25mm ID, 0.25um 7cm Diameter, No Cage No Guarantee for Breakage
10620-6850	Stabilwax Cap. Column	15m, 0.25mmID, 0.25um 5" cage for HP 6850
10621	Stabilwax Cap. Column	15m, 0.32mm ID, 0.25um
10621-125	Stabilwax Cap. Column	15m, 0.32mmID, 0.25um w/5m Integra Guard
10622	Stabilwax Cap. Column	15m, 0.53mm ID, 0.25um
10623	Stabilwax Cap. Column	30m, 0.25mm ID, 0.25um
10623-112	Stabilwax Cap. Column	20m, 0.25mm ID, 0.25um
10623-124	Stabilwax Cap. Column	30m, 0.25mm ID, 0.25um with 5m Integra-Guard Column
10623-12468	Stabilwax Cap. Column	30m, 0.25mm ID, 0.25um 5m, 0.25mm guard 5in cage for HP 6850
10623-127	Stabilwax Cap. Column	30m, 0.25mm ID, 0.25um with 10m Integra-Guard Column
10623-273	Stabilwax Cap. Column	30m, 0.25mm ID, 0.25um 3.5"OD w/o Cage
10623-280	Stabilwax Cap. Column	30m, 0.25mm ID, 0.25um 4in star cage No guarantee for breakage
10623-364	Stabilwax Cap. Column	30m, 0.25mmID, 0.25um 5m, 0.25mmID Siltek guard column w/Siltek presstight

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



HROMalytic +61(0)3 9762 2034
ECHnology Pty Ltd

Australian Distributors
Importers & Manufacturers
www.chromtech.net.au

Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

[Ctrl F]
> Cat.#s

> Current System AUD Prices

