

10623-600	Stabilwax Cap. Column	30m, 0.25mm ID, 0.25um Pack of 6
10623-6850	Stabilwax Cap. Column	30m, 0.25mm ID, 0.25um 5" Cage for
10624	Stabilwax Cap. Column	30m, 0.32mm ID, 0.25um
10624-106	Stabilwax Cap. Column	25m, 0.32mm ID, 0.25um
10624-125	Stabilwax Cap. Column	30m, 0.32mm ID, 0.25um with 5m Integra-Guard Column
10624-128	Stabilwax Cap. Column	30m, 0.32mm ID, 0.25um with 10m Integra-Guard Column
10624-600	Stabilwax Cap. Column	30m, 0.32mm ID, 0.25um Pack of 6
10624-6850	Stabilwax Cap. Column	30m, 0.32mm ID, 0.25um 5" Cage
10625	Stabilwax Cap. Column	30m, 0.53mm ID, 0.25um
10625-051	Stabilwax Cap. Column	30m, 0.53mm ID, 0.25um No Cage
10625-126	Stabilwax Cap. Column	30m, 0.53mm ID, 0.25um with 5m Integra-Guard Column
10626	Stabilwax Cap. Column	60m, 0.25mm ID, 0.25um
10626-105	Stabilwax Cap. Column	50m, 0.25mm ID, 0.25um
10626-124	Stabilwax Cap. Column	60m, 0.25mm ID, 0.25um with 5m INTEGRA guard
10626-127	Stabilwax Cap. Column	60m, 0.25mm ID, 0.25um with 10 meter Integra Guard Column
10626-600	Stabilwax Cap. Column	60m, 0.25mm ID, 0.25um Pack of 6
10626-6850	Stabilwax Cap. Column	60m, 0.25mm ID, 0.25um 5" Cage for HP 6850
10627	Stabilwax Cap. Column	60m, 0.32mm ID, 0.25um
10627-105	Stabilwax Cap. Column	50m, 0.32mm ID, 0.25um
10627-109	Stabilwax Cap. Column	50m, 0.32mm ID 0.25um
10627-109685	Stabilwax Cap. Column	50m, 0.32mm ID, 0.25um For HP 6850
10627-125	Stabilwax Cap. Column	60m, 0.32mm ID, 0.25um with 5m Integra Guard Column
10627-128	Stabilwax Cap. Column	60m, 0.32mm ID, 0.25um w/10m 0.32mm Integra Guard
10628	Stabilwax Cap. Column	60m, 0.53mm ID, 0.25um
10635	Stabilwax Cap. Column	15m, 0.25mm ID, 0.50um
10635-104	Stabilwax Cap. Column	3 x 5m, 0.25mm ID, 0.50um
10635-124	Stabilwax Cap. Column	15m, 0.25mm ID, 0.50um with 5m Integra-Guard Column
10636	Stabilwax Cap. Column	15m, 0.32mm ID, 0.50um
10636-104	Stabilwax Cap. Column	3 x 5m, 0.32mm ID, 0.50um
10636-125	Stabilwax Cap. Column	15m, 0.32mm ID, 0.50um with 5m Integra-Guard Column
10636-280	Stabilwax Cap. Column	15m, 0.32mm ID, 0.50um 4" Star Cage - No Guarantee for Breakage
10636-391	Stabilwax Cap. Column	15m, 0.32mm ID, 0.50um 7cm Diameter, No Cage, No Guarantee for Breakage
10636-6850	Stabilwax Cap. Column	15m, 0.32mm ID, 0.50um on a 5" Agilent 6850 Cage
10637	Stabilwax Cap. Column	15m, 0.53mm ID, 0.50um
10637-6850	Stabilwax Cap. Column	15m, 0.53mm ID, 0.50um w/5" HP6850 Cage
10638	Stabilwax Cap. Column	30m, 0.25mm ID, 0.50um
10638-042	Stabilwax Cap. Column	30m, 0.25mm ID, 0.50um Nordion Cage
10638-124	Stabilwax Cap. Column	30m, 0.25mm ID, 0.50um with 5m Integra-Guard Column
10638-124685	Stabilwax Cap. Column	30m, 0.25mm ID, 0.50um w/ 5m Integra-Guard Column For HP 6850 GCs
10638-127	Stabilwax Cap. Column	30m, 0.25mm ID, 0.50um with 10 meter Integra Guard Column
10638-273	Stabilwax Cap. Column	30m, 0.25mm ID, 0.50um 3.5"OD w/o Cage
10638-6850	Stabilwax Cap. Column	30m, 0.25mm ID, 0.50um For HP 6850s
10639	Stabilwax Cap. Column	30m, 0.32mm ID, 0.50um
10639-101	Stabilwax Cap. Column	(3) 10m, 0.33mm ID, 0.50um
10639-106	Stabilwax Cap. Column	25m, 0.32mm ID, 0.50um
10639-122	Stabilwax Cap. Column	15m & 10m, 0.32mm ID, 0.50um
10639-125	Stabilwax Cap. Column	30m, 0.32mm ID, 0.50um with 5m Integra-Guard Column
10639-128	Stabilwax Cap. Column	30m, 0.32mm ID, 0.50um with 10m Integra-Guard Column
10639-282	Stabilwax Cap. Column	30m, 0.32mm ID, 0.50um 5" Diameter Star Cage No Guarantee for Breakage
10639-600	Stabilwax Cap. Column	30m, 0.32mm ID, 0.50um 6pk
10639-6850	Stabilwax Cap. Column	30m, 0.32mm ID, 0.50um 5" Cage for HP 6850
10640	Stabilwax Cap. Column	30m, 0.53mm ID, 0.50um
10640-106	Stabilwax Cap. Column	25m, 0.53mm ID, 0.50um
10640-126	Stabilwax Cap. Column	30m, 0.53mm ID, 0.50um with 5m Integra-Guard Column
10640-129	Stabilwax Cap. Column	30m, 0.53mm ID, 0.50um with 10m Integra-Guard Column
10641	Stabilwax Cap. Column	60m, 0.25mm ID, 0.50um
10641-105	Stabilwax Cap. Column	50m, 0.25mm ID, 0.50um
10641-124	Stabilwax Cap. Column	60m, 0.25mm ID, 0.50um with 5m Integra Guard Column
10641-127	Stabilwax Cap. Column	60m, 0.25mm ID, 0.50um with 10m Integra Guard Column
10641-6850	Stabilwax Cap. Column	60m, 0.25mm ID, 0.50um 5" cage for HP 6850
10642	Stabilwax Cap. Column	60m, 0.32mm ID, 0.50um
10642-105	Stabilwax Cap. Column	50m, 0.32mm ID, 0.50um
10642-125	Stabilwax Cap. Column	60m, 0.32mm ID, 0.50um with 5m Integra-Guard Column
10642-128	Stabilwax Cap. Column	60m, 0.32mm ID, 0.50um with 10m Integra-Guard Column
10642-600	Stabilwax Cap. Column	60m, 0.32mm ID, 0.50um 6pk
10642-6850	Stabilwax Cap. Column	60m, 0.32mm ID, 0.50um 5" cage for HP 6850

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



HROMalytic +61(0)3 9762 2034
ECHnology Pty Ltd

Australian Distributors
 Importers & Manufacturers
www.chromtech.net.au

Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

(Ctrl F)
> Cat.#s

> **Current System AUD Prices**

