

10643	Stabilwax Cap. Column	60m, 0.53mm ID, 0.50um
10643-105	Stabilwax Cap. Column	50m, 0.53mm ID, 0.5um
10651	Stabilwax Cap. Column	15m, 0.32mm ID, 1.00um
10651-051	Stabilwax Cap. Column	15m, 0.32mm ID, 1.0um No Cage, No Guarantee for Breakage
10651-107	Stabilwax Cap. Column	10m, 0.32mm ID, 1.00um
10651-125	Stabilwax Cap. Column	15m, 0.32mm ID, 1.00um with 5m Integra-Guard Column
10651-6850	Stabilwax Cap. Column	15m, 0.32mm ID, 1.00um 5" Cage for HP6850
10652	Stabilwax Cap. Column	15m, 0.53mm ID, 1.00um
10652-104	Stabilwax Cap. Column	3 x 5m, 0.53mm ID, 1.00um
10652-107	Stabilwax Cap. Column	10m, 0.53mm ID, 1.00um
10652-126	Stabilwax Cap. Column	15m, 0.53mm ID, 1.00um w/5m Integra-Guard Column
10652-280	Stabilwax Cap. Column	15m, 0.53mm ID, 1.00um 4" Coil (Star Cage) No Guarantee for Breakage
10652-289	Stabilwax Cap. Column	15m, 0.53mm ID, 1.00um 4.5" Coil
10652-6850	Stabilwax Cap. Column	15m, 0.53mm ID, 1.00um 5" HP 6850 Cage
10654	Stabilwax Cap. Column	30m, 0.32mm ID, 1.00um
10654-101	Stabilwax Cap. Column	3 x 10m, 0.32mm ID, 1.00um
10654-102	Stabilwax Cap. Column	10m & 20m, 0.32mm ID, 1.00um
10654-125	Stabilwax Cap. Column	30m, 0.32mm ID, 1.00um with 5m Integra-Guard Column
10654-1256850	Stabilwax Cap. Column	30m, 0.32mm ID, 1.00um w/ 5m Integra-Guard Column For HP 6850 GCs
10654-128	Stabilwax Cap. Column	30m, 0.32mm ID, 1.00um with 10m Integra-Guard Column
10654-600	Stabilwax Cap. Column	30m, 0.32mm ID, 1.00um Package of 6
10654-6006850	Stabilwax Cap. Column	30m, 0.32mm ID, 1.00um Pack of 6 5" cage for HP 6850
10654-6850	Stabilwax Cap. Column	30m, 0.32mm ID, 1.00um on 6850 Cage
10655	Stabilwax Cap. Column	30m, 0.53mm ID, 1.00um
10655-101	Stabilwax Cap. Column	3 x 10m, 0.53mm ID, 1.00um
10655-102	Stabilwax Cap. Column	10m & 20m, 0.53mm ID, 1.00um
10655-106	Stabilwax Cap. Column	25m, 0.53mm ID, 1.00um
10655-112	Stabilwax Cap. Column	20m, 0.53mm ID, 1.00um
10655-126	Stabilwax Cap. Column	30m, 0.53mm ID, 1.00um with 5m Integra-Guard Column
10655-1266850	Stabilwax Cap. Column	30m, 0.53mm ID, 1.00um w/5m Integra Guard, 5" HP6850 Cage
10655-129	Stabilwax Cap. Column	30m, 0.53mm ID, 1.00um with 10m Integra-Guard Column
10655-144	Stabilwax Cap. Column	5m & 25m, 0.53mm ID, 1.00um
10655-289	Stabilwax Cap. Column	30m, 0.53mm ID, 1.00um
10655-600	Stabilwax Cap. Column	30m, 0.53mm ID, 1.00um Package of 6
10655-6850	Stabilwax Cap. Column	30m, 0.53mm ID, 1.0um on a 6850 cage
10655-68506850	Stabilwax Cap. Column	30m, 0.53mm ID, 1.0um For 6850 GCs, 6pk
10657	Stabilwax Cap. Column	60m, 0.32mm ID, 1.00um
10657-105	Stabilwax Cap. Column	50m, 0.32mm ID, 1.00um
10657-125	Stabilwax Cap. Column	60m, 0.32mm ID, 1.00um with 5m Integra-Guard Column
10657-128	Stabilwax Cap. Column	60m, 0.32mm ID, 1.00um with 10m Integra-Guard Column
10657-600	Stabilwax Cap. Column	60m, 0.32mm ID, 1.00um Pack of 6
10657-6850	Stabilwax Cap. Column	60m, 0.32mm ID, 1.00um 5" HP 6850 Cage
10658	Stabilwax Cap. Column	60m, 0.53mm ID, 1.00um
10658-105	Stabilwax Cap. Column	50m, 0.53mm ID, 1.00um
10658-120	Stabilwax Cap. Column	10m, 20m, 30m, 0.53mm ID, 1.00um
10658-126	Stabilwax Cap. Column	60m, 0.53mm ID, 1.00um with 5m Integra-Guard Column
10658-129	Stabilwax Cap. Column	60m, 0.53mm ID, 1.00um with 10m Integra-Guard Column
10658-305	Stabilwax Cap. Column	60m, 0.53mm ID, 1.00um w/5m x 0.53mm ID Guard Column Presstight with glue
10658-6850	Stabilwax Cap. Column	60m, 0.53mm ID, 1.00um 5" Cage for HP6850
10666	Stabilwax Cap. Column	15m, 0.53mm ID, 1.50um
10666-107	Stabilwax Cap. Column	10m, 0.53mm ID, 1.50um
10666-126	Stabilwax Cap. Column	15m, 0.53mm ID, 1.5um w/5m 0.53mm Integra Guard
10666-129	Stabilwax Cap. Column	15m, 0.53mm ID, 1.50um 10m, 0.53mm ID Integra Guard
10666-305	Stabilwax Cap. Column	15m, 0.53mm ID, 1.50um w/5m x 0.53mm ID Guard Column Presstight with glue
10666-306	Stabilwax Cap. Column	15m, 0.53mm ID, 1.50um 10m, 0.53mm ID Guard Column w/Presstight
10667	Stabilwax Cap. Column	15m, 0.53mm ID, 2.00um
10667-107	Stabilwax Cap. Column	10m, 0.53mm ID, 2.00um
10667-126	Stabilwax Cap. Column	15m, 0.53mm ID, 2.00um with 5m Integra-Guard Column
10667-289	Stabilwax Cap. Column	15m, 0.53mm ID, 2.00um 4.5"Dia.Coil/No Cage
10669	Stabilwax Cap. Column	30m, 0.53mm ID, 1.50um
10669-042	Stabilwax Cap. Column	30m, 0.53mm ID, 1.50um 5" Nordion Cage
10669-126	Stabilwax Cap. Column	30m, 0.53mm ID, 1.50um with 5m Integra-Guard Column
10669-600	Stabilwax Cap. Column	30m, 0.53mm ID, 1.50um 6pk
10669-6850	Stabilwax Cap. Column	30m, 0.53mm ID, 1.50um 5" Cage for HP 6850
10670	Stabilwax Cap. Column	30m, 0.53mm ID, 2.00um
10670-106	Stabilwax Cap. Column	25m, 0.53mm ID, 2.00um

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



HROMalytic +61(0)3 9762 2034
ECHnology Pty Ltd

Australian Distributors
 Importers & Manufacturers
www.chromtech.net.au

Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

(Ctrl F)
> Cat.#s

> Current System AUD Prices

