

10670-112	Stabilwax Cap. Column
10670-126	Stabilwax Cap. Column
10670-12668	Stabilwax Cap. Column
10670-129	Stabilwax Cap. Column
10670-12968	Stabilwax Cap. Column
10670-600	Stabilwax Cap. Column
10670-6850	Stabilwax Cap. Column
10672	Stabilwax Cap. Column
10672-126	Stabilwax Cap. Column
10672-129	Stabilwax Cap. Column
10672-6850	Stabilwax Cap. Column
10705	Rtx-2330 Cap. Column
10705-6850	Rtx-2330 Cap. Column
10706	Rtx-2330 Cap. Column
10707	Rtx-2330 Cap. Column
10708	Rtx-2330 Cap. Column
10708-6850	Rtx-2330 Cap. Column
10709	Rtx-2330 Cap. Column
10710	Rtx-2330 Cap. Column
10711	Rtx-2330 Cap. Column
10711-003	Rtx-2330 Cap. Column
10711-00360	Rtx-2330 Cap. Column
10711-600	Rtx-2330 Cap. Column
10712	Rtx-2330 Cap. Column
10713	Rtx-2330 Cap. Column
10714	Rtx-2330 Cap. Column
10715	Rtx-2330 Cap. Column
10720	Rtx-2330 Cap. Column
10721	Rtx-2330 Cap. Column
10722	Rtx-2330 Cap. Column
10723	Rtx-2330 Cap. Column
10723-6850	Rtx-2330 Cap. Column
10724	Rtx-2330 Cap. Column
10724-031	Rtx-2330 Cap. Column
10724-6850	Rtx-2330 Cap. Column
10725	Rtx-2330 Cap. Column
10726	Rtx-2330 Cap. Column
10726-105	Rtx-2330 Cap. Column
10726-303	Rtx-2330 Cap. Column
10726-309	Rtx-2330 Cap. Column
10726-6850	Rtx-2330 Cap. Column
10727	Rtx-2330 Cap. Column
10727-280	Rtx-2330 Cap. Column
10727-6850	Rtx-2330 Cap. Column
10728	Rtx-2330 Cap. Column
10729	Rtx-2330 Cap. Column
10729-303	Rtx-2330 Cap. Column
10729-6850	Rtx-2330 Cap. Column
10730	Rtx-2330 Cap. Column
10730-6850	Rtx-2330 Cap. Column
10750	Stx-500 Cap. Column
10750-102	Stx-500 Cap. Column
10751	Stx-500 Cap. Column
10755	Rtx-Dioxin Cap. Column
10758	Rtx-Dioxin2 Cap. Column
10758-600	Rtx-Dioxin2 Cap. Column
10759	Rtx-Dioxin2 Cap. Column
10820	Stabilwax-DB Cap. Column
10820-6850	Stabilwax-DB Cap. Column
10821	Stabilwax-DB Cap. Column
10821-600	Stabilwax-DB Cap. Column
10823	Stabilwax-DB Cap. Column
10823-6850	Stabilwax-DB Cap. Column
10824	Stabilwax-DB Cap. Column
10827	Stabilwax DB Cap Column
10838	Stabilwax-DB Cap. Column

20m, 0.53mm ID, 2.00um
30m, 0.53mm ID, 2.00um with 5m Integra Guard Column
30m, 0.53mm ID, 2.00um w/5m Integra Guard Column
30m, 0.53mm ID, 2.00um with 10m Integra Guard Column
30m, 0.53mm ID, 2.00um w/10m Integra Guard, 5"/HP6850 Cage
30m, 0.53mm ID, 2.00um Pack of 6
30m, 0.53mm ID, 2.00um 5" HP 6850 Cage
60m, 0.53mm ID, 1.50um
60m, 0.53mm ID, 1.5um w/5m 0.53mm Integra Guard
60m, 0.53mm ID, 1.5um w/10m 0.53mm Integra Guard
60m, 0.53mm ID, 1.50um 5" HP 6850 Cage
15m, 0.25mm ID, 0.10um
15m, 0.25mm ID, 0.10um w/5" HP6850 Cage
15m, 0.32mm ID, 0.10um
15m, 0.53mm ID, 0.10um
30m, 0.25mm ID, 0.10um
30m, 0.25mm ID, 0.10um 5" Cage for HP6850
30m, 0.32mm ID, 0.10um
30m, 0.53mm ID, 0.10um
60m, 0.25mm ID, 0.10um
60m, 0.25mm ID, 0.10um For use with Dioxins
60m, 0.25mm ID, 0.10um 6pk For use with Dioxins
60m, 0.25mm ID, 0.10um 6pk
60m, 0.32mm ID, 0.10um
60m, 0.53mm ID, 0.10um
105m, 0.25mm ID, 0.10um
105m, 0.32mm ID, 0.10um
15m, 0.25mm ID, 0.20um
15m, 0.32mm ID, 0.20um
15m, 0.53mm ID, 0.20um
30m, 0.25mm ID, 0.20um
30m, 0.25mm ID, 0.20um 5" HP6850 Cage
30m, 0.32mm ID, 0.20um
30m, 0.32mm ID, 0.20um Cage column in customers cage.
30m, 0.32mmID, 0.20um 5" Cage for HP6850
30m, 0.53mm ID, 0.20um
60m, 0.25mm ID, 0.20um
50m, 0.25mm ID, 0.20um
60m, 0.25mm ID, 0.20um w/5m x 0.25mm ID Guard Column
60m, 0.25mmID, 0.20um w/10m 0.25mm Presstight Guard Col.
60m, 0.25mmID, 0.20um 5" cage for HP 6850
60m, 0.32mm ID, 0.20um
60m, 0.32mm ID, 0.20um 4" star cage No guarantee for breakage
60m, 0.32mm ID, 0.20um 5" HP6850 Cage
60m, 0.53mm ID, 0.20um
105m, 0.25mm ID, 0.20um
105m, 0.25mm ID, 0.20um w/5m x 0.25mm ID Guard Column Presstight with glue
105m, 0.25mmID, 0.20um 5" cage for HP 6850
105m, 0.32mm ID, 0.20um
105m, 0.32mm ID, 0.20um 5in cage for 6850
30m, 0.25mm ID, 0.15um (formally Rtx-500)
10m and 20m, 0.25mm ID, 0.15um (formerly Rtx-500)
60m, 0.25mm ID, 0.15um (formally Rtx-500)
60m, 0.25mm ID, 0.15um
60m, 0.25mm ID, 0.25um
60m, 0.25mm ID, 0.25um Pack of 6
40m, 0.18mm ID, 0.18um
15m, 0.25mm ID, 0.25um
15m, 0.25mm ID, 0.25um w/5" HP6850 Cage
15m, 0.32mm ID, 0.25um
15m, 0.32mm ID, 0.25um Pack of 6
30m, 0.25mm ID, 0.25um
30m, 0.25mm ID, 0.25um 5" Cage for HP 6850
30m, 0.32mm ID, 0.25um
60m, 0.32mm ID, 0.25um
30m, 0.25mm ID, 0.50um

(Ctrl F)
> Cat.#s



> Current System AUD Prices