

10838-6850	Stabilwax-DB Cap. Column	30m, 0.25mm ID, 0.50um For HP 685
10839	Stabilwax-DB Cap. Column	30m, 0.32mm ID, 0.50um
10839-304	Stabilwax-DB Cap. Column	30m, 0.32mm ID, 0.50um
10839-316	Stabilwax-DB Cap. Column	30m, 0.32mm ID, 0.50um w/5m x 0.32mm ID Polar Deact Guard Col Presstight wi
10840	Stabilwax-DB Cap. Column	30m, 0.53mm ID, 0.50um
10851	Stabilwax-DB Cap. Column	15m, 0.32mm ID, 1.00um
10851-600	Stabilwax-DB Cap. Column	15m, 0.32mm ID, 1.00um Pack of 6
10852	Stabilwax-DB Cap. Column	15m, 0.53mm ID, 1.00um
10852-600	Stabilwax-DB Cap. Column	15m, 0.53mm ID, 1.00um Pack of 6
10854	Stabilwax-DB Cap. Column	30m, 0.32mm ID, 1.00um
10854-031	Stabilwax-DB Cap. Column	30m, 0.32mm ID, 1.00um Cage column in customers cage.
10854-6850	Stabilwax-DB Cap. Column	30m, 0.32mm ID, 1.00um 5" Cage
10855	Stabilwax-DB Cap. Column	30m, 0.53mm ID, 1.00um
10855-051	Stabilwax-DB Cap. Column	30m, 0.53mm ID, 1.00um No Cage No guarantee for breakage
10855-600	Stabilwax-DB Cap. Column	30m, 0.53mm ID, 1.00um Pack of 6
10855-6850	Stabilwax-DB Cap. Column	30m, 0.53mm ID, 1.00um 5" HP6850 Cage
10857	Stabilwax-DB Cap. Column	60m, 0.32mm ID, 1.00um
10857-105	Stabilwax-DB Cap. Column	50m, 0.32mm ID, 1.00um
10857-6850	Stabilwax-DB Cap. Column	60m, 0.32mm ID, 1.00um For HP 6850 GCs
10858	Stabilwax-DB Cap. Column	60m, 0.53mm ID, 1.00um
10858-6850	Stabilwax-DB Cap. Column	60m, 0.53mm ID, 1.00 5in cage for HP 6850
10869	Stabilwax-DB Cap. Column	30m, 0.53mm ID, 1.50um
10869-111	Stabilwax-DB Cap. Column	2 x 15m, 0.53mm ID, 1.50um
10900	Rtx-Volatiles Cap. Column	30m, 0.25mm ID, 1.00um
10900-124	Rtx-Volatiles Cap. Column	30m, 0.25mm ID, 1.00um with 5m, 0.25mm Integra Guard
10900-600	Rtx-Volatiles Cap. Column	30m, 0.25mm ID, 1.00um Pack of 6
10900-6850	Rtx-Volatiles Cap. Column	30m, 0.25mm ID, 1.00um 5" Cage for HP 6850 GCs
10901	Rtx-Volatiles Cap. Column	30m, 0.32mm ID, 1.50um
10901-102	Rtx-Volatiles Cap. Column	10m & 20m, 0.32mm ID, 1.50um
10901-111	Rtx-Volatiles Cap. Column	2 x 15m, 0.32mm ID, 1.50um
10901-128	Rtx-Volatiles Cap. Column	30m, 0.32mm ID, 1.50um 10, 0.32mm ID Guard
10901-6850	Rtx-Volatiles Cap. Column	30m, 0.32mm ID, 1.50um 5in cage for HP 6850
10902	Rtx-Volatiles Cap. Column	30m, 0.53mm ID, 2.00um
10902-051	Rtx-Volatiles Cap. Column	30m, 0.53mm ID, 2.00um No Cage, No Guarantee for Breakage
10902-102	Rtx-Volatiles Cap. Column	20m & 10m, 0.53mm ID, 2.00um
10902-111	Rtx-Volatiles Cap. Column	2-15m, 0.53mm ID, 2.00um
10902-112	Rtx-Volatiles Cap. Column	20m, 0.53mm ID, 2.00um
10902-126	Rtx-Volatiles Cap. Column	30m, 0.53mm ID, 2.00um with 5m Integra-Guard Column
10902-129	Rtx-Volatiles Cap. Column	30m, 0.53mm ID, 2.00um with 10m Integra-Guard Column
10902-130	Rtx-Volatiles Cap. Column	1x15m & 3x5m, 0.53mm ID, 2.00um
10903	Rtx-Volatiles Cap. Column	60m, 0.25mm ID, 1.00um
10903-124	Rtx-Volatiles Cap. Column	60m, 0.25mm ID, 1.00um with 5m Integra-Guard Column
10903-6850	Rtx-Volatiles Cap. Column	60m, 0.25mm ID, 1.00um 5in cage for HP 6850
10904	Rtx-Volatiles Cap. Column	60m, 0.32mm ID, 1.50um
10904-125	Rtx-Volatiles Cap. Column	60m, 0.32mm ID, 1.50um with 5m Integra-Guard Column
10904-128	Rtx-Volatiles Cap. Column	60m, 0.32mm ID, 1.50um with 10m Integra-Guard Column
10905	Rtx-Volatiles Cap. Column	60m, 0.53mm ID, 2.00um
10905-126	Rtx-Volatiles Cap. Column	60m, 0.53mm ID, 2.00um with 5m Integra-Guard Column
10905-129	Rtx-Volatiles Cap. Column	60m, 0.53mm ID, 2.00um with 10m Integra-Guard Column
10906	Rtx-Volatiles Cap. Column	105m, 0.53mm ID, 2.00um
10906-124	Rtx-Volatiles Cap. Column	105m, 0.53mm ID, 2.00um with 5m Integra-Guard Column
10908	Rtx-502.2 Cap. Column	30m, 0.53mm ID, 3.00um
10908-600	Rtx-502.2 Cap. Column	30m, 0.53mm ID, 3.0um Pack of 6
10908-6850	Rtx-502.2 Cap. Column	30m, 0.53mm ID, 3.0um 5" HP6850 Cage
10909	Rtx-502.2 Cap. Column	60m, 0.53mm ID, 3.00um
10909-600	Rtx-502.2 Cap. Column	60m, 0.53mm ID, 3.00um Package of 6
10909-6850	Rtx-502.2 Cap. Column	60m, 0.53mm ID, 3.00um 5" Cage for Agilent 6850
10910	Rtx-502.2 Cap. Column	105m, 0.53mm ID, 3.00um
10910-081	Rtx-502.2 Cap. Column	45m & 60m, 0.53mm ID, 3.00um
10910-305	Rtx-502.2 Cap. Column	105m, 0.53mm ID, 3.00um w/5m x 0.53mm ID Guard Column Presstight with glue
10910-600	Rtx-502.2 Cap. Column	105m, 0.53mm ID, 3.00um Pack of 6
10915	Rtx-502.2 Cap. Column	30m, 0.25mm ID, 1.40um
10915-6850	Rtx-502.2 Cap. Column	30m, 0.25mm ID 1.40um 5" HP 6850 Cage
10916	Rtx-502.2 Cap. Column	60m, 0.25mm ID, 1.40um
10916-600	Rtx-502.2 Cap. Column	60m, 0.25mm ID, 1.40um 6pk
10916-6850	Rtx-502.2 Cap. Column	60m, 0.25mm ID, 1.40um 5" cage for HP 6850

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



HROMalytic +61(0)3 9762 2034
ECHnology Pty Ltd

Australian Distributors
 Importers & Manufacturers
www.chromtech.net.au

Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

[Ctrl F]
 > Cat.#s

> Current System AUD Prices

