

10919	Rtx-502.2 Cap. Column
10919-304	Rtx-502.2 Cap. Column
10919-600	Rtx-502.2 Cap. Column
10919-6850	Rtx-502.2 Cap. Column
10920	Rtx-502.2 Cap. Column
10920-115	Rtx-502.2 Cap. Column
10920-304	Rtx-502.2 Cap. Column
10920-6850	Rtx-502.2 Cap. Column
10921	Rtx-502.2 Cap. Column
10921-365	Rtx-502.2 Cap. Column
10921-600	Rtx-502.2 Cap. Column
10921-6850	Rtx-502.2 Cap. Column
10921-68506	Rtx-502.2 Cap. Column
10968	Rtx-624 Cap. Column
10968-124	Rtx-624 Cap. Column
10968-12468	Rtx-624 Cap. Column
10968-127	Rtx-624 Cap. Column
10968-390	Rtx-624 Cap. Column
10968-6850	Rtx-624 Cap. Column
10969	Rtx-624 Cap. Column
10969-124	Rtx-624 Cap. Column
10969-127	Rtx-624 Cap. Column
10969-600	Rtx-624 Cap. Column
10969-6850	Rtx-624 Cap. Column
10970	Rtx-624 Cap. Column
10970-101	Rtx-624 Cap. Column
10970-125	Rtx-624 Cap. Column
10970-128	Rtx-624 Cap. Column
10970-12868	Rtx-624 Cap. Column
10970-282	Rtx-624 Cap. Column
10970-600	Rtx-624 Cap. Column
10970-6850	Rtx-624 Cap. Column
10971	Rtx-624 Cap. Column
10971-126	Rtx-624 Cap. Column
10971-12668	Rtx-624 Cap. Column
10971-129	Rtx-624 Cap. Column
10971-282	Rtx-624 Cap. Column
10971-305	Rtx-624 Cap. Column
10971-600	Rtx-624 Cap. Column
10971-6850	Rtx-624 Cap. Column
10972	Rtx-624 Cap. Column
10972-042	Rtx-624 Cap. Column
10972-105	Rtx-624 Cap. Column
10972-115	Rtx-624 Cap. Column
10972-125	Rtx-624 Cap. Column
10972-128	Rtx-624 Cap. Column
10972-6850	Rtx-624 Cap. Column
10973	Rtx-624 Cap. Column
10973-126	Rtx-624 Cap. Column
10973-129	Rtx-624 Cap. Column
10973-140	Rtx-624 Cap. Column
10973-6850	Rtx-624 Cap. Column
10974	Rtx-624 Cap. Column
10974-126	Rtx-624 Cap. Column
10974-129	Rtx-624 Cap. Column
10974-325	Rtx-624 Cap. Column
10974-600	Rtx-624 Cap. Column
10974-6850	Rtx-624 Cap. Column
10975	Rtx-624 Cap. Column
10975-306	Rtx-624 Cap. Column
10975-6850	Rtx-624 Cap. Column
10982	Rtx-624 Cap. Column
10986	Rtx-502.2 Cap. Column
10986-042	Rtx-502.2 Cap. Column
10986-311	Rtx-502.2 Cap. Column
10986-6850	Rtx-502.2 Cap. Column

30m, 0.32mm ID, 1.80um
30m, 0.32mm ID, 1.80um w/5m x 0.32mm ID Guard Column Presstight with glue
30m, 0.32mm ID, 1.80um 6pk
30m, 0.32mm ID, 1.80um For HP 6850s
60m, 0.32mm ID, 1.80um
20m & 40m 0.32mmID, 1.8um
60m, 0.32mm ID, 1.80um w/5m x 0.32mm ID Guard Column Presstight with glue
60m, 0.32mm ID, 1.80um 5in cage for HP 6850
105m, 0.32mm ID, 1.80um
105m, 0.32mmID, 1.80um 5m, 0.32mm Siltek guard column w/Siltek presstight
105m, 0.32mm ID, 1.80um Pack of 6
105m, 0.32mm ID, 1.80um w/5" Cage for HP 6850
105m, 0.32mm ID, 1.80um 5" cage for HP 6850 6pk
30m, 0.25mm ID, 1.40um
30m, 0.25mm ID, 1.40um with 5m Integra-Guard Column
30m, 0.25mm ID, 1.40um w/5m Integra-Guard Column, 5" Cage for HP6850 GCs
30m, 0.25mm ID, 1.40um 10m, 0.25mm Integra Guard
30m, 0.25mm ID, 1.40um 7cm Coil, No Cage No Guarantee for Breakage
30m, 0.25mm ID, 1.40um w/5" Cage for HP 6850
60m, 0.25mm ID, 1.40um
60m, 0.25mm ID, 1.40um with 5m Integra-Guard Column
60m, 0.25mm ID, 1.40um with 10 meter Integra Guard Column
60m, 0.25mm ID, 1.40um Pack of 6
60m, 0.25mm ID, 1.40um 5" cage for HP 6850 GC
30m, 0.32mm ID, 1.80um
30m, 0.32mm ID, 1.80um Break into 3x10m columns
30m, 0.32mm ID, 1.80um with 5m Integra Guard Column
30m, 0.32mm ID, 1.80um with 10m Integra Guard Column
30m, 0.32mm ID, 1.80um w/10m Integra Guard on a 5 Inch HP6850 Cage
30m, 0.32mm ID, 1.80um Use 5 inch Star Cage No Guarantee Against Breakage
30m, 0.32mm ID, 1.80um Pack of 6
30m, 0.32mm ID, 1.80um 5" HP 6850 Cage
30m, 0.53mm ID, 3.00um
30m, 0.53mm ID, 3.00um with 5m Integra-Guard Column
30m, 0.53mm ID, 3.00um with 5m Integra-Guard Column 5" HP 6850 Cage
30m, 0.53mm ID, 3.00um with 10m Integra-Guard Column
30m, 0.53mm ID, 3.00um 5" star cage No guarantee for breakage
30m, 0.53mm ID, 3.00um w/5m x 0.53mm ID Guard Column Presstight with glue
30m, 0.53mm ID, 3.00um Pack of 6
30m, 0.53mm ID, 3.0um w/5" HP6850 Cage
60m, 0.32mm ID, 1.80um
60m, 0.32mmID, 1.80um w/Nordion Cage
50m, 0.32mm ID, 1.80um
20m & 40m 0.32mmID, 1.8um
60m, 0.32mm ID, 1.80um with 5m Integra-Guard Column
60m, 0.32mm ID, 1.80um with 10m Integra-Guard Column
60m, 0.32mm ID, 1.80um 5" Cage for HP6850
60m, 0.53mm ID, 3.00um
60m, 0.53mm ID, 3.00um 5m, 0.53mm guard built in
60m, 0.53mm ID, 3.00um with 10m Integra-Guard Column
45m, 0.53mm ID, 3.00um
60m, 0.53mm ID, 3.0um 5" HP6850 Cage
75m, 0.53mm ID, 3.00um
75m, 0.53mm ID, 3.00um with 5m Integra-Guard Column
75m, 0.53mm ID, 3.00um with 10m Integra-Guard Column
75m, 0.53mm ID, 3.00um 5m Guard Column w/Cap Vu-Union
75m, 0.53mm ID, 3.00um 6pk
75m, 0.53mm ID, 3.00um w/5" HP6850 Cage
105m, 0.53mm ID, 3.00um
105m, 0.53mm ID, 3.00um w/10m 0.53mm PT Guard Column
105m, 0.53mm ID, 3.0um w/ 6850 cage
75m, 0.45mm ID, 2.55um
75m, 0.45mm ID, 2.55um
75m, 0.45mm ID, 2.55um Nordion Cage
75m, 0.45mm ID, 2.55um w/5m 0.45mm ID Guard Column connected with a Capil
75m, 0.45mm ID, 2.55um 5" cage for HP 6850

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



HROMalytic +61(0)3 9762 2034
ECHnology Pty Ltd

Australian Distributors
Importers & Manufacturers
www.chromtech.net.au

Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

