



10992	Rtx-1 Cap. Column	75m, 0.25mm ID, 2.55um
10998	Rt-TCEP Cap. Column	30m, 0.25mm ID, 0.40um
10999	Rt-TCEP Cap. Column	60m, 0.25mm ID, 0.40um
10999-105	Rt-TCEP Cap. Column	50m, 0.25mm ID, 0.40um
10999-6850	Rt-TCEP Cap. Column	60m, 0.25mm ID, 0.40um 5" cage for HP6850
11005	Stabilwax-DA Cap. Column	15m, 0.25mm ID, 0.10um
11005-6850	Stabilwax-DA Cap. Column	15m, 0.25mm ID, 0.10um 5" cage
11006	Stabilwax-DA Cap. Column	15m, 0.32mm ID, 0.10um
11007	Stabilwax-DA Cap. Column	15m, 0.53mm ID, 0.10um
11008	Stabilwax-DA Cap. Column	30m, 0.25mm ID, 0.10um
11008-6850	Stabilwax-DA Cap. Column	30m, 0.25mm ID, 0.10um 5in cage for HP 6850
11009	Stabilwax-DA Cap. Column	30m, 0.32mm ID, 0.10um
11010	Stabilwax-DA Cap. Column	30m, 0.53mm ID, 0.10um
11011	Stabilwax-DA Cap. Column	60m, 0.25mm ID, 0.10um
11012	Stabilwax-DA Cap. Column	60m, 0.32mm ID, 0.10um
11013	Stabilwax-DA Cap. Column	60m, 0.53mm ID, 0.10um
11020	Stabilwax-DA Cap. Column	15m, 0.25mm ID, 0.25um
11020-6850	Stabilwax-DA Cap. Column	15m, 0.25mm ID, 0.25um 5" Cage for HP6850 GCs
11021	Stabilwax-DA Cap. Column	15m, 0.32mm ID, 0.25um
11021-104	Stabilwax-DA Cap. Column	3 x 5m, 0.32mm ID, 0.25um
11021-6850	Stabilwax-DA Cap. Column	15m, 0.32mm ID, 0.25um 5" Cage for Agilent GCs
11022	Stabilwax-DA Cap. Column	15m, 0.53mm ID, 0.25um
11022-305	Stabilwax-DA Cap. Column	15m, 0.53mm ID, 0.25um 5m Guard Column w/Presstight
11023	Stabilwax-DA Cap. Column	30m, 0.25mm ID, 0.25um
11023-280	Stabilwax-DA Cap. Column	30m, 0.25mm ID, 0.25um Cage in 4 inch Star Cage
11023-303	Stabilwax-DA Cap. Column	30m, 0.25mm ID, 0.25um w/5m 0.25mm Presstight Guard Column
11023-600	Stabilwax-DA Cap. Column	30m, 0.25mm ID, 0.25um Pack of 6
11023-6850	Stabilwax-DA Cap. Column	30m, 0.25mm ID, 0.25um 5" Cage for HP6850
11024	Stabilwax-DA Cap. Column	30m, 0.32mm ID, 0.25um
11024-106	Stabilwax-DA Cap. Column	25m, 0.32mm ID, 0.25um
11024-600	Stabilwax-DA Cap. Column	30m, 0.32mm ID, 0.25um Pack of 6
11024-6850	Stabilwax-DA Cap. Column	30m, 0.32mm ID, 0.25um 5" HP6850 Cage
11025	Stabilwax-DA Cap. Column	30m, 0.53mm ID, 0.25um
11025-318	Stabilwax-DA Cap. Column	30m, 0.53mm ID, 0.25um w/15m x 0.53mm ID Polar Deact Guard Col Presstight v
11025-6850	Stabilwax-DA Cap. Column	30m, 0.53mm ID, 0.25um 5" Cage for HP6850
11026	Stabilwax-DA Cap. Column	60m, 0.25mm ID, 0.25um
11026-042	Stabilwax-DA Cap. Column	60m, 0.25mm ID, 0.25um Nordion Cage
11026-105	Stabilwax-DA Cap. Column	50m, 0.25mm ID, 0.25um
11027	Stabilwax-DA Cap. Column	60m, 0.32mm ID, 0.25um
11027-105	Stabilwax-DA Cap. Column	50m, 0.32mm ID, 0.25um
11028	Stabilwax-DA Cap. Column	60m, 0.53mm ID, 0.25um
11035	Stabilwax-DA Cap. Column	15m, 0.25mm ID, 0.50um
11035-6850	Stabilwax-DA Cap. Column	15m, 0.25mm ID, 0.50um 5" cage for HP 6850
11036	Stabilwax-DA Cap. Column	15m, 0.32mm ID, 0.50um
11036-107	Stabilwax-DA Cap. Column	10m, 0.32mm ID, 0.50um
11036-280	Stabilwax-DA Cap. Column	15m, 0.32mm ID, 0.50um 4" star cage no guarantee for breakage
11037	Stabilwax-DA Cap. Column	15m, 0.53mm ID, 0.50um
11037-107	Stabilwax-DA Cap. Column	10m, 0.53mm ID, 0.50um
11037-6850	Stabilwax-DA Cap. Column	15m, 0.53mm ID, 0.50um 5" Cage for HP
11038	Stabilwax-DA Cap. Column	30m, 0.25mm ID, 0.50um
11038-6850	Stabilwax-DA Cap. Column	30m, 0.25mm ID, 0.50um 5" Cage for HP 6850
11039	Stabilwax-DA Cap. Column	30m, 0.32mm ID, 0.50um
11039-6850	Stabilwax-DA Cap. Column	30m, 0.32mm ID, 0.50um 5" HP6850 Cage
11040	Stabilwax-DA Cap. Column	30m, 0.53mm ID, 0.50um
11040-102	Stabilwax-DA Cap. Column	10m & 20m 0.53mm ID, 0.50um
11040-6850	Stabilwax-DA Cap. Column	30m, 0.53mm ID, 0.50um 5" Cage for HP6850 GCs
11041	Stabilwax-DA Cap. Column	60m, 0.25mm ID, 0.50um
11041-303	Stabilwax-DA Cap. Column	60m, 0.25mm ID, 0.50um w/5m 0.25mm Guard Col. w/Presstight
11042	Stabilwax-DA Cap. Column	60m, 0.32mm ID, 0.50um
11042-105	Stabilwax-DA Cap. Column	50m, 0.32mm ID, 0.50um
11042-1056850	Stabilwax-DA Cap. Column	50m, 0.32mm ID, 0.50um 5in cage for HP 6850
11042-316	Stabilwax-DA Cap. Column	60m, 0.32mm ID, 0.50um w/5m, 0.32mm PT Polar Guard
11043	Stabilwax-DA Cap. Column	60m, 0.53mm ID, 0.50um
11043-105	Stabilwax-DA Cap. Column	50m, 0.53mm ID, 0.50um
11051	Stabilwax-DA Cap. Column	15m, 0.32mm ID, 1.00um
11051-107	Stabilwax-DA Cap. Column	10m, 0.32mm ID, 1.00um