

11052	Stabilwax-DA Cap. Column	15m, 0.53mm ID, 1.00um
11052-104	Stabilwax-DA Cap. Column	3-5m, 0.53mm ID, 1.00um
11052-107	Stabilwax-DA Cap. Column	10m, 0.53mm ID, 1.00um
11052-305	Stabilwax-DA Cap. Column	15m, 0.53mm ID, 1.00um w/5m, 0.53mm PT Guard Column
11052-6850	Stabilwax-DA Cap. Column	15m, 0.53mm ID, 1.00um For HP 6850 GCs
11054	Stabilwax-DA Cap. Column	30m, 0.32mm ID, 1.00um
11054-031	Stabilwax-DA Cap. Column	30m, 0.32mm ID, 1.00um Cage column in customers cage.
11054-600685	Stabilwax-DA Cap. Column	30m, 0.32mm ID, 1.00um Pack of 6 5" cage for HP 6850
11054-6850	Stabilwax-DA Cap. Column	30m, 0.32mm ID, 1.00um on 6850 Cage
11055	Stabilwax-DA Cap. Column	30m, 0.53mm ID, 1.00um
11055-101	Stabilwax-DA Cap. Column	3 x 10m, 0.53mm ID, 1.00um
11055-102	Stabilwax-DA Cap. Column	10m & 20m 0.53mm ID, 1.00um
11055-106	Stabilwax-DA Cap. Column	25m, 0.53mm ID, 1.00um
11055-289	Stabilwax-DA Cap. Column	30m, 0.53mm ID, 1.00um 4.5" Coil, No Cage
11055-305	Stabilwax-DA Cap. Column	30m, 0.53mm ID, 1.00um 5m, 0.53mm Presstight Guard Column
11055-6850	Stabilwax-DA Cap. Column	30m, 0.53mm ID, 1.00um 5" Cage for HP 6850
11057	Stabilwax-DA Cap. Column	60m, 0.32mm ID, 1.00um
11057-163	Stabilwax-DA Cap. Column	60m, 0.32mm ID, 1.00um 5m, 0.32mm Guard Column w/ Vu 2 Union
11057-6850	Stabilwax-DA Cap. Column	60m, 0.32mm ID, 1.00um 5" cage for 6850
11058	Stabilwax-DA Cap. Column	60m, 0.53mm ID, 1.00um
11058-138	Stabilwax-DA Cap. Column	45m & 15m, 0.53mm ID, 1.00um
11058-6850	Stabilwax-DA Cap. Column	60m, 0.53mm ID, 1.00um 5" Cage for HP6850
11062	Stabilwax-DA Cap. Column	15m, 0.53mm ID, 1.50um
11062-107	Stabilwax-DA Cap. Column	10m, 0.53mm ID, 1.50um
11065	Stabilwax-DA Cap. Column	30m, 0.53mm ID, 1.50um
11065-600	Stabilwax-DA Cap. Column	30m, 0.53mm ID, 1.50um Pack of 6
11065-6850	Stabilwax-DA Cap. Column	30m, 0.53mm ID, 1.50um 5" Cage for HP6850
11068	Stabilwax-DA Cap. Column	60m, 0.53mm ID, 1.50um
11120	Rtx-CLP Cap. Column	15m, 0.25mm ID, 0.25um
11120-364	Rtx-CLP Cap. Column	15m, 0.25mm ID, 0.25um 5m, 0.25mm ID Siltek guard column w/Siltek presstight
11123	Rtx-CLP Cap. Column	30m, 0.25mm ID, 0.25um
11123-600	Rtx-CLP Cap. Column	30m, 0.25mm ID, 0.25um Pack of 6
11123-6850	Rtx-CLP Cap. Column	30m, 0.25mm ID, 0.25um For HP 6850 GCs
11126	Rtx-CLP Cap. Column	60m, 0.25mm ID, 0.25um
11136	Rtx-CLP Cap. Column	15m, 0.32mm ID, 0.50um
11136-107	Rtx-CLP Cap. Column	10m, 0.32mm ID, 0.50um
11136-600	Rtx-CLP Cap. Column	15m, 0.32mm ID, 0.50um Pack of 6
11137	Rtx-CLP Cap. Column	15m, 0.53mm ID, 0.50um
11139	Rtx-CLP Cap. Column	30m, 0.32mm ID, 0.50um
11139-304	Rtx-CLP I Cap. Column	30m, 0.32mm ID, 0.50um w/5m x 0.32mm ID Guard Column Presstight with glue
11139-365	Rtx-CLP Cap. Column	30m, 0.32mm ID, 0.50um w/5m, 0.32mm ID Siltek guard column w/Siltek presstight
11139-600	Rtx-CLP Cap. Column	30m, 0.32mm ID, 0.50um Pack of 6
11139-6850	Rtx-CLP Cap. Column	30m, 0.32mm ID, 0.50um 5" cage for HP 6850
11140	Rtx-CLP Cap. Column	30m, 0.53mm ID, 0.50um
11140-282	Rtx-CLP Cap. Column	30m, 0.53mm ID, 0.50um recoil into 5" Star cage
11140-366	Rtx-CLP Cap. Column	30m, 0.53mm ID, 0.50um w/5m 0.53mm Siltek Guard Column w/Presstight
11140-600	Rtx-CLP Cap. Column	30m, 0.53mm ID, 0.50um Pack of 6
11140-6850	Rtx-CLP Cap. Column	30m, 0.53mm ID, 0.50um 5" HP6850 Cage
11141	Rtx-CLP Cap. Column	30m, 0.32mm ID, 0.32um
11141-163	Rtx-CLP Cap. Column	30m, 0.32mm ID, 0.32um 5m, 0.32mm ID, Guard w/Vu 2 Union
11141-280	Rtx-CLP Cap. Column	30m, 0.32mm ID, 0.32um 4in star cage No guarantee for breakage
11141-600	Rtx-CLP Cap. Column	30m, 0.32mm ID, 0.32um Pack of 6
11190	Stx-CLP Cap. Column Kit	0.25mm ID Kit Includes 1 ea: 11543/11443/10026 w/Angled Y Presstight
11191	Stx-CLP Cap. Column Kit	0.32mm ID 11544/11444 /10027 With Angled Y Presstight Connector
11191-600	Stx-CLP Cap. Column Kit	Pack of 6 0.32mm ID Kits 11544/11444/10027 w/Angled Y Presstight Connector
11193	Stx-CLP Cap. Column Kit	0.32mm ID Kit Includes 1 ea: 11546/11444/10027, w/Angled Y Presstight
11196	Rtx-CLP Cap. Column Kit	0.32mm ID 11141/11324/10027 w/Angled Y Presstight
11196-496	Rtx-CLP Cap. Column Kit	0.32mm ID 11141/11324/10027 Connected with Angled Y Presstight
11197	Rtx-CLP Cap. Column Kit	0.53mm ID 11140/11340/10045 w/Angled Y Presstight
11197-496	Rtx-CLP Cap. Column	Y connect 11140/11340/10028 w/Angled Y Presstight
11198	Rtx-CLP Cap. Column Kit	11139/11324/10027 w/Angled Y Presstight
11198-495	Rtx-CLP Cap. Column	Kit, 11139, 11324, 10027 Connected w/a Y Vu-Union
11198-496	Rtx-CLP Cap. Column	Kit 11139/11324/10027 Connected w/Angled Y Presstight
11198-530	Rtx-CLP Cap. Column	Kit 11139/11324/10027 with Pesticide Mix AB#1 w/Angled Y Presstight
11198-535	Rtx-CLP Cap. Column	Kit 11139/11324/10027 with Pesticide Mix AB#2 w/Angled Y Presstight
11199	Rtx-CLP Cap. Column Kit	0.25mm ID 11123/11323/10026 w/Angled Y Presstight

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



**HROMalytic** +61(0)3 9762 2034  
**ECHnology** Pty Ltd  
 Website NEW : [www.chromalytic.net.au](http://www.chromalytic.net.au) E-mail : [info@chromtech.net.au](mailto:info@chromtech.net.au) Tel: 03 9762 2034 . . . in AUSTRALIA

**Australian Distributors**  
 Importers & Manufacturers  
[www.chromtech.net.au](http://www.chromtech.net.au)

[Ctrl F]  
> Cat.#s

> Current System AUD Prices

