

12038-6850	Rtx-1701	Cap. Column
12039	Rtx-1701	Cap. Column
12039-106	Rtx-1701	Cap. Column
12039-125	Rtx-1701	Cap. Column
12039-128	Rtx-1701	Cap. Column
12039-128685	Rtx-1701	Cap. Column
12039-6850	Rtx-1701	Cap. Column
12040	Rtx-1701	Cap. Column
12040-126	Rtx-1701	Cap. Column
12040-129	Rtx-1701	Cap. Column
12041	Rtx-1701	Cap. Column
12042	Rtx-1701	Cap. Column
12042-125	Rtx-1701	Cap. Column
12042-6850	Rtx-1701	Cap. Column
12043	Rtx-1701	Cap. Column
12044	Rtx-1701	Cap. Column
12045	Rtx-1701	Cap. Column
12050	Rtx-1701	Cap. Column
12050-124	Rtx-1701	Cap. Column
12051	Rtx-1701	Cap. Column
12051-051	Rtx-1701	Cap. Column
12051-600	Rtx-1701	Cap. Column
12052	Rtx-1701	Cap. Column
12052-126	Rtx-1701	Cap. Column
12052-6850	Rtx-1701	Cap. Column
12053	Rtx-1701	Cap. Column
12053-124	Rtx-1701	Cap. Column
12053-600	Rtx-1701	Cap. Column
12053-6850	Rtx-1701	Cap. Column
12054	Rtx-1701	Cap. Column
12054-031	Rtx-1701	Cap. Column
12054-125	Rtx-1701	Cap. Column
12054-128	Rtx-1701	Cap. Column
12054-600	Rtx-1701	Cap. Column
12054-6850	Rtx-1701	Cap. Column
12054-68506	Rtx-1701	Cap. Column
12055	Rtx-1701	Cap. Column
12055-126	Rtx-1701	Cap. Column
12055-129	Rtx-1701	Cap. Column
12055-6850	Rtx-1701	Cap. Column
12056	Rtx-1701	Cap. Column
12056-124	Rtx-1701	Cap. Column
12056-127	Rtx-1701	Cap. Column
12056-6850	Rtx-1701	Cap. Column
12057	Rtx-1701	Cap. Column
12057-105	Rtx-1701	Cap. Column
12057-125	Rtx-1701	Cap. Column
12057-6850	Rtx-1701	Cap. Column
12058	Rtx-1701	Cap. Column
12058-105	Rtx-1701	Cap. Column
12058-126	Rtx-1701	Cap. Column
12058-305	Rtx-1701	Cap. Column
12058-6850	Rtx-1701	Cap. Column
12059	Rtx-1701	Cap. Column
12060	Rtx-1701	Cap. Column
12060-6850	Rtx-1701	Cap. Column
12066	Rtx-1701	Cap. Column
12067	Rtx-1701	Cap. Column
12067-104	Rtx-1701	Cap. Column
12069	Rtx-1701	Cap. Column
12069-125	Rtx-1701	Cap. Column
12069-125685	Rtx-1701	Cap. Column
12069-6850	Rtx-1701	Cap. Column
12070	Rtx-1701	Cap. Column
12070-126	Rtx-1701	Cap. Column
12070-600	Rtx-1701	Cap. Column

30m, 0.25mm ID, 0.50um 5in cage for
30m, 0.32mm ID, 0.50um
25m, 0.32mm ID, 0.50um
30m, 0.32mm ID, 0.50um with 5m Integra-Guard Column
30m, 0.32mm ID, 0.50um with 10m Integra-Guard Column
30m, 0.32mm ID, 0.50um w/10m Integra-Guard Column 5" cage for HP6850
30m, 0.32mm ID, 0.50um 5" HP6850 Cage
30m, 0.53mm ID, 0.50um
30m, 0.53mm ID, 0.50um with 5m Integra-Guard Column
30m, 0.53mm ID, 0.50um with 10m Integra-Guard Column
60m, 0.25mm ID, 0.50um
60m, 0.32mm ID, 0.50um
60m, 0.32mm ID, 0.50um w/5m, 0.32mm Integra Guard
60m, 0.32mm ID, 0.50um 5" Cage for HP 6850
60m, 0.53mm ID, 0.50um
105m, 0.25mm ID, 0.50um
105m, 0.32mm ID, 0.50um
15m, 0.25mm ID, 1.00um
15m, 0.25mm ID, 1.00um w/5m 0.25mm Integra Guard
15m, 0.32mm ID, 1.00um
15m, 0.32mm ID, 1.00um No Cage
15m, 0.32mm ID, 1.00um Pack of 6
15m, 0.53mm ID, 1.00um
15m, 0.53mm ID, 1.00um w/5m, 0.53mm Integra Guard
15m, 0.53mm ID, 1.00um 5" cage for HP 6850
30m, 0.25mm ID, 1.00um
30m, 0.25mm ID, 1.00um with 5m Integra-Guard Column
30m, 0.25mm ID, 1.00um 6pk
30m, 0.25mm ID, 1.00um w/5" Cage for HP6850
30m, 0.32mm ID, 1.00um
30m, 0.32mm ID, 1.00um Customer Supplied Cage
30m, 0.32mm ID, 1.00um with 5m Integra-Guard Column
30m, 0.32mm ID, 1.00um w/10m 0.32mm Integra-Guard
30m, 0.32mm ID, 1.00um Pack of 6
30m, 0.32mm ID, 1.00um 5" HP6850 Cage
30m, 0.32mm ID, 1.00um 5" HP 6850 Cage, Pack of 6
30m, 0.53mm ID, 1.00um
30m, 0.53mm ID, 1.00um with 5m Integra-Guard Column
30m, 0.53mm ID, 1.00um with 10m Integra-Guard Column
30m, 0.53mm ID, 1.00um 5" Cage for HP6850
60m, 0.25mm ID, 1.00um
60m, 0.25mm ID, 1.0um with 5m INTEGRA guard
60m, 0.25mm ID, 1.00um w/10m 0.25mm Integra Guard
60m, 0.25mm ID, 1.00um 5" cage
60m, 0.32mm ID, 1.00um
50m, 0.32mm ID, 1.00um
60m, 0.32mm ID, 1.00um with 5m Integra Guard Column
60m, 0.32mm, 1.00um w/5" HP6850 Cage
60m, 0.53mm ID, 1.00um
50m, 0.53mm ID, 1.00um
60m, 0.53mm ID, 1.00um with 5m Integra-Guard Column
60m, 0.53mm ID, 1.00um w/5m x 0.53mm ID Guard Column Presstight with glue
60m, 0.53mm ID, 1.00um 5" Cage for HP6850
105m, 0.25mm ID, 1.00um
105m, 0.32mm ID, 1.00um
105m, 0.32mm ID, 1.00um w/5" HP6850 Cage
15m, 0.32mm ID, 1.50um
15m, 0.53mm ID, 1.50um
3 x 5m, 0.53mm ID, 1.50um
30m, 0.32mm ID, 1.50um
30m, 0.32mm ID, 1.50um with 5 meter Integra Guard Column
30m, 0.32mm ID, 1.50um w/5m Integra Guard on 5" Cage for Agilent 6850
30m, 0.32mm ID, 1.50um 5" HP6850 Cage
30m, 0.53mm ID, 1.50um
30m, 0.53mm ID, 1.5um w/5m 0.53mm Integra Guard
30m, 0.53mm ID, 1.50um Pack of 6

(Ctrl F)
> Cat.#s

> Current System AUD Prices

