

| | | |
|-------------|---------------------|---|
| 12636-128 | Rtx-5MS Cap. Column | 15m, 0.32mm ID, 0.50um 10m, 0.32mm |
| 12637 | Rtx-5MS Cap. Column | 15m, 0.53mm ID, 0.50um |
| 12637-126 | Rtx-5MS Cap. Column | 15m, 0.53mm ID, 0.50um with 5m Integra Guard Column |
| 12638 | Rtx-5MS Cap. Column | 30m, 0.25mm ID, 0.50um |
| 12638-101 | Rtx-5MS Cap. Column | 3 x 10m, 0.25mm ID, 0.50um |
| 12638-112 | Rtx-5MS Cap. Column | 20m, 0.25mm ID, 0.50um |
| 12638-124 | Rtx-5MS Cap. Column | 30m, 0.25mm ID, 0.50um with 5m Integra-Guard Column |
| 12638-12460 | Rtx-5MS Cap. Column | 30m, 0.25mm ID, 0.50um w/5m Integra Guard, 6pk |
| 12638-127 | Rtx-5MS Cap. Column | 30m, 0.25mm ID, 0.50um with 10m Integra-Guard Column |
| 12638-12760 | Rtx-5MS Cap. Column | 30m, 0.25mm ID, 0.50um w/10m Integra Guard, Pack of 6 |
| 12638-337 | Rtx-5MS Cap. Column | 30m, 0.25mm ID, 0.50um w/10m 0.25mm IP Deact Guard Column w/Vac Vu-Unio |
| 12638-600 | Rtx-5MS Cap. Column | 30m, 0.25mm ID, 0.50um Pack of 6 |
| 12638-6850 | Rtx-5MS Cap. Column | 30m, 0.25mm ID, 0.50um 5in cage for HP 6850 |
| 12639 | Rtx-5MS Cap. Column | 30m, 0.32mm ID, 0.50um |
| 12639-106 | Rtx-5MS Cap. Column | 25m, 0.32mm ID, 0.50um |
| 12639-125 | Rtx-5MS Cap. Column | 30m, 0.32mm ID, 0.50um with 5m Integra-Guard Column |
| 12639-127 | Rtx-5MS Cap. Column | 30m, 0.32mm ID, 0.50um 10m Integra guard column built in |
| 12639-128 | Rtx-5MS Cap. Column | 30m, 0.32mm ID, 0.50um with 10m Integra-Guard Column |
| 12639-600 | Rtx-5MS Cap. Column | 30m, 0.32mm ID, 0.50um Pack of 6 |
| 12640 | Rtx-5MS Cap. Column | 30m, 0.53mm ID, 0.50um |
| 12640-126 | Rtx-5MS Cap. Column | 30m, 0.53mm ID, 0.50um with 5m Integra-Guard Column |
| 12640-129 | Rtx-5MS Cap. Column | 30m, 0.53mm ID, 0.50um with 10m Integra-Guard Column |
| 12640-600 | Rtx-5MS Cap. Column | 30m, 0.53mm ID, 0.50um Pack of 6 |
| 12641 | Rtx-5MS Cap. Column | 60m, 0.25mm ID, 0.50um |
| 12641-103 | Rtx-5MS Cap. Column | 3-20m, 0.25mm ID, 0.50um |
| 12641-124 | Rtx-5MS Cap. Column | 60m, 0.25mm ID, 0.50um with 5m Integra Guard Column |
| 12641-127 | Rtx-5MS Cap. Column | 60m, 0.25mm ID, 0.50um w/10m Integra Guard |
| 12641-6850 | Rtx-5MS Cap. Column | 60m, 0.25mm ID, 0.50um 5" Cage for HP 6850 GCs |
| 12642 | Rtx-5MS Cap. Column | 60m, 0.32mm ID, 0.50um |
| 12642-105 | Rtx-5MS Cap. Column | 50m, 0.32mm ID, 0.50um |
| 12642-128 | Rtx-5MS Cap. Column | 60m, 0.32mm ID, 0.50um w/10m 0.32mm Integra Guard |
| 12650 | Rtx-5MS Cap. Column | 15m, 0.25mm ID, 1.00um |
| 12650-104 | Rtx-5MS Cap. Column | 3x5m, 0.25mm ID, 1.00um |
| 12650-123 | Rtx-5MS Cap. Column | 5m & 10m, 0.25mm ID, 1.00um |
| 12650-124 | Rtx-5MS Cap. Column | 15m, 0.25mm ID, 1.00 w/5m, 0.25mm Integra Guard |
| 12650-127 | Rtx-5MS Cap. Column | 15m, 0.25mm ID, 1.00um 10m, 0.25mm ID Guard |
| 12651 | Rtx-5MS Cap. Column | 15m, 0.32mm ID, 1.00um |
| 12651-125 | Rtx-5MS Cap. Column | 15m, 0.32mm ID, 1.00um w/5m 0.32mm Integra Guard |
| 12651-128 | Rtx-5MS Cap. Column | 15m, 0.32mm ID, 1.00um w/10m, 0.32mm Integra Guard |
| 12652 | Rtx-5MS Cap. Column | 15m, 0.53mm ID, 1.00um |
| 12652-126 | Rtx-5MS Cap. Column | 15m, 0.53mm ID, 1.00um with 5m, 0.53mm ID Integra Guard Column |
| 12653 | Rtx-5MS Cap. Column | 30m, 0.25mm ID, 1.00um |
| 12653-124 | Rtx-5MS Cap. Column | 30m, 0.25mm ID, 1.00um with 5m Integra-Guard Column |
| 12653-127 | Rtx-5MS Cap. Column | 30m, 0.25mm ID, 1.00um with 10m Integra-Guard Column |
| 12653-12760 | Rtx-5MS Cap. Column | 30m, 0.25mm ID, 1.00um w/ 10m IntergraGuard Column, 6pk |
| 12653-600 | Rtx-5MS Cap. Column | 30m, 0.25mm ID, 1.00um Pack of 6 |
| 12654 | Rtx-5MS Cap. Column | 30m, 0.32mm ID, 1.00um |
| 12654-125 | Rtx-5MS Cap. Column | 30m, 0.32mm ID, 1.00um with 5m Integra-Guard Column |
| 12654-128 | Rtx-5MS Cap. Column | 30m, 0.32mm ID, 1.00um with 10m Integra-Guard Column |
| 12655 | Rtx-5MS Cap. Column | 30m, 0.53mm ID, 1.00um |
| 12655-126 | Rtx-5MS Cap. Column | 30m, 0.53mm ID, 1.00um with 5m Integra-Guard Column |
| 12655-129 | Rtx-5MS Cap. Column | 30m, 0.53mm ID, 1.00um with 10m Integra-Guard Column |
| 12655-6850 | Rtx-5MS Cap. Column | 30m, 0.53mm ID, 1.00um 5" Cage for HP 6850 |
| 12667 | Rtx-5MS Cap. Column | 15m, 0.53mm ID, 1.50um |
| 12667-126 | Rtx-5MS Cap. Column | 15m, 0.53mm ID, 1.50um w/ 5m Integra Guard Column |
| 12667-282 | Rtx-5MS Cap. Column | 15m, 0.53mm ID, 1.50um 5in star cage, no guarantee for breakage |
| 12670 | Rtx-5MS Cap. Column | 30m, 0.53mm ID, 1.50um |
| 12670-126 | Rtx-5MS Cap. Column | 30m, 0.53mm ID, 1.50um with 5m Integra-Guard Column |
| 12670-129 | Rtx-5MS Cap. Column | 30m, 0.53mm ID, 1.50um 10m Integra Guard |
| 12690 | Rtx-5MS Cap. Column | 15m, 0.28mm ID, 0.25um |
| 12691 | Rtx-5MS Cap. Column | 15m, 0.28mm ID, 0.50um |
| 12692 | Rtx-5MS Cap. Column | 15m, 0.28mm ID, 1.0 m |
| 12693 | Rtx-5MS Cap. Column | 30m, 0.28mm ID, 0.25um |
| 12693-244 | Rtx-5MS Cap. Column | 30m, 0.28mm ID, 0.25um with 10m Integra Guard Column |
| 12694 | Rtx-5MS Cap. Column | 30m, 0.28mm ID, 0.50um |
| 12694-243 | Rtx-5MS Cap. Column | 30m, 0.28mm ID, 0.50um with 5 meter Integra Guard Column |

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



HROMalytic +61(0)3 9762 2034
ECHnology Pty Ltd

Australian Distributors
 Importers & Manufacturers
www.chromtech.net.au

Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

(Ctrl F)
> Cat.#s

> Current System AUD Prices

