

12754-600	Rtx-5Sil MS Cap. Column
12754-6850	Rtx-5sil MS Cap. Column
12755	Rtx-5Sil MS Cap. Column
12755-106	Rtx-5Sil MS Cap. Column
12755-126	Rtx-5Sil MS Cap. Column
12767	Rtx-5Sil MS Cap. Column
12770	Rtx-5Sil MS Cap. Column
12770-042	Rtx-5Sil MS Cap. Column
12770-126	Rtx-5Sil MS Cap. Column
12780	Rtx-5Sil MS Cap. Column
12780-125	Rtx-5Sil MS Cap. Column
12781	Rtx-5Sil MS Cap. Column
12782	Rtx-5Sil MS Cap. Column
12790	Rtx-5Sil MS Cap. Column
12791	Rtx-5Sil MS Cap. Column
12791-244	Rtx-5Sil MS Cap. Column
12792	Rtx-5Sil MS Cap. Column
12793	Rtx-5Sil MS Cap. Column
12793-243	Rtx-5Sil MS Cap. Column
12793-244	Rtx-5Sil MS Cap. Column
12794	Rtx-5Sil MS Cap. Column
12794-243	Rtx-5Sil MS Cap. Column
12794-244	Rtx-5Sil MS Cap. Column
12794-600	Rtx-5Sil MS Cap. Column
12795	Rtx-5Sil MS Cap. Column
12795-243	Rtx-5Sil MS Cap. Column
12795-244	Rtx-5Sil MS Cap. Column
12796	Rtx-5Sil MS Cap. Column
12797	Rtx-5Sil MS Cap. Column
12798	Rtx-5Sil MS Cap. Column
12923	Rtx-440 Cap. Column
12923-127	Rtx-440 Cap. Column
12923-6850	Rtx-440 Cap. Column
12924	Rtx-440 Cap. Column
12938	Rtx-440 Cap. Column
12939	Rtx-440 Cap. Column
12940	Rtx-440 Cap. Column
12955	Rtx-440 Cap. Column
12998	Rtx-TNT1 Cap. Column
12999	Rtx-TNT2 Cap. Column
13005	Rt-2330 NB Cap. Column
13006	Rt-2330 NB Cap. Column
13008	Rt-2330 NB Cap. Column
13009	Rt-2330 NB Cap. Column
13011	Rt-2330 NB Cap. Column
13012	Rt-2330 NB Cap. Column
13014	Rt-2330 NB Cap. Column
13015	Rt-2330 NB Cap. Column
13020	Rt-2330 NB Cap. Column
13021	Rt-2330 NB Cap. Column
13023	Rt-2330 NB Cap. Column
13024	Rt-2330 NB Cap. Column
13026	Rt-2330 NB Cap. Column
13027	Rt-2330 NB Cap. Column
13029	Rt-2330 NB Cap. Column
13030	Rt-2330 NB Cap. Column
13035	Rt-2340 NB Cap. Column
13036	Rt-2340 NB Cap. Column
13038	Rt-2340 NB Cap. Column
13039	Rt-2340 NB Cap. Column
13041	Rt-2340 NB Cap. Column
13042	Rt-2340 NB Cap. Column
13044	Rt-2340 NB Cap. Column
13045	Rt-2340 NB Cap. Column
13050	Rt-2340 NB Cap. Column
13051	Rt-2340 NB Cap. Column

30m, 0.32mm ID, 1.00um Pack of 6
30m, 0.32mmID, 1.00um 5" cage for t
30m, 0.53mm ID, 1.00um
25m, 0.53mm ID, 1.00um
30m, 0.53mmID, 1.00um with 5m Integra Guard Column
15m, 0.53mm ID, 1.50um
30m, 0.53mm ID, 1.50um
30m, 0.53mm ID, 1.50um 5" Nordion Cage
30m, 0.53mm ID, 1.50um w/5m 0.53mm Integra Guard
60m, 0.32mm ID, 0.25um
60m, 0.32mm ID, 0.25um 5m, 0.32mm guard
25m, 0.32mm ID, 1.0um
60m, 0.32mm ID, 1.0um
15m, 0.28mm ID, 0.25um
15m, 0.28mm ID, 0.50um
15m, 0.28mm ID, 0.50um w/10m, 0.28mm Integra Guard
15m, 0.28mm ID, 1.00um
30m, 0.28mm ID, 0.25um
30m, 0.28mm ID, 0.25um w/5m, .28mm Integra Guard
30m, 0.28mm ID, 0.25um w/10m, .28mm Integra Guard
30m, 0.28mm ID, 0.50um
30m, 0.28mm ID, 0.50um w/5m, .28mm Integra Guard
30m, 0.28mm ID, 0.50um w/10m Integra Guard
30m, 0.28mm ID, 0.50um Pack of 6
30m, 0.28mm ID, 1.00um
30m, 0.28mm ID, 1.00um w/5m, .28mm Integra Guard
30m, 0.28mm ID, 1.00um w/10m, 0.28mm Integra Guard
60m, 0.25mm ID, 0.5um
60m, 0.25mm ID, 1.0um
40m, 0.45mm ID, 1.5um
30m, 0.25mm ID, 0.25um
30m, 0.25mm ID, 0.25um w/ 10m, 0.25 IntegraGuard
30m, 0.25mmID, 0.25um 5" cage for HP 6850
30m, 0.32mm ID, 0.25um
30m, 0.25mm ID, 0.50um
30m, 0.32mm ID, 0.50um
30m, 0.53mm ID, 0.50um
30m, 0.53mm ID, 1.0um
6m, 0.53mm ID, 1.5um Sold as 3-pk only
6m, 0.53mm ID, 1.5um Sold as 3-pk only
15m, 0.25mm ID, 0.10um
15m, 0.32mm ID, 0.10um
30m, 0.25mm ID, 0.10um
30m, 0.32mm ID, 0.10um
60m, 0.25mm ID, 0.10um
60m, 0.32mm ID, 0.10um
105m, 0.25mm ID, 0.10um
105m, 0.32mm ID, 0.10um
15m, 0.25mm ID, 0.20um
15m, 0.32mm ID, 0.20um
30m, 0.25mm ID, 0.20um
30m, 0.32mm ID, 0.20um
60m, 0.25mm ID, 0.20um
60m, 0.32mm ID, 0.20um
105m, 0.25mm ID, 0.20um
105m, 0.32mm ID, 0.20um
15m, 0.25mm ID, 0.10um
15m, 0.32mm ID, 0.10um
30m, 0.25mm ID, 0.10um
30m, 0.32mm ID, 0.10um
60m, 0.25mm ID, 0.10um
60m, 0.32mm ID, 0.10um
105m, 0.25mm ID, 0.10um
105m, 0.32mm ID, 0.10um
15m, 0.25mm ID, 0.20um
15m, 0.32mm ID, 0.20um

[Ctrl F]  
> Cat.#s

> Current System AUD Prices

