



13420-096	Rxi-5ms Cap. Column	2-6m, 0.25mm ID, 0.25um
13420-104	Rxi-5ms Cap. Column	3 x 5m, 0.25mm ID, 0.25um
13420-107	Rxi-5ms Cap Column	10m, 0.25mm ID, 0.25um
13420-170	Rxi-5ms Cap. Column	CURRENTLY NOT AVAILABLE, USE CAT #13420 15m, 0.25mm ID, 0.25um 5m,
13420-600	Rxi-5ms Cap. Column	15m, 0.25mm ID, 0.25um 6pk
13420-6850	Rxi-5ms Cap. Column	15m, 0.25mm ID, 0.25um 5in cage for HP 6850
13421	Rxi-5ms Cap. Column	15m, 0.32mm ID, 0.25um
13421-600	Rxi-5ms Cap. Column	15m, 0.32mm ID, 0.25um 6pk
13421-6850	Rxi-5ms Cap. Column	15m, 0.32mm ID, 0.25um 5in cage for HP 6850
13422	Rxi-5ms Cap. Column	15m, 0.53mm ID, 0.25um
13422-107	Rxi-5ms Cap. Column	10m, 0.53mm ID, 0.25um
13423	Rxi-5ms Cap. Column	30m, 0.25mm ID, 0.25um
13423-112	Rxi-5ms Cap. Column	20m, 0.25mm ID, 0.25um
13423-170	Rxi-5ms Cap. Column	Indefinite Backorder 30m, 0.25mm ID, 0.25um 5m, 0.25mm Rxi guard w/Alumase;
13423-172	Rxi-5ms Cap. Column	CURRENTLY NOT AVAILABLE, USE CAT #13423 30m, 0.25mm ID, 0.25um 5m,
13423-173	Rxi-5ms Cap. Column	CURRENTLY NOT AVAILABLE, USE CAT #13423 30m, 0.25mm ID, 0.25um w/1
13423-280	Rxi-5ms Cap. Column	30m, 0.25mm ID, 0.25um 4in Star Cage No guarantee for breakage
13423-309	Rxi-5ms Cap. Column	30m, 0.25mm ID, 0.25um w/10m,0.25mm IP Guard Column w/Presstight
13423-600	Rxi-5ms Cap. Column	30m, 0.25mm ID, 0.25um Pack of 6
13423-6850	Rxi-5ms Cap. Column	30m, 0.25mm ID, 0.25um 5" HP6850 Cage
13423-68506	Rxi-5ms Cap. Column	30m, 0.25mm ID, 0.25um 5in cage for HP 6850 6pk
13424	Rxi-5ms Cap. Column	30m, 0.32mm ID, 0.25um
13424-174	Rxi-5ms Cap. Column	CURRENTLY NOT AVAILABLE, USE CAT #13424 30m 0.32mm ID, 0.25um w/10
13424-600	Rxi-5ms Cap. Column	30m, 0.32mm ID, 0.25um 6pk
13424-6850	Rxi-5ms Cap. Column	30m, 0.32mm ID, 0.25um 5" cage for HP 6850
13425	Rxi-5ms Cap. Column	30m, 0.53mm ID, 0.25um
13426	Rxi-5ms Cap. Column	60m, 0.25mm ID, 0.25um
13426-051	Rxi-5ms Cap. Column	60m, 0.25mm ID, 0.25um No cage (no guarantee for breakage)
13426-105	Rxi-5ms Cap. Column	50m, 0.25mm ID, 0.25
13427	Rxi-5ms Cap. Column	60m, 0.32mm ID, 0.25um
13427-051	Rxi-5ms Cap. Column	60m, 0.32mm ID, 0.25um No cage(no guarantee for breakage)
13435	Rxi-5ms Cap. Column	15m, 0.25mm ID, 0.50um
13436	Rxi-5ms Cap. Column	15m, 0.32mm ID, 0.50um
13437	Rxi-5ms Cap. Column	15m, 0.53mm ID, 0.50um
13438	Rxi-5ms Cap. Column	30m, 0.25mm ID, 0.50um
13438-170	Rxi-5ms Cap. Column	30m, 0.25mm ID, 0.50um Indefinite Backorder 5m, 0.25mm Rxi guard w/AlumaSe
13438-600	Rxi-5ms Cap. Column	30m, 0.25mm ID, 0.50um 6pk
13439	Rxi-5ms Cap. Column	30m, 0.32mm ID, 0.50um
13439-171	Rxi-5ms Cap. Column	30m, 0.32mm ID, 0.50um w/5m 0.32mm Rxi Guard Column Joined w/AlumaSeal (
13439-6850	Rxi-5ms Cap. Column	30m, 0.32mm ID, 0.50um 5in cage for HP 6850
13440	Rxi-5ms Cap. Column	30m, 0.53mm ID, 0.50um
13440-175	Rxi-5ms Cap. Column	CURRENTLY NOT AVAILABLE, USE CAT #13440 30m, 0.53mm ID, 0.50um 10n
13440-6850	Rxi-5ms Cap. Column	30m, 0.53mm ID, 0.50um
13441	Rxi-5ms Cap. Column	60m, 0.25mm ID, 0.50um
13442	Rxi-5ms Cap. Column	60m, 0.32mm ID, 0.50um
13442-105	Rxi-5ms Cap. Column	50m, 0.32mm ID, 0.50um
13450	Rxi-5ms Cap. Column	15m, 0.25mm ID, 1.0um
13451	Rxi-5ms Cap. Column	15m, 0.32mm ID, 1.0um
13452	Rxi-5ms Cap. Column	15m, 0.53mm ID, 1.0um
13452-107	Rxi-5ms Cap. Column	10m, 0.53mm ID, 1.0um
13453	Rxi-5ms Cap. Column	30m, 0.25mm ID, 1.0um
13453-163	Rxi-5ms Cap. Column	30m, 0.25mm ID, 1.0um 5m, 0.32mm Guard w/Vu 2 Union
13453-6850	Rxi-5ms Cap. Column	30m, 0.25mm ID, 1.0um For HP 6850
13454	Rxi-5ms Cap. Column	30m, 0.32mm ID, 1.0um
13454-106	Rxi-5ms Cap. Column	25m, 0.32mm ID, 1.0um
13455	Rxi-5ms Cap. Column	30m, 0.53mm ID, 1.0um
13455-600	Rxi-5ms Cap. Column	30m, 0.53mm ID, 1.0um Pack of 6
13456	Rxi-5ms Cap. Column	60m, 0.25mm ID, 1.0um
13456-280	Rxi-5ms Cap. Column	60m, 0.25mm ID, 1.0um 4in star cage, no guarantee for breakage
13457	Rxi-5ms Cap. Column	60m, 0.32mm ID, 1.0um
13457-105	Rxi-5ms Cap Column	50m, 0.32mm ID, 1.0um
13457-6850	Rxi-5ms Cap. Column	60m, 0.32mm ID, 1.0um 5" cage for HP 6850
13467	Rxi-5ms Cap. Column	15m, 0.53mm ID, 1.5um
13470	Rxi-5ms Cap. Column	30m, 0.53mm ID, 1.5um
13470-600	Rxi-5ms Cap. Column	30m, 0.53mm ID, 1.5um Pack of 6
13470-6850	Rxi-5ms Cap. Column	30m, 0.53mm ID, 1.5um 5in cage for HP 6850