



13481	Rxi-5ms Cap. Column	30m, 0.25mm ID, 0.40um
13497	Rxi-5ms Cap. Column	12m, 0.20mm ID, 0.33um
13498	Rxi-5ms Cap. Column	25m, 0.20mm ID, 0.33um
13498-600	Rxi-5ms Cap. Column	25m, 0.20mm ID, 0.33um Pack of 6
13498-6850	Rxi-5ms Cap. Column	25m, 0.20mm ID, 0.33 um for HP 6850 Config
13499	Rxi-5ms Cap. Column	50m, 0.20mm ID, 0.33um
13501	Rxi-17 Cap. Column	10m, 0.10mm ID, 0.10um
13501-067	Rxi-17 Cap. Column	5 x 2m, 0.10mm ID, 0.10um
13502	Rxi-17 Cap. Column	20m, 0.18mm ID, 0.18um
13502-600	Rxi-17 Cap. Column	20m, 0.18mm ID, 0.18um Pack of 6
13520	Rxi-17 Cap. Column	15m, 0.25mm ID, 0.25um
13521	Rxi-17 Cap. Column	15m, 0.32mm ID, 0.25um
13522	Rxi-17 Cap. Column	15m, 0.53mm ID, 0.25um
13522-107	Rxi-17 Cap. Column	10m, 0.53mm ID, 0.25um
13523	Rxi-17 Cap. Column	30m, 0.25mm ID, 0.25um
13523-6850	Rxi-17 Cap. Column	30m, 0.25mm ID, 0.25um For HP 6850 GCs
13524	Rxi-17 Cap. Column	30m, 0.32mm ID, 0.25um
13524-6850	Rxi-17 Cap. Column	30m, 0.32mm ID, 0.25um 5in cage for HP 6850
13525	Rxi-17 Cap. Column	30m, 0.53mm ID, 0.25um
13535	Rxi-17 Cap. Column	15m, 0.25mm ID, 0.50um
13536	Rxi-17 Cap. Column	15m, 0.32mm ID, 0.50um
13537	Rxi-17 Cap. Column	15m, 0.53mm ID, 0.50um
13538	Rxi-17 Cap. Column	30m, 0.25mm ID, 0.50um
13539	Rxi-17 Cap. Column	30m, 0.32mm ID, 0.50um
13540	Rxi-17 Cap. Column	30m, 0.53mm ID, 0.50um
13550	Rxi-17 Cap. Column	15m, 0.25mm ID, 1.0um
13551	Rxi-17 Cap. Column	15m, 0.32mm ID, 1.0um
13551-6850	Rxi-17 Cap. Column	15m, 0.32mm ID, 1.0um 5" Cage for Agilent GCs
13552	Rxi-17 Cap. Column	15m, 0.53mm ID, 1.00um
13553	Rxi-17 Cap. Column	30m, 0.25mm ID, 1.0um
13554	Rxi-17 Cap. Column	30m, 0.32mm ID, 1.0um
13554-031	Rxi-17 Cap. Column	30m, 0.32mm ID, 1.0um Customer Supplied Cage
13554-106	Rxi-17 Cap. Column	25m, 0.32mm ID, 1.0um
13555	Rxi-17 Cap. Column	30m, 0.53mm ID, 1.00um
13566	Rxi-17 Cap. Column	15m, 0.32mm ID, 1.5um
13567	Rxi-17 Cap. Column	15m, 0.53mm ID, 1.5um
13567-107	Rxi-17 Cap. Column	10m, 0.53mm ID, 1.5um
13567-6850	Rxi-17 Cap. Column	15m, 0.53mm ID, 1.5um 5in cage for HP 6850
13569	Rxi-17 Cap. Column	30m, 0.53mm ID, 0.83um
13570	Rxi-17 Cap. Column	30m, 0.53mm ID, 1.5um
13570-6850	Rxi-17 Cap. Column	30m, 0.53mm ID, 1.5um 5" Cage for HP 6850
13605	Rxi-5Sil MS Cap. Column	15m, 0.25mm ID, 0.10um
13605-123	Rxi-5Sil MS Cap. Column	1-10m and 1-5m, 0.25mm ID, 0.10um
13608	Rxi-5Sil MS Cap. Column	30m, 0.25mm ID, 0.10um
13620	Rxi-5Sil MS Cap. Column	15m, 0.25mm ID, 0.25um
13620-079	Rxi-5Sil MS Cap. Column	12m, 0.25mm ID, 0.25um
13620-104	Rxi-5Sil MS Cap. Column	3 x 5m, 0.25mm ID, 0.25um
13620-124	Rxi-5Sil MS Cap. Column	15m, 0.25mm ID, 0.25um w/ 5m, 0.25mm ID Integra Guard
13620-127	Rxi-5Sil MS Cap. Column	15m, 0.25mm ID, 0.25um w/10m Integra Guard
13620-600	Rxi-5Sil MS Cap. Column	15m, 0.25mm ID, 0.25um Pack of 6
13621	Rxi-5Sil MS Cap. Column	15m, 0.32mm ID, 0.25um
13621-124	Rxi-5Sil MS Cap. Column	15m, 0.32mm ID, 0.25um 5m, 0.25mm ID Guard
13621-125	Rxi-5Sil MS Cap. Column	15m, 0.32mm ID, 0.25um 5m, 0.32mm ID Integra-guard
13623	Rxi-5Sil MS Cap. Column	30m, 0.25mm ID, 0.25um
13623-106	Rxi-5Sil MS Cap. Column	25m, 0.25mm ID, 0.25um
13623-124	Rxi-5Sil MS Cap. Column	30m, 0.25mm ID, 0.25um 5m, 0.25mm ID Integra Guard
13623-12460	Rxi-5Sil MS Cap. Column	30m, 0.25mm ID, 0.25um 5m, 0.25mm ID, 0.25um 6pk
13623-12468	Rxi-5Sil MS Cap. Column	30m, 0.25mm ID, 0.25um 5m, 0.25mm ID IntergraGuard 5" HP 6850 Cage
13623-127	Rxi-5Sil MS Cap. Column	30m, 0.25mm ID, 0.25um 10m, 0.25mm ID Integra Guard
13623-12760	Rxi-5Sil MS Cap. Column	30m, 0.25mm ID, 0.25um 10m, 0.25mm ID Integra Guard Pack of 6
13623-12768	Rxi-5Sil MS Cap. Column	30m, 0.25mm ID, 0.25um 10m, 0.25mm ID IntergraGuard 5" HP 6850 Cage
13623-170	Rxi-5Sil MS Cap. Column	30m, 0.25mm ID, 0.25um Indefinite Backorder 5m, 0.25mm Rxi guard w/AlumaSe
13623-600	Rxi-5Sil MS Cap. Column	30m, 0.25mm ID, 0.25um 6pk
13623-6850	Rxi-5Sil MS Cap. Column	30m, 0.25mm ID, 0.25um 5" HP 6850 Cage
13624	Rxi-5Sil MS Cap. Column	30m, 0.32mm ID, 0.25um
13624-125	Rxi-5Sil MS Cap. Column	30m, 0.32mm ID, 0.25um w/ 5m Integra-Guard Column