

|              |                       |  |
|--------------|-----------------------|--|
| 14639-125    | Rtx-35 MS Cap. Column | 30m, 0.32mm ID, 0.50um w/5m 0.32n  |
| 14639-128685 | Rtx-35 MS Cap. Column | 30m, 0.32mm ID, 0.50um 10m, 0.32n  |
| 14640        | Rtx-35 MS Cap. Column | 30m 0.53mm ID, 0.50um  |
| 14640-126    | Rtx-35 MS Cap. Column | 30m, 0.53mm ID, 0.50um w/5m Integra Guard                                    |
| 14650        | Rtx-35 MS Cap. Column | 15m 0.25mm ID, 1.00um  |
| 14651        | Rtx-35 MS Cap. Column | 15m 0.32mm ID, 1.00um  |
| 14652        | Rtx-35 MS Cap. Column | 15m 0.53mm ID, 1.00um  |
| 14652-6850   | Rtx-35 MS Cap. Column | 15m, 0.53mm ID, 1.00um 5" cage for HP 6850                                   |
| 14653        | Rtx-35 MS Cap. Column | 30m 0.25mm ID, 1.00um  |
| 14653-124    | Rtx-35 MS Cap. Column | 30m, 0.25mm ID, 1.00um 5m, 0.25mm Guard                                      |
| 14654        | Rtx-35 MS Cap. Column | 30m 0.32mm ID, 1.00um  |
| 14655        | Rtx-35 MS Cap. Column | 30m 0.53mm ID, 1.00um  |
| 14655-126    | Rtx-35 MS Cap. Column | 30m, 0.53mm ID, 1.00um w/5m, 0.53mm Integra Guard                            |
| 14667        | Rtx-35 MS Cap. Column | 15m 0.53mm ID, 1.50um  |
| 14670        | Rtx-35 MS Cap. Column | 30m 0.53mm ID, 1.50um  |
| 15005        | Rtx-200 Cap. Column   | 15m, 0.25mm ID, 0.10um   |
| 15006        | Rtx-200 Cap. Column   | 15m, 0.32mm ID, 0.10um   |
| 15007        | Rtx-200 Cap. Column   | 15m, 0.53mm ID, 0.10um   |
| 15008        | Rtx-200 Cap. Column   | 30m, 0.25mm ID, 0.10um   |
| 15009        | Rtx-200 Cap. Column   | 30m, 0.32mm ID, 0.10um   |
| 15010        | Rtx-200 Cap. Column   | 30m, 0.53mm ID, 0.10um   |
| 15011        | Rtx-200 Cap. Column   | 60m, 0.25mm ID, 0.10um   |
| 15012        | Rtx-200 Cap. Column   | 60m, 0.32mm ID, 0.10um   |
| 15013        | Rtx-200 Cap. Column   | 60m, 0.53mm ID, 0.10um   |
| 15014        | Rtx-200 Cap. Column   | 105m, 0.25mm ID, 0.10um  |
| 15015        | Rtx-200 Cap. Column   | 105m, 0.32mm ID, 0.10um  |
| 15020        | Rtx-200 Cap. Column   | 15m, 0.25mm ID, 0.25um   |
| 15020-104    | Rtx-200 Cap. Column   | 3 x 5m, 0.25mm ID, 0.25um  |
| 15020-123    | Rtx-200 Cap. Column   | 10m & 5m, 0.25mm ID, 0.25um  |
| 15020-6850   | Rtx-200 Cap. Column   | 15m, 0.25mm ID, 0.25um 5" cage for HP 6850                                   |
| 15021        | Rtx-200 Cap. Column   | 15m, 0.32mm ID, 0.25um   |
| 15022        | Rtx-200 Cap. Column   | 15m, 0.53mm ID, 0.25um   |
| 15023        | Rtx-200 Cap. Column   | 30m, 0.25mm ID, 0.25um   |
| 15023-309    | Rtx-200 Cap. Column   | 30m, 0.25mm ID, 0.25um 10m, 0.25mm ID IP Guard Column w/ Presstight          |
| 15023-6850   | Rtx-200 Cap. Column   | 30m, 0.25mm ID, 0.25um 5" HP6850 Cage  |
| 15024        | Rtx-200 Cap. Column   | 30m, 0.32mm ID, 0.25um   |
| 15024-310    | Rtx-200 Cap. Column   | 30m, 0.32mm ID, 0.25um 10m, 0.32mm ID IP Guard w/Presstight                  |
| 15024-600    | Rtx-200 Cap. Column   | 30m, 0.32mm ID, 0.25um Pack of 6   |
| 15024-6850   | Rtx-200 Cap. Column   | 30m, 0.32mm ID, 0.25um 5" 6850 Cage  |
| 15024-68506  | Rtx-200 Cap. Column   | 30m, 0.32mm ID, 0.25um 5" 6850 Cage Pack of 6                                |
| 15025        | Rtx-200 Cap. Column   | 30m, 0.53mm ID, 0.25um   |
| 15026        | Rtx-200 Cap. Column   | 60m, 0.25mm ID, 0.25um   |
| 15027        | Rtx-200 Cap. Column   | 60m, 0.32mm ID, 0.25um   |
| 15027-6850   | Rtx-200 Cap. Column   | 60m, 0.32mm ID, 0.25um 5in cage for HP 6850                                  |
| 15028        | Rtx-200 Cap. Column   | 60m, 0.53mm ID, 0.25um   |
| 15029        | Rtx-200 Cap. Column   | 105m, 0.25mm ID, 0.25um  |
| 15030        | Rtx-200 Cap. Column   | 105m, 0.32mm ID, 0.25um  |
| 15035        | Rtx-200 Cap. Column   | 15m, 0.25mm ID, 0.50um   |
| 15036        | Rtx-200 Cap. Column   | 15m, 0.32mm ID, 0.50um   |
| 15037        | Rtx-200 Cap. Column   | 15m, 0.53mm ID, 0.50um   |
| 15038        | Rtx-200 Cap. Column   | 30m, 0.25mm ID, 0.50um   |
| 15038-364    | Rtx-200 Cap. Column   | 30m, 0.25mm ID, 0.50um 5m, 0.25mm ID Siltek guard column w/Siltek presstight |
| 15038-6850   | Rtx-200 Cap. Column   | 30m, 0.25mm ID, 0.50um 5" Cage for HP 6850                                   |
| 15039        | Rtx-200 Cap. Column   | 30m, 0.32mm ID, 0.50um   |
| 15039-6850   | Rtx-200 Cap. Column   | 30m, 0.32mm ID, 0.50um on a 6850 Cage  |
| 15040        | Rtx-200 Cap. Column   | 30m, 0.53mm ID, 0.50um   |
| 15040-600    | Rtx-200 Cap. Column   | 30m, 0.53mm ID, 0.50um Pack of 6   |
| 15041        | Rtx-200 Cap. Column   | 60m, 0.25mm ID, 0.50um   |
| 15041-6850   | Rtx-200 Cap. Column   | 60m, 0.25mm ID, 0.50um 5" Cage for HP 6850 GCs                               |
| 15042        | Rtx-200 Cap. Column   | 60m, 0.32mm ID, 0.50um   |
| 15042-6850   | Rtx-200 Cap. Column   | 60m, 0.32mm ID, 0.50um 5" HP6850 Cage  |
| 15043        | Rtx-200 Cap. Column   | 60m, 0.53mm ID, 0.50um   |
| 15044        | Rtx-200 Cap. Column   | 105m, 0.25mm ID, 0.50um  |
| 15045        | Rtx-200 Cap. Column   | 105m, 0.32mm ID, 0.50um  |
| 15050        | Rtx-200 Cap. Column   | 15m, 0.25mm ID, 1.00um   |
| 15051        | Rtx-200 Cap. Column   | 15m, 0.32mm ID, 1.00um   |

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

|  |  |
|--|--|
|  <p><b>HROMalytic</b> +61(0)3 9762 2034<br/> <b>ECHnology</b> Pty Ltd</p>   | <p><b>Australian Distributors</b><br/>         Importers &amp; Manufacturers<br/> <a href="http://www.chromtech.net.au">www.chromtech.net.au</a></p> |
| <p>Website NEW : <a href="http://www.chromalytic.net.au">www.chromalytic.net.au</a> E-mail : <a href="mailto:info@chromtech.net.au">info@chromtech.net.au</a> Tel: 03 9762 2034 . . . in AUSTRALIA</p> |  |

(Ctrl F)  
> Cat.#s

> Current System AUD Prices

