

16076-129	Rtx-1301	Cap. Column
16082	Rtx-1301	Cap. Column
16082-104	Rtx-1301	Cap. Column
16082-126	Rtx-1301	Cap. Column
16082-6850	Rtx-1301	Cap. Column
16085	Rtx-1301	Cap. Column
16085-126	Rtx-1301	Cap. Column
16085-12660	Rtx-1301	Cap. Column
16085-12668	Rtx-1301	Cap. Column
16085-129	Rtx-1301	Cap. Column
16085-164	Rtx-1301	Cap. Column
16085-305	Rtx-1301	Cap. Column
16085-600	Rtx-1301	Cap. Column
16085-6850	Rtx-1301	Cap. Column
16088	Rtx-1301	Cap. Column
16088-105	Rtx-1301	Cap. Column
16088-126	Rtx-1301	Cap. Column
16088-129	Rtx-1301	Cap. Column
16088-6850	Rtx-1301	Cap. Column
16091	Rtx-1301	Cap. Column
16092	Rtx-1301	Cap. Column
16092-125	Rtx-1301	Cap. Column
16092-6850	Rtx-1301	Cap. Column
16093	Rtx-1301	Cap. Column
16093-6850	Rtx-1301	Cap. Column
17005	Rtx-65TG	Cap. Column
17005-107	Rtx-65TG	Cap. Column
17006	Rtx-65TG	Cap. Column
17007	Rtx-65TG	Cap. Column
17008	Rtx-65TG	Cap. Column
17008-106	Rtx-65TG	Cap. Column
17008-112	Rtx-65TG	Cap. Column
17008-303	Rtx-65TG	Cap. Column
17008-600	Rtx-65TG	Cap. Column
17008-6850	Rtx-65TG	Cap. Column
17009	Rtx-65TG	Cap. Column
17009-6850	Rtx-65TG	Cap. Column
17010	Rtx-65TG	Cap. Column
17020	Rtx-65	Cap. Column
17021	Rtx-65	Cap. Column
17022	Rtx-65	Cap. Column
17023	Rtx-65	Cap. Column
17024	Rtx-65	Cap. Column
17025	Rtx-65	Cap. Column
17035	Rtx-65	Cap. Column
17036	Rtx-65	Cap. Column
17037	Rtx-65	Cap. Column
17038	Rtx-65	Cap. Column
17039	Rtx-65	Cap. Column
17040	Rtx-65	Cap. Column
17050	Rtx-65	Cap. Column
17051	Rtx-65	Cap. Column
17052	Rtx-65	Cap. Column
17053	Rtx-65	Cap. Column
17054	Rtx-65	Cap. Column
17055	Rtx-65	Cap. Column
17055-6850	Rtx-65	Cap. Column
18000	Rtx-BAC2	Cap. Column
18000-305	Rtx-BAC2	Cap. Column
18000-600	Rtx-BAC2	Cap. Column
18000-6850	Rtx-BAC2	Cap. Column
18001	Rtx-BAC1	Cap. Column
18001-126	Rtx-BAC1	Cap. Column
18001-129	Rtx-BAC1	Cap. Column
18001-600	Rtx-BAC1	Cap. Column
18001-6850	Rtx-BAC1	Cap. Column

75m, 0.53mm ID, 3.00um 10m, 0.53mm
15m, 0.53mm ID, 3.00um
3 x 5m, 0.53mm ID, 3.00 um
15m, 0.53mm ID, 3.00um 5m, 0.53mm Guard Column built in
15m, 0.53mm ID, 3.00um For HP 6850 GCs
30m, 0.53mm ID, 3.00um (G43)
30m, 0.53mm ID, 3.00um (G43) with 5m Integra-Guard Column Rtx-G43 (Rtx-130
30m, 0.53mm ID, 3.00um (G43) w/5m Integra Guard, 6pk
30m, 0.53mm ID, 3.00um (G43) w/5m Integra Guard/5" 6850 Cage
30m, 0.53mm ID, 3.00um with 10m Integra-Guard Column
30m, 0.53mm ID, 3.00um (G43) w/ 5m, 0.53 Guard Column w/ Vu2 Union
30m, 0.53mm ID, 3.00um w/5m x 0.53mm ID Guard Column Presstight with glue
30m, 0.53mm ID, 3.00um (G43) 6 pack
30m, 0.53mm ID, 3.00um (G43) 5" HP6850 Cage
60m, 0.53mm ID, 3.00um
50m, 0.53mm ID, 3.00um
60m, 0.53mm ID, 3.00um with 5m Integra Guard Column
60m, 0.53mm ID, 3.00um with 10m Integra-Guard Column
60m, 0.53mm ID, 3.00um 5" cage for HP 6850
105m, 0.53mm ID, 3.00um
30m, 0.32mm ID, 1.8um
30m, 0.32mm ID, 1.8um 5m, 0.32mm Guard Column
30m, 0.32mm ID, 1.8um For HP 6850 GCs
60m, 0.32mm ID, 1.8um
60m, 0.32mm ID, 1.8um For HP 6850 Cage
15m, 0.25mm ID, 0.10um
10m, 0.25mm ID, 0.10um
15m, 0.32mm ID, 0.10um
15m, 0.53mm ID, 0.10um
30m, 0.25mm ID, 0.10um
25m, 0.25mm ID, 0.10um
20m, 0.25mm ID, 0.10um
30m, 0.25mm ID, 0.10um w/5m x 0.25mm ID Guard Column Presstight with Glue
30m, 0.25mm ID, 0.10um 6pk
30m, 0.25mm ID, 0.10um 5" HP6850 Cage
30m, 0.32mm ID, 0.10um
30m, 0.32mm ID, 0.10um 5in cage for HP 6850
30m, 0.53mm ID, 0.10um
15m, 0.25mm ID, 0.25um
15m, 0.32mm ID, 0.25um
15m, 0.53mm ID, 0.25um
30m, 0.25mm ID, 0.25um
30m, 0.32mm ID, 0.25um
30m, 0.53mm ID, 0.25um
15m, 0.25mm ID, 0.50um
15m, 0.32mm ID, 0.50um
15m, 0.53mm ID, 0.50um
30m, 0.25mm ID, 0.50um
30m, 0.32mm ID, 0.50um
30m, 0.53mm ID, 0.50um
15m, 0.25mm ID, 1.00um
15m, 0.32mm ID, 1.00um
15m, 0.53mm ID, 1.00um
30m, 0.25mm ID, 1.00um
30m, 0.32mm ID, 1.00um
30m, 0.53mm ID, 1.00um
30m, 0.53mm ID, 1.00um 5" cage for HP 6850
30m, 0.53mm ID, 2.00um
30m, 0.53mm ID, 2.00um W/ 5m, 0.53mm ID, IP Guard Column w/ Presstight
30m, 0.53mm ID, 2.00um Package of 6
30m, 0.53mm ID, 2.00um on 5" 6850 cage
30m, 0.53mm ID, 3.00um
30m, 0.53mm ID, 3.00um w/5m Integra Guard
30m, 0.53mm ID, 3.00um 10m, 0.53mm guard built in
30m, 0.53mm ID, 3.00um Package of 6
30m, 0.53mm ID, 3.00um w/5" coil

