

18002	Rtx-BAC2 Cap. Column
18002-6850	Rtx-BAC2 Cap. Column
18003	Rtx-BAC1 Cap. Column
18003-125	Rtx-BAC1 Cap. Column
18003-128	Rtx-BAC1 Cap. Column
18003-6850	Rtx-BAC1 Cap. Column
18010	Rtx-1 F&F Cap. Column
18010-125	Rtx-1 F&F Cap. Column
18010-6850	Rtx-1 F&F Cap. Column
18023	Rtx-1 F&F Cap. Column
18023-124	Rtx-1 F&F Cap. Column
18023-6850	Rtx-1 F&F Cap. Column
18024	Rtx-1 F&F Cap. Column
18024-111	Rtx-1 F&F Cap. Column
18026	Rtx-1 F&F Cap. Column
18026-105	Rtx-1 F&F Cap. Column
18027	Rtx-1 F&F Cap. Column
18037	Rtx-1 F&F Cap. Column
18038	Rtx-1 F&F Cap. Column
18038-124	Rtx-1 F&F Cap. Column
18039	Rtx-1 F&F Cap. Column
18040	Rtx-1 F&F Cap. Column
18041	Rtx-1 F&F Cap. Column
18042	Rtx-1 F&F Cap. Column
18043	Rtx-1 F&F Cap. Column
18052	Rtx-1 F&F Cap. Column
18053	Rtx-1 F&F Cap. Column
18054	Rtx-1 F&F Cap. Column
18055	Rtx-1 F&F Cap. Column
18055-280	Rtx-1 F&F Cap. Column
18055-282	Rtx-1 F&F Cap. Column
18056	Rtx-1 F&F Cap. Column
18056-6850	Rtx-1 F&F Cap. Column
18057	Rtx-1 F&F Cap. Column
18058	Rtx-1 F&F Cap. Column
18067	Rtx-1 F&F Cap. Column
18067-6850	Rtx-1 F&F Cap. Column
18070	Rtx-1 F&F Cap. Column
18073	Rtx-1 F&F Cap. Column
18074	Rtx-Mineral Oil Cap. Col.
18075	Rtx-Mineral Oil Cap. Col.
18076	Rtx-VolatileAmine
18077	Rtx-VolatileAmine
18078	Rtx-VolatileAmine
18079-123	Rtx-Mineral Oil Cap. Col
19000	Micropacked GC Column
19001	Micropacked GC Column
19001-291	Micropacked GC Column
19001-888	Micropacked GC Column
19002	Micropacked GC Column
19002-895	Micropacked GC Column
19002-900	Micropacked Column
19003	Micropacked GC Column
19003-895	Micropacked GC Column
19003-900	Micropacked GC Column
19004	Micropacked GC Column
19005	Micropacked GC Column
19006	Micropacked GC Column
19007	Micropacked GC Column
19007-895	Micropacked GC Column
19008	Micropacked GC Column
19009	Micropacked GC Column
19010	Micropacked GC Column
19011	Micropacked GC Column
19011-853	Micropacked GC Column
19012	Micropacked GC Column

30m, 0.32mm ID, 1.20um
30m, 0.32mmID, 1.20um 5" cage for t
30m, 0.32mm ID, 1.80um
30m, 0.32mm ID, 1.8um w/5m 0.32mm Integra Guard
30m, 0.32mm ID, 1.80um 10m, 0.32mm guard built in
30m, 0.32mm ID, 1.80um on 5" HP6850 Cage
50m, 0.32mm ID, 0.50um
50m, 0.32mm ID, 0.50um with 5m Integra Guard Column
50m, 0.32mm ID, 0.50um w/5" HP6850 Cage
30m, 0.25mm ID, 0.25um
30m, 0.25mm ID, 0.25um with 5m Integra-Guard Column
30m, 0.25mm ID, 0.25um 5" Cage for HP6850
30m, 0.32mm ID, 0.25um
2 x 15m, 0.32mm ID, 0.25um
60m, 0.25mm ID, 0.25um
50m, 0.25mm ID, 0.25um
60m, 0.32mm ID, 0.25um
15m, 0.53mm ID, 0.50um
30m, 0.25mm ID, 0.50um
30m, 0.25mm ID, 0.50um with 5m Integra-Guard Column
30m, 0.32mm ID, 0.50um
30m, 0.53mm ID, 0.50um
60m, 0.25mm ID, 0.50um
60m, 0.32mm ID, 0.50um
60m, 0.53mm ID, 0.50um
15m, 0.53mm ID, 1.00um
30m, 0.25mm ID, 1.00um
30m, 0.32mm ID, 1.00um
30m, 0.53mm ID, 1.00um
30m, 0.53mm ID, 1.00um 4in star cage No guarantee for breakage
30m, 0.53mm ID, 1.00um 5in star cage no guarantee for breakage
60m, 0.25mm ID, 1.00um
60m, 0.25mm ID, 1.00um 5in cage for HP 6850
60m, 0.32mm ID, 1.00um
60m, 0.53mm ID, 1.00um
15m, 0.53mm ID, 1.50um
15m, 0.53mm ID, 1.50um 5" HP6850 Cage
30m, 0.53mm ID, 1.50um
60m, 0.53mm ID, 1.50um
15m, 0.32mm ID, 0.15um
15m, 0.32mm ID, 0.30um
Cap. Column 15m x 0.32mm
Cap. Column 30m x 0.32mm
Cap. Column 60m x 0.32mm
10m and 5m 0.32mm ID, 0.10um
5A Mole Sieve 80/100 1m, 1.00mm ID
5A Mole Sieve 80/100 2m, 1.00mm ID
5A Molesieve 80/100 2m 1.00mmID column in 2" diameter
5A MoleSieve 80/100 2m, 1.0mm ID, Special Config
5A Mole Sieve 80/100 1m, 0.75mm ID
5A Mole Sieve 80/100 1m, 0.75mm ID, SRI 8610C
5A Molesieve 80/100 1m .075mmID Pre Cond
5A Mole Sieve 80/100 2m, 0.75mm ID
5A Mole Sieve 80/100 2m, 0.75mm ID, SRI 8610C
5A Molesieve 80/100 2m 0.75mmID Pre Cond
13X Mole Sieve 80/100 1m, 1.00mm ID
13X Mole Sieve 80/100 2m, 1.00mm ID
13X Mole Sieve 80/100 1m, 0.75mm ID
13X Mole Sieve 80/100 2m, 0.75mm ID
13X Mole Sieve 80/100 2m, 0.75mmID SRI 8610C
HAYESEP S 100/120 1m, 1.00mm ID
HAYESEP S 100/120 2m, 1.00mm ID
HAYESEP S 100/120 1m, 0.75mm ID
HAYESEP S 100/120 2m, 0.75mm ID
Hayesep S 100/120 2m 0.75mmID Shimadzu 17A
HAYESEP R 100/120 1m, 1.00mm ID

(Ctrl F)
> Cat.#s

> Current System AUD Prices

