

19767	Rt-QS-BOND PLOT Column	15m, 0.25mm ID, 8um
19768	Rt-QS-BOND PLOT Column	30m, 0.25mm ID, 8um
19769	Rt-S-BOND PLOT Column	15m, 0.25mm ID, 8um
19770	Rt-S-BOND PLOT Column	30m, 0.25mm ID, 8um
19771	Rt-U-BOND PLOT Column	15m, 0.25mm ID, 8um
19772	Rt-U-BOND PLOT Column	30m, 0.25mm ID, 8um
19773	Rt-Msieve 5A PLOT Column	15m, 0.25mm ID, 20um
19775	Rt-Alumina BOND (Na2SO4)	30m, 0.25mm ID, 4um
19776	Rt-Alumina BOND (KCl)	30m, 0.25mm ID, 4um
19777	Rt-Alumina BOND/MAPD	30m, 0.53mm ID, 10um
19778	Rt-Alumina BOND/MAPD	50m, 0.53mm ID, 10um
19779	Rt-Alumina BOND/MAPD	30m, 0.32mm ID, 5um
19780	Rt-Alumina BOND/MAPD	50m, 0.32mm ID, 5um
19800	Micropacked GC Column	Rt-Sulfur 2m, 1/16" OD, 1.00mm ID
19801	Micropacked GC Column	Rt-Sulfur 1m, 1/16" OD, 1.00mm ID
19802	Micropacked GC Column	Rt-Sulfur 2m, 0.75mm ID
19803	Micropacked GC Column	Rt-Sulfur 1m, 0.75mm ID
19804	Micropacked Column	Rt-XLSulfur 1m, 1.00mm ID, 1/16" OD Column Does Not Include Ferrules and Nur
19804-895	Micropacked Column	Rt-XLSulfur 1m, 1.00mm ID, 1/16"OD SRI 8610C Column Does Not Include Ferru
19805	Micropacked GC Column	Rt-XLSulfur 2m, 1.00mm ID, 1/16" OD Column Does Not Include Ferrules and Nur
19805-293	Micropacked GC Column	Rt-XLSulfur 2m, 1.00mm ID, 1/16"OD 3.5inch Diameter Coil Column Does not incl
19806	Micropacked GC Column	Rt-XLSulfur 1m, 0.75mm ID, 0.95mm OD Column Does Not Include Ferrules and
19806-810	Micropacked Column	Rt-XLSulfur 1m, 0.75mm ID, 0.95mm OD, HP Column Does Not Include Ferrules
19806-900	Micropacked Column	Rt-XLSulfur 1m, 0.75mm ID, 0.95mm OD, PreCond Column Does Not Include Fer
19807	Micropacked Column	Rt-XLSulfur 2m, 0.75mm ID, 0.95mm OD Column Does Not Include Ferrules and
19807-811	Micropacked Column	Rt-XLSulfur 2m, 0.75mm ID, 0.95mm OD HP 6850 Cage Column Does Not Includ
19808	Micropacked GC Column	ShinCarbon ST 100/120 2m,1mmID,1/16"OD,Silco
19808-80090	Micropacked Column	ShinCarbon ST 100/120 2m 1mmID, 1/16" Silco Gen. Conf. NOC
19808-810	Micropacked Column	ShinCarbon ST 100/120 2m,1mmID,1/16"OD,Silco HP
19808-840	Micropacked Column	ShinCarbon ST 100/120 2m 1mmID, Silco PE AutoSys 8300,8400,8700 Claris
19808-850	Micropacked Column	ShinCarbon ST 100/120, 2m, 1mm ID, SILCO For Shimadzu 14A, 2014
19808-888	Micropacked Column	ShinCarbon ST 100/120 2m, 1mm ID Silco Customer Supplied Dimensions
19808-895	Micropacked Column	ShinCarbon ST 100/120 2m, 1mmID 1/16"OD Silco SRI 8610C
19808-900	Micropacked GC Column	ShinCarbon ST 100/120 2m, 1mmID, 1/16"OD, Silco Preconditioned
19808-901	Micropacked Column	ShinCarbon ST 100/120 2m,1mmID, 1/16"OD,Silco NOC
19809	Micropacked GC Column	ShinCarbon ST 100/120 1m,1mmID,1/16"OD,Silco
19809-810	Micropacked Column	ShinCarbon ST 100/120 1m 1/16" Silco HP
19809-81090	Micropacked Column	ShinCarbon ST 100/120 1m,1mmID,1/16"OD,Silco HP NOC
19810	Micropacked Column	ShinCarbon ST 100/120 1m,0.75mmID,0.95mmOD,Silco
19810-900	Micropacked Column	ShinCarbon ST 100/120 1m .95mmOD Silco Pre Cond
19908	Rtx-VMS Cap. Column	30m, 0.45mm ID, 2.55um
19909	Rtx-VMS Cap. Column	60m, 0.45mm ID, 2.55um
19915	Rtx-VMS Cap. Column	30m, 0.25mm ID, 1.40um
19915-6850	Rtx-VMS Cap. Column	30m, 0.25mm ID, 1.40um 5" Cage for HP6850
19916	Rtx-VMS Cap. Column	60m, 0.25mm ID, 1.40um
19916-600	Rtx-VMS Cap. Column	60m, 0.25mm ID, 1.40um Pack of 6
19916-6850	Rtx-VMS Cap. Column	60m, 0.25mm ID, 1.40um 5in cage for HP 6850
19919	Rtx-VMS Cap. Column	30m, 0.32mm ID, 1.80um
19919-6850	Rtx-VMS Cap. Column	30m, 0.32mm ID, 1.80um 5" HP6850 Cage
19920	Rtx-VMS Cap. Column	60m, 0.32mm ID, 1.80um
19974	Rtx-VMS Cap. Column	75m, 0.53mm ID, 3.0um
19985	Rtx-VMS Cap. Column	30m, 0.53mm ID, 3.0um
19988	Rtx-VMS Cap. Column	60m, 0.53mm ID, 3.0um
20101	Tool Set	Slide-Lok Tweezer & 15cm Ruler
20106	Tool	File, Needle, 4" Tapered 2 Pack
20108	Tool Set	Nylon Tube Brushes & Pipe Cleaners
20109	String	High Temperature String 10 meters
20110	Tool	Wrench, 1/4" X 5/16" Open End 2 Pack
20112	Tool Set	Brushes, SS Tube & SS Surface 4 Pack
20113	Tool	SS Jet Reamers, Pack of 6
20114	Tool	Mini Wool Puller/Inserter Tool 2pk
20116	Ceramic Scoring Wafers	with Holders, Pack of 5
20117	Tool	Septum Puller
20120	Tool Kit	FID & Injector Cleaning Kit
20121	Teflon Transfer Line	Precleaned, Pack of 5
20122	Mini Hand Drill	Includes one of each size: 0.4, 0.5, 0.8mm

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

 HROMalytic +61(0)3 9762 2034 ECHnology Pty Ltd		Australian Distributors Importers & Manufacturers www.chromtech.net.au
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA		

[Ctrl F]
> Cat.#s

> Current System AUD Prices

