

20409	Heat Sink
20411	Dual-Column Direct
20411-214.1	Dual-Column Direct
20412	Dual-Column Direct
20417	Connector, Vu-Union
20419	Connector, Vu-Union
20420	Ferrule, Vespel/Graphite
20421	Ferrule, Vespel/Graphite
20422	Ferrule, Vespel/Graphite
20423	Ferrule, Vespel/Graphite
20427	Connector, Vu-Union
20428	Connector, Vu-Union
20429	Connector, Presstight
20430	Connector, Presstight
20434	Connector, Vu-Union
20435	Dual-Column Mini-Lam
20436	Dual-Column Mini-Lam
20437	O-Rings
20445	Polyimide Resin
20446	Connector, Presstight
20446-261	Connector, Presstight
20447	Connector, Presstight
20447-261	Connector, Presstight
20448	Connector, Presstight
20448-261	Connector, Presstight
20449	Connector, Presstight
20469	Connector, Presstight
20474	Inlet Seals
20475	Inlet Seals
20476	Inlet Seals
20477	Inlet Seals
20480	Connector, Presstight
20482	Connector, Presstight
20483	Connector, Presstight
20484	Connector, Presstight
20485	Connector, Presstight
20486	Connector, Presstight
20487	Connector, Presstight
20504	Installation Fittings
20508	Dbl Gooseneck Drilled
20508-210.1	Dbl Gooseneck Drilled
20508-214.1	Dbl Gooseneck Drilled
20509	Dbl Gooseneck Drilled
20509-210.5	Dbl Gooseneck Drilled
20509-214.5	Dbl Gooseneck Drilled
20522	Replacement Scoring Wheel
20523	Restek Tubing Scorer
20535	Ferrule, Stainless Steel
20536	MXT Connector, Siltek
20537	MXT Y Connector, Siltek
20543	Capillary Column Adapter
20544	Capillary Column Adapter
20568	Ferrules, PEEK
20569	Ferrules, Graphite
20584	Sample Valve
20585	Sample Valve
20586	Sample Valve
20587	Sample Valve
20588	Sample Valve
20589	Sample Valve
20600	Trap, Oxygen
20601	Trap, Oxygen
20610	Regulator, Minicyl
20611	Regulator, Minicyl
20612	Rinsing Reservoir Kit
20613	Accessory

for Agilent 5890 GC Split/Splitless Inj
Injection Tee IP Deact., ea
Injection Tee Siltek Deact., ea
Injection Tee Kit IP Deact., Tee
Microbore Replacement Inserts Pack of 3 0.15/0.45mm
Capillary Replacement Inserts Pack of 3 0.33/0.74mm
Vu-Union 1/16" X 0.4mm ID Pack of 10
Vu-Union 1/16" X 0.5mm ID Pack of 10
Vu-Union 1/16" X 0.8mm ID Pack of 10
Vu-Union 1/16" X 0.3mm ID Pack of 10
Vacuum
Vacuum Replacement Inserts Pack of 3
Universal, Deactivated Pack of 5
Universal, Deactivated Pack of 25
Y Replacement Inserts Pack of 3
Direct Injection Tee IP Deact., ea
Direct Injection Tee Kit IP Deact. Tee
for Agilent GC's, 5-pk
5 Grams
Universal Angled, Pack of 5
Universal Angled, Pack of 5 Deactivated
Universal Angled, Pack of 25
Universal, Angled, Deactivated Pack of 25
Universal Angled, Pack of 100
Universal Angled, Pack of 100 Deactivated
Universal, Siltek Deactivated Pack of 25
Universal, Angled Y Siltek Deact Pack of 3
0.8mm Siltek Cross Disk Pack of 10 for HP GCs
0.8mm Siltek Cross Disk Pack of 2 for HP GCs
0.8mm Gold Plated Cross Disk Pack of 10 for HP GCs
0.8mm Gold Plated Cross Disk Pack of 2 for HP GCs
Universal, Siltek Deactivated Pack of 5
Universal, Angled Siltek Deactivated Pack of 5
Universal, Angled Siltek Deactivated Pack of 25
Universal, Angled Siltek Deactivated Pack of 100
Universal Y, Siltek Deactivated
Universal Y, Siltek Deactivated Pack of 3
Universal, Angled Y Siltek Deactivated
Vu-Tight
Uniliner, 4mm x 6.3x78.5 for Agilent GCs IP Deact., ea
Uniliner, 4mm x 6.3 x 78.5 for Agilent GCs Base Deact., ea
Uniliner, 4mm x 6.3x78.5 for Agilent GCs Siltek Deact., ea
Uniliner, 4mm x 6.3x78.5 for Agilent GCs IP Deact., 5pk
Uniliner, 4mm x 6.3 x 78.5 for Agilent GCs Base Deact., 5pk
Uniliner, 4mm x 6.3x78.5 for Agilent GCs Siltek Deact., 5pk
for the Restek MXT Tubing Scorer (Cat. # 20523)
for MXT Columns:0.25mm- 0.53mm ID, 0.5-0.8mm OD
0.32mm for MXT Connector, 10pk
for 0.32mmID Tubing
for 0.32mmID Tubing
Siltek Treated Adapter for use on Thermo Trace and Focus SSL GC Split/Splitless:
Siltek Treated Adapter for Thermo GCs, for use with M4 Ferrules
1/16", for use w/Secure Fit Fittings, 10-pk
1/16", for use w/Secure Fit Fittings, 10-pk
Sulfinert Coated,4 Port Manual, 1/16" Fittings 0.40mm bore
Sulfinert Coated,6 Port Manual, 1/16" Fittings 0.40mm bore
Sulfinert Coated,10 Port Manual, 1/16" Fittings 0.40mm bore
Replacement Rotor for 4 Port Sulfinert Coated Sample Valves
Replacement Rotor for 6 Port Sulfinert Coated Sample Valves
Replacement Rotor for 10 Port Sulfinert Coated Sample Valves
High Capacity, 1/4" Fittings
High Capacity, 1/8" Fittings
1/8" Female Fittings
1/4" Female Fittings
Complete Kit
Rinsing Reservoir

(Ctrl F)
> Cat.#s

> Current System AUD Prices



Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

		<p>Australian Distributors Importers & Manufacturers www.chromtech.net.au</p>
<p>Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA</p>		