

| | |
|-----------|--------------------------|
| 20618 | String |
| 20619 | Cage |
| 20620 | Cage |
| 20623 | Trap, Oxygen |
| 20624 | Trap, Oxygen |
| 20625 | Trap, Oxygen |
| 20626 | Trap, Hydrocarbon |
| 20631 | Septum Nut |
| 20634 | Regulator, Back Pressure |
| 20635 | Regulator, Back Pressure |
| 20636 | Trap, Hydrocarbon |
| 20637 | Trap, Hydrocarbon |
| 20638 | Trap, Moisture |
| 20643 | MSD Source Nut |
| 20645 | Inlet Kit |
| 20646 | Regulator, Brass |
| 20647 | Regulator, Brass |
| 20648 | Regulator, Brass |
| 20650 | Replacement Cable |
| 20652 | Replacement Cable |
| 20654 | Replacement Cable |
| 20655 | Replacement Cable |
| 20657 | Replacement Cable |
| 20658 | Replacement Cable |
| 20660 | Replacement Cable |
| 20662 | Regulator, SS |
| 20663 | Regulator, SS |
| 20664 | Regulator, SS |
| 20665 | Regulator, SS |
| 20666 | Regulator, SS |
| 20667 | Regulator, SS |
| 20668350 | Switchover System, Brass |
| 20668580 | Switchover System, Brass |
| 20668590 | Switchover System, Brass |
| 20670 | FID Jet |
| 20671 | FID Jet |
| 20672 | FID Jet |
| 20673 | FID Jet |
| 20674 | PID Lamp |
| 20675 | PID Lamp |
| 20676 | PID Lamp |
| 20677 | Generator, Nitrogen |
| 20677-551 | Generator, Nitrogen |
| 20678 | Electrolyte Solution |
| 20680 | Generator, Zero Air |
| 20680-550 | Generator, Zero Air |
| 20680-551 | Generator, Zero Air |
| 20681 | Generator, Zero Air |
| 20681-550 | Generator, Zero Air |
| 20682 | Generator, Zero Air |
| 20682-550 | Generator, Zero Air |
| 20682-551 | Generator, Zero Air |
| 20683 | Generator, Zero Air |
| 20683-550 | Generator, Zero Air |
| 20684 | Generator, Zero Air |
| 20684-550 | Generator, Zero Air |
| 20684-551 | Generator, Zero Air |
| 20685 | Trap, Molecular Sieve |
| 20686 | Trap, Molecular Sieve |
| 20688 | Generator, Hydrogen |
| 20697 | Generator, Nitrogen |
| 20697-550 | Generator, Nitrogen |
| 20697-551 | Generator, Nitrogen |
| 20697-552 | Generator, Nitrogen |
| 20698 | Trap, Split Vent |
| 20699 | Trap, Split Vent |

| |
|---|
| High Temperature String 450 Meters |
| Restek 7/8" Cage with 1m High Temp |
| Restek 1 1/2" Cage with 1m High Temp |
| Indicating, High Capacity 1/4" Fittings |
| Indicating, High Capacity 1/8" Fittings |
| Indicating, High Capacity Refill Cartridge For Cat #'s 20624/20623 Only |
| Carbon Refill |
| For HP GCs |
| Kit for HP GCs |
| for HP GCs |
| Indicating, 1/4" Fittings |
| Indicating, 1/8" Fittings |
| 1/4" Fittings |
| Pack of 2 |
| Dual Column 1/8" For HP GC |
| Single Stage, Ultra High Purity Inert Gas, CGA 580 |
| Single Stage, Ultra High Purity Hydrogen, CGA 350 |
| Single Stage, Ultra High Purity Air, CGA 590 |
| Discontinue When Stock is Depleted HP5890GC to 3396 Integrator |
| HP5890GC to Strip Chart/Intg |
| Discontinue When Stock is Depleted HP5890GC to 3396 Remote Start |
| Discontinue When Stock is Depleted HP3396 Intg Remote Start |
| HP5890GC Remote Start Cable |
| Discontinue When Stock is Depleted HP3396 Intg to Generic GC |
| Discontinue When Stock is Depleted Remote Start HP7673A/35900C |
| Dual Stage, Ultra High Purity Inert Gas, CGA 580 |
| Dual Stage, Ultra High Purity Hydrogen, CGA 350 |
| Dual Stage, Ultra High Purity Air, CGA 590 |
| Single Stage, Ultra High Purity Inert Gas, CGA 580 |
| Single Stage, Ultra High Purity Hydrogen, CGA 350 |
| Single Stage, Ultra High Purity Air, CGA 590 |
| Automatic Switchover System With Line Regulator For Use with H2, P5(CGA 350) |
| Automatic Switchover System With Line Regulator For Use with N2, He, Ar(CGA 350) |
| Automatic Switchover System With Line Regulator For Use with Air(CGA 590) |
| Capillary Adaptable Jet for Agilent 5890/6890/6850 GCs, (0.011" ID Tip) |
| Capillary Adaptable Jet for Agilent 5890/6890/6850 GCs, 3pk (0.011" ID Tip) |
| Siltek, Capillary Adaptable Jet for Agilent 5890/6890/6850 GCs, ea (0.011" ID Tip) |
| Siltek, Capillary Adaptable Jet for Agilent 5890/6890/6850 GCs, 3pk (0.011" ID Tip) |
| Polishing Kit |
| Model 108-10.0/10.6 |
| Model 103C |
| General Purpose N2-14 Does not Ship UPS or Fed Ex (Ships on Skid) Domestic (|
| General Purpose with European Cord Set Domestic Orders Drop Shipped from M. |
| for Models 75-32, 75-34, 75-36 H2PD-150, H2PD-300, 250mL HAZ FEES APPLY |
| 3500cc/min Capacity Model HPZA-3500 Dim-21" L18.5" H16" 41# 12-month warr |
| 3500cc/min Capacity with UK Cord Domestic Orders Drop Shipped from Manufac |
| 3500cc/min Capacity with European Cord Set Domestic Orders Drop Shipped from |
| 7000cc/min Capacity Model HPZA-7000 Domestic Orders Drop Ship from Manufa |
| 7000cc/min Capacity Model HPZA-7000 Dim-W21" L18.5 H16" 41# United Kingdc |
| 18,000cc/min Capacity Model HPZA-18000 Domestic Orders Drop Ship from Man |
| 18,000/min Capacity Model HPZA-18000-220 Dim W21" L18.5" H16" 41# United I |
| 18,000cc/min Capacity Dim W21" L18.5" H16" 41# w/European Cord Set Domesti |
| 30,000cc/min Capacity Model HPZA-30000 Domestic Orders Drop Ship from Man |
| 30,000cc/min Capacity Model HPZA-30000 Dim W21"L18.5"H16" 41# Domestic C |
| 1000cc/min Capacity MUST SHIP UPS Model 75-83NA Dim W15" L8" H17" 17# \ |
| 1000cc/min Capacity with UK Cord Domestic Orders Drop Shipped from Manufac |
| 1000cc/min Capacity with European Cord Set Domestic Orders Drop Shipped from |
| Rechargeable "S" 1/4" Fittings |
| Rechargeable "S" 1/8" Fittings |
| H2PD-300 Model, 300cc/min Capacity Ships via UPS Only, Domestic Orders Dro |
| Ultra High Purity Zero Grade UHPN2-1100 Does Not Ship UPS or Fed Ex (Ships |
| Ultra High Purity Zero Grade with UK Cord Domestic Orders Drop Shipped from M |
| Ultra High Purity Zero Grade with European Cord Set Domestic Orders Drop Ship |
| Ultra High Purity Zero Grade UHPN2-1100 w/IEC Connector Only- 230 VAC 50/60 |
| High Capacity |
| High Capacity, Pack of 5 |

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



HROMalytic +61(0)3 9762 2034

ECHnology Pty Ltd

Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

Australian Distributors

Importers & Manufacturers

www.chromtech.net.au

