



20994 Low Pressure Drop Liner
20994-209.1 Low Pressure Drop Liner
20994-210.1 Low Pressure Drop Liner
20994-211.1 Low Pressure Drop Liner
20994-213.1 Low Pressure Drop Liner
20994-214.1 Low Pressure Drop Liner
20994-216.1 Low Pressure Drop Liner
20995 Low Pressure Drop Liner
20995-209.5 Low Pressure Drop Liner
20995-211.5 Low Pressure Drop Liner
20995-213.5 Low Pressure Drop Liner
20995-214.5 Low Pressure Drop Liner
20996 Low Pressure Drop Liner
20997 Cyclo Dbl Gooseneck Liner
20997-210.25 Cyclo Dbl Gooseneck Liner
20997-214.25 Cyclo Dbl Gooseneck Liner
20998 Drilled Uniliner Liner
20998-200.25 Drilled Uniliner Liner
20998-214.25 Drilled Uniliner Liner
20999 Fused Silica Wool
21000 Hardware
21001 FID Ignitor
21002 Splitless Gooseneck Siltek
21003 Splitless Gooseneck Metal
21004 Split/Splitless Metal Liner
21004-205 Split/Splitless Metal Liner
21004-231.5 Split/Splitless Metal Lnr
21005 Uniliner Liner
21005-214.1 Uniliner Liner
21006 Uniliner Liner
21006-205 Uniliner Liner
21007 Ferrule, Graphite
21008 Ferrules, Graphite
21009 Inlet Seals
21010 Inlet Seals
21011 Inlet Seals
21012 Inlet Seals
21015 EZ No-Vent Ferrules
21016 EZ No-Vent Ferrules
21018 EZ-vent Transfer Line
21020 Split Precision Liner
21020-210.1 Split Precision Liner
21020-213.1 Split Precision Liner
21021 Split Precision Liner
21021-203.5 Split Precision Liner
21021-211.5 Split Precision Liner
21021-213.5 Split Precision Liner
21022 Split Precision Liner
21022-211.1 Split Precision Liner
21022-213.1 Split Precision Liner
21022-214.1 Split Precision Liner
21022-230.1 Split Precision Liner
21022-231.1 Split Precision Liner
21023 Split Precision Liner
21023-203.5 Split Precision Liner
21023-205 Split Precision Liner
21023-211.5 Split Precision Liner
21023-213.5 Split Precision Liner
21023-214.5 Split Precision Liner
21023-231.5 Split Precision Liner
21024 Split Precision Liner
21024-211.1 Split Precision Liner
21024-231.1 Split Precision Liner
21025 Split Precision Liner
21025-205 Split Precision Liner
21025-211.5 Split Precision Liner

4mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, ea
4mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, ea
4mm x 6.3 x 78.5 for Agilent GCs Base Deact., w/Deact. Wool, ea
4mm x 6.3 x 78.5 for Agilent GCs Base Deact. w/ Base Deact Wool, Ea
4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/Deact. Wool, ea
4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., ea
4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/CarboFrit, ea
4mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, 5pk
4mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/CarboFrit, 5pk
4mm x 6.3 x 78.5 for Agilent GCs Base Deact., w/Base Deact. Wool, 5pk
4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/Deact. Wool, 5pk
4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., 5pk
4mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, 25pk
4mm x 6.3 x 78.5 for Agilent GCs IP Deact., 25pk
4mm x 6.3 x 78.5 for Agilent GCs Base Deact., 25pk
4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., 25pk
w/hole on top 4mm x 6.3 x 78.5 for Agilent GCs IP Deact., 25pk
w/hole on top 4mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, 25pk
w/hole on top 4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., 25pk
Base Deactivated 10 g
FID flow measuring adapter
for Agilent 5890/6890/6850/7890 GCs
Metal Liner, 3.8mm x 5.0 x 54 for Varian GCs, 5pk
Liner, 3.5mm x 5.0 x 95 for Shimadzu GCs Siltek Deact., w/Deact. Wool, 5pk
5.0mm x 8.0 x 105 for Thermo GCs Siltek Deact., w/Deact. Wool, 5pk
5.0mm x 8.0 x 105 for Thermo GCs Siltek Deact., 5pk
5.0mm x 8.0 x 105 for Thermo GCs IP Deact., w/ SV Wool, 5pk
5mm x 8.0 x 105 for Thermo GCs IP Deact., w/Deact. Wool, ea
5mm x 8.0 x 105 for Thermo GCs Siltek Deact., ea
5mm x 8.0 x 105 for Thermo GCs IP Deact., w/Deact. Wool, 5pk
5mm x 8.0 x 105 for Thermo GCs IP Deact, No Wool, 5pk
0.5mm Compact, for Agilent GCs, 10-pk
0.5mm Compact, for Agilent GCs, 50-pk
1.2mm Gold Plated Cross Disk for HP 5890/6890 GCs, 2pk
1.2mm Gold Plated Cross Disk for HP 5890/6890 GCs, 10pk
1.2mm Siltek Cross Disk for HP 5890/6890 GCs, 2pk
1.2mm Siltek Cross Disk for HP 5890/6890 GCs, 10pk
for connecting Cap. Col. to Connector 0.4mmID, 2pk
for connecting Cap. Col. to Connector 0.5mm ID, 2pk
Replacement EZ-vent deactivated transfer line 100um: 3 feet
3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., w/Deact. Wool, ea
3.5mm x 5.0 x 95 for Shimadzu GCs Base Deact., ea
3.5mm x 5.0 x 95 for Shimadzu GCs Siltek Deact., w/Deact. Wool, ea
3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., w/Deact. Wool, 5pk
3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., w/ Double Deact. Wool, 5pk
3.5mm x 5.0 95 for Shimadzu GCs Base Deact., w/Base Deact. Wool, 5pk
3.5mm x 5.0 x 95 for Shimadzu GCs Siltek Deact., w/Deact. Wool, 5pk
4mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, ea
4mm x 6.3 x 78.5 for Agilent GCs Base Deact., w/Base Deact. Wool, ea
4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/Deact. Wool, ea
4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., ea
4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/Base Deact. Wool, ea
4mm x 6.3 x 78.5 for Agilent GCs IP Deact., SV Wool, ea
4mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, 5pk
4mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/Triple Deact. Wool, 5pk
4mm x 6.3 x 78.5 for Agilent GCs IP Deact., No Wool, 5pk
4mm x 6.3 x 78.5 for Agilent GCs Base Deact., w/Base Deact. Wool, 5pk
4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/Deact. Wool, 5pk
4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., 5pk
4mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/ SV Wool, 5pk
3.4mm x 5.0 x 54, for Varian GCs IP Deact., w/Deact. Wool, ea
3.4mm x 5.0 x 54, for Varian GCs Base Deact., w/Base Deact. Wool, ea
3.4mm x 5.0 x 54, for Varian GCs IP Deact., w/Deact. Wool, Ea
3.4mm x 5.0 x 54, for Varian GCs IP Deact., w/Deact. Wool, 5pk
3.4mm x 5.0 x 54, for Varian GCs IP Deact, No Wool, 5pk
3.4mm x 5.0 x 54, for Varian GCs Base Deact., w/Base Deact. Wool, 5pk

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

		+61(0)3 9762 2034 Australian Distributors Importers & Manufacturers www.chromtech.net.au
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA		