

21025-213.5 Split Precision Liner
 21026 Split Precision Liner
 21026-211.1 Split Precision Liner
 21027 Split Precision Liner
 21027-211.5 Split Precision Liner
 21027-213.5 Split Precision Liner
 21028 Splitless Precision Liner
 21028-211.1 Splitless Precision Liner
 21028-213.1 Splitless Precision Liner
 21029 Splitless Precision Liner
 21029-211.5 Splitless Precision Liner
 21029-213.5 Splitless Precision Liner
 21029-231.5 Splitless Precision Liner
 21030 Split Precision Liner
 21031 Split Precision Liner
 21032 Low Pressure Drop
 21032-211.1 Low Pressure Drop Liner
 21032-213.1 Low Pressure Drop Liner
 21032-214.1 Low Pressure Drop Liner
 21032-231.1 Low Pressure Drop
 21033 Low Pressure Drop
 21033-205 Low Pressure Drop Liner
 21033-211.5 Low Pressure Drop Liner
 21033-213.5 Low Pressure Drop Liner
 21033-214.5 Low Pressure Drop Liner
 21033-231.5 Low Pressure Drop Liner
 21034 Gauge
 21035 MCS Bypass Line
 21036 Ferrule, Graphite
 21037 Ferrule, Graphite
 21038 Ferrule, Graphite
 21039 Ferrule, Vespel/Graphite
 21040 Fingertight Nut, Knurled
 21041 Fingertight Nut, Knurled
 21042 Fingertight Nut, Knurled
 21043 EZ No-Vent Ferrules
 21044 Capillary Column Caps
 21045 Split Liner w/Glass Frit
 21045-210.1 Split Liner w/Glass Frit
 21045-214.1 Split Liner w/Glass Frit
 21046 Split Liner w/Glass Frit
 21046-200.5 Split Liner w/Glass Frit
 21046-210.5 Split Liner w/Glass Frit
 21046-214.5 Split Liner w/Glass Frit
 21047 GC Column Hanger
 21050 1.0ml Micro-Vial,Accuform
 21051 3.0ml Micro-Vial,Accuform
 21052 Uniliner Liner
 21052-214.1 Uniliner Liner
 21053 Uniliner Liner
 21053-214.5 Uniliner Liner
 21054 Drilled Uniliner, Hole
 21054-200.1 Drilled Uniliner, Hole
 21054-210.1 Drilled Uniliner, Hole
 21054-211.1 Drilled Uniliner, Hole
 21054-213.1 Drilled Uniliner, Hole
 21054-214.1 Drilled Uniliner, Hole
 21054-216.1 Drilled Uniliner, Hole
 21054-231.1 Drilled Uniliner, Hole
 21055 Drilled Uniliner, Hole
 21055-200.5 Drilled Uniliner, Hole
 21055-202.5 Drilled Uniliner, Hole
 21055-210.5 Drilled Uniliner, Hole
 21055-211.5 Drilled Uniliner, Hole
 21055-213.5 Drilled Uniliner, Hole
 21055-214.5 Drilled Uniliner, Hole

Page 66
 3.4mm x 5.0 x 54, for Varian GCs Silt
 4mm x 6.2 x 92.1 for PE GCs IP Deact
 4mm x 6.2 x 92.1 for PE GCs Base Deact., w/Base Deact. Wool, ea
 4mm x 6.2 x 92.1 for PE GCs IP Deact., w/Deact. Wool, 5pk
 4mm x 6.2 x 92.1 for PE GCs Base Deact. w/Base Deact. Wool, 5pk
 4mm x 6.2 x 92.1 for PE GCs Siltek Deact., w/Deact. Wool, 5pk
 5mm x 8.0 x 105 for Thermo GCs IP Deact., w/Deact Wool, ea
 5mm x 8.0 x 105 for Thermo GCs Base Deact., w/Base Deact. Wool, ea
 5mm x 8.0 x 105 for Thermo GCs Siltek Deact., w/Deact. Wool, ea
 5mm x 8.0 x 105 for Thermo GCs IP Deact., w/Deact. Wool, 5pk
 5mm x 8.0 x 105 for Thermo GCs Base Deact., w/Base Deact. Wool, 5pk
 5mm x 8.0 x 105 for Thermo GCs Siltek Deact., w/Deact. Wool, 5pk
 5mm x 8.0 x 105 for Thermo GCs IP Deact., w/ SV Wool, 5pk
 4mm x 6.3 x 72 for Varian GCs IP Deact., w/Deact. Wool, ea
 4mm x 6.3 x 72 for Varian GCs IP Deact., w/Deact. Wool, 5pk
 Precision Liner 4mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, ea
 4mm x 6.3 x 78.5 for Agilent GCs Base Deact., w/Base Deact. Wool, ea
 4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/Deact. Wool, ea
 4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., ea
 Precision Liner 4mm x 6.3 x 78.5 for Agilent GC's IP Deact., SV Wool, ea
 Precision Liner 4mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, 5pk
 4mm x 6.3 x 78.5 for Agilent GCs IP Deact., No Wool, 5pk
 4mm x 6.3 x 78.5 for Agilent GCs Base Deact., w/Base Deact. Wool, 5pk
 4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/Deact. Wool, 5pk
 4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact, 5pk
 4mm x 6.3 x 78.5 for Agilent GCs IP Deact., SV Wool, 5pk
 Capillary Installation Gauge for Agilent style fittings (Compact Ferrules)
 Moisture Control System Bypass Line for Tekmar 3000 P&T
 0.4mm Encapsulated Ferrule Pack of 10
 0.5mm Encapsulated Ferrule Pack of 10
 0.8mm Encapsulated Ferrule Pack of 10
 1/32" x 0.4mm ID Pack of 5
 HP style nut for use with compact ferrules Pack of 2
 HP style nut for use with standard 1/16" ferrules Pack of 2
 for use with std. 1/16" compression fittings Pack of 2
 for Connecting Transfer Line to EZ No-Vent Connector, 0.4mm ID, 2-pk
 Color Coded Glass Caps, 10 sets (20 caps)
 4mm x 6.3 x 78.5 for Varian GCs IP Deact., ea
 4mm x 6.3 x 78.5 for Varian GCs Base Deact., ea
 4mm x 6.3 x 78.5 for Varian GCs Siltek Deact., ea
 4mm x 6.3 x 78.5 for Varian GCs IP Deact., 5pk
 4mm x 6.3 x 78.5 for Varian GCs Deact. Wool, 5 pk
 4mm x 6.3 x 78.5 for Varian GCs Base Deact., 5pk
 4mm x 6.3 x 78.5 for Varian GCs Siltek Deact., 5pk
 GC Column Hanger with 4 Col. Caps Pack of 2
 Borosilicate Glass, Screw Thread Graduated, With Open Top Closure Pack of 12
 Borosilicate Glass, Screwed Thread, Graduated, With Open Top Closure Pack of
 1mm x 6.3 x 78.5 for Agilent GCs IP Deact., ea
 1mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., ea
 1mm x 6.3 x 78.5 for Agilent GCs IP Deact., 5pk
 1mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., 5pk
 on Top, 4.0mm x 6.3 x 78.5 for Agilent GCs IP Deact., ea
 on Top, 4.0mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, ea
 on Top, 4.0mm x 6.3 x 78.5 for Agilent GCs Base Deact., ea
 on Top, 4.0mm x 6.3 x 78.5 for Agilent GCs Base Deact., w/Base Deact Wool, ea
 on Top, 4.0mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/Deact. Wool, ea
 on Top, 4.0mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., ea
 on Top, 4.0mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/CarboFrit, ea
 on Top, 4.0mm x 6.3 x 78.5 for Agilent GC's IP Deact., SV Wool, Ea
 on Top, 4.0mm x 6.3 x 78.5 for Agilent GCs IP Deact., 5pk
 on Top, 4.0mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, 5pk
 on Top, 4.0mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/Glass Wool, 5pk
 on Top, 4.0mm x 6.3 x 78.5 for Agilent GCs Base Deact., 5pk
 on Top, 4.0mm x 6.3 x 78.5 for Agilent GCs Base Deact., w/Base Deact. Wool, 5pk
 on Top, 4.0mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/Deact. Wool, 5pk
 on Top, 4.0mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., 5pk



Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

HROMalytic +61(0)3 9762 2034
ECHnology Pty Ltd
 Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

Australian Distributors
 Importers & Manufacturers
www.chromtech.net.au