

21055-231.5	Drilled Uniliner, Hole	on Top, 4.0mm x 6.3 x 78.5 for Agilen
21058	Ferrule, Graphite	1/16" x 1.0mm ID Pack of 10
21059	Ferrule, Graphite	Compact 1.0mm ID Pack of 10
21060	Ferrule, Graphite	1/16" x 1.6mm ID Pack of 10
21061	Ferrule, Graphite	Compact 1.6mm ID Pack of 10
21065	Micropacked Install Kit	for 1/16" x 1mm ID columns valve application
21066	Micropacked Install Kit	direct injection for 1/16" x 1mm ID columns
21067	Packed Col. Install Kit	Valve Application for 1/8"OD (2mmID) Packed Column
21073	Micro I Liner	1mm x 6.0 x 243 for APEX GCs IP Deact., ea
21074	MIDI II Liner	2mm x 6.0 x 243 for APEX GCs IP Deact., ea
21074-214.1	MIDI II Liner	2mm x 6.0 x 243 for APEX GCs Siltek Deact., ea
21075	Mega IV Liner	4mm x 6.0 x 243 for APEX GCs IP Deact., ea
21075-214.1	Mega IV Liner	4mm x 6.0 x 243 for APEX GCs Siltek Deact., ea
21076	Nut Driver	1/4" Nut Driver
21077	Splitless Liner	2mm x 6.5 x 78.5 for Varian GCs IP Deact., w/Deact Wool, 5pk
21077-205	Splitless Liner	2mm x 6.5 x 78.5 for Varian GCs IP Deact., No Wool, 5pk
21077-214.5	Splitless Liner	2mm x 6.5 x 78.5 for Varian GCs Siltek Deact., 5pk
21079	Split Liner	4mm x 6.3 x 78.5 for Varian GCs IP Deact., w/Deact. Wool, 5pk
21079-205	Split Liner	4mm x 6.3 x 78.5 for Varian GCs IP Deact., 5pk
21079-209.5	Split Liner	4mm x 6.3 x 78.5 for Varian GCs IP Deact., w/Carbofrit, 5pk
21079-213.5	Split Liner	4mm x 6.3 x 78.5 for Varian GCs Siltek Deact., w/Deact. Wool, 5pk
21080	Split/Splitless Metal Liner	1.0mm x 2.75 x 120 for Thermo GCs Siltek Deact., ea
21081	Split/Splitless Metal Liner	1.0mm x 2.75 x 120 for Thermo GCs Siltek Deact., 5pk
21082	Split/Splitless Metal Liner	2.0mm x 2.75 x 120 for Thermo GCs Siltek Deact., ea
21082-200.1	Split/Splitless Metal	Liner 2.0mm x 2.75 x 120 for Thermo GCs Siltek Deact., w/Deact. Wool, ea
21083	Split/Splitless Metal Liner	2.0mm x 2.75 x 120 for Thermo GCs Siltek Deact., 5pk
21083-200.5	Split/Splitless Metal Liner	2.0mm x 2.75 x 120 for Thermo GCs Siltek Deact., w/Deact. Wool, 5pk
21083-203.5	Split/Splitless Metal Lin	2.0mm x 2.75 x 120 for Thermo GCs Siltek Deact., Dbl Deact. Wool, 5pk
21083-209.5	Split/Splitless Metal Liner	2.0mm x 2.75 x 120 for Thermo GCs Siltek Deact., w/CarboFrit, 5pk
21083-231.5	Split/Splitless Metal Lin	2.0mm x 2.75 x 120 for Thermo GCs Siltek Deact., w/ SV Wool, 5pk
21101	FastPack Kit	Inlet Maintenance Kit HP 4mm Splitless, Pack of 5 Kits
21101	FastPack Kit	Inlet Maintenance Kit HP 4mm Splitless, Pack of 5 Kits
21102	FastPack Kit	Inlet Maintenance Kit HP 4mm Gooseneck Splitless Pack of 5 Kits
21102	FastPack Kit	Inlet Maintenance Kit HP 4mm Gooseneck Splitless Pack of 5 Kits
21102	FastPack Kit	Inlet Maintenance Kit HP 4mm Gooseneck Splitless Pack of 5 Kits
21104	FastPack Kit	Inlet Maintenance Kit HP 4mm split w/FS Wool Pack of 5 Kits
21104	FastPack Kit	Inlet Maintenance Kit HP 4mm split w/FS Wool Pack of 5 Kits
21104	FastPack Kit	Inlet Maintenance Kit HP 4mm split w/FS Wool Pack of 5 Kits
21105	Vu2 Union	Fits 0.18/0.28mm ID Columns
21106	Vu2 Union	Fits 0.32mm ID Columns
21107	Vu2 Union	Fits 0.45/0.53mm ID Columns
21108	Knurled Nut	Pack of 2
21109	Moisture Control Bypass	Line for Tekmar 3100 P&T
21110	SPME Liner	0.75mm x 6.35 x 78.5 for Agilent GCs IP Deact., ea
21110-210.1	SPME Liner	0.75mm x 6.35 x 78.5 for Agilent GCs Base Deact., ea
21110-214.1	SPME Liner	0.75mm x 6.35 x 78.5 for Agilent GCs Siltek Deact., ea
21111	SPME Liner	0.75mm x 6.35 x 78.5 for Agilent GCs IP Deact., 5pk
21111-210.5	SPME Liner	0.75mm x 6.35 x 78.5 for Agilent GCs Base Deact., 5pk
21111-214.5	SPME Liner	0.75mm x 6.35 x 78.5 for Agilent GCs Siltek Deact., 5pk
21112	SPME Liner	0.75mm x 6.30 x 74 for Varian GCs IP Deact., ea
21113	SPME Liner	0.75mm x 6.30 x 74 for Varian GCs IP Deact., 5pk
21113-214.5	SPME Liner	0.75mm x 6.30 x 74 for Varian GCs Siltek Deact, 5pk
21114	Split Liner	1mm x 2.75 x 120 for Thermo GCs IP Deact., ea
21114-210.1	Split Liner	1mm x 2.75 x 120 for Thermo GCs Base Deact., ea
21114-214.1	Split Liner	1mm x 2.75 x 120 for Thermo GCs Siltek Deact.,ea
21115	Split Liner	1mm x 2.75 x 120 for Thermo GCs IP Deact., 5pk
21115-210.5	Split Liner	1mm x 2.75 x 120 for Thermo GCs Base Deact., 5pk
21115-214.5	Split Liner	1mm x 2.75 x 120 for Thermo GCs Siltek Deact., 5pk
21116	Split Liner	2mm x 2.75 x 120 for Thermo GCs IP Deact., ea
21116-200.1	Split Liner	2mm x 2.75 x 120 for Thermo GCs IP Deact., w/Deact. Wool, ea
21116-210.1	Split Liner	2mm x 2.75 x 120 for Thermo GCs Base Deact., ea
21116-211.1	Split Liner	2mm x 2.75 x 120 for Thermo GCs Base Deact, w/Base Deact. Wool, ea
21116-213.1	Split Liner	2mm x 2.75 x 120 for Thermo GCs Siltek Deact., w/Deact. Wool, ea
21116-214.1	Split Liner	2mm x 2.75 x 120 for Thermo GCs Siltek Deact., ea
21116-216.1	Split Liner	2mm x 2.75 x 120 for Thermo GCs Siltek Deact., w/CarboFrit, ea

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



HROMalytic +61(0)3 9762 2034
ECHnology Pty Ltd

Australian Distributors
 Importers & Manufacturers
www.chromtech.net.au

Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

[Ctrl F]
> Cat.#s

> Current System AUD Prices

