

21273 Splitless Liner
21273-210.5 Splitless Liner
21274 Splitless Liner
21275 Syringe, SGE
21276 Syringe
21277 Syringe
21278 Syringe
21279 Syringe
21283 Syringe
21284 Plunger Assembly, SGE
21285 Open Top Drilled Uniliner
21285-200.1 Open Top Drilled Uniliner
21285-210.1 Open Top Drilled Uniliner
21285-213.1 Open Top Drilled Uniliner
21285-214.1 Open Top Drilled Uniliner
21286 Open Top Drilled Uniliner
21286-200.5 Open Top Drilled Uniliner
21286-210.5 Open Top Drilled Uniliner
21286-214.5 Open Top Drilled Uniliner
21287 Open Top Drilled Uniliner
21287-214.1 Open Top Drilled Uniliner
21288 Open Top Drilled Uniliner
21288-214.5 Open Top Drilled Uniliner
21288-231.5 Open Top Drilled Uniliner
21289 Gooseneck Drilled
21289-214.1 Gooseneck Drilled
21290 Gooseneck Drilled
21290-214.5 Gooseneck Drilled
21291 Gooseneck Drilled
21292 Gooseneck Drilled
21293 Drilled Uniliner Liner
21294 Drilled Uniliner Liner
21295 Gooseneck Drilled
21296 Gooseneck Drilled
21297 Gooseneck Drilled
21298 Gooseneck Drilled
21299 Septa Holder
21301 ECD/FID Repl. Fitting Kit
21302 ECD Siltek Metal Liner
21303 DI Sleeve Adaptor Kit
21305 Inlet Seals
21306 Inlet Seals
21307 Inlet Seals
21308 Inlet Seals
21309 Septum Nut
21311 Fingertight Nut
21312 Fingertight Nut
21313 MSD Conversion Fitting
21314 MSD Conversion Fitting
21315 Inlet Seals
21316 Inlet Seals
21317 Inlet Seals
21318 Inlet Seals
21319 Inlet Seals
21320 Inlet Seals
21321 Wrench, Cylinder Valve
21322 Wrench, Cylinder Valve
21323 EZ No-Vent Connector Kit
21325 GC Installation Kit
21327 Regulator Manifold
21333 Single Cylinder Holder
21334 Flash Arrestor, Brass
21336 Fitting, CGA 580
21337 Fitting, CGA 350
21338 Fitting, CGA 590
21339 Flexible Hose, SS

1mm x 6.20 x 92.1 for PE GCs IP Deact., ea
1mm x 6.20 x 92.1 for PE GCs Base Deact., ea
1mm x 6.20 x 92.1 for PE GCs IP Deact., ea
500 ml Jumbo
1000 ml Jumbo
2000 ml Jumbo
Spare Plunger O-Ring 500 ml
Spare Plunger O-Ring 1000 ml
Luer-Lock Valve Adaptor 2pk
SGE Gas Tight RN Syringe 10 uL, Teflon Tip, 2pk
Liner, Hole on Top, 3.5mm x 5.0 x 95 for Shimadzu GCs, IP Deact., ea
Liner, Hole on Top, 3.5mm x 5.0 x 95 for Shimadzu GCs, IP Deact., w/Deact. Wor
Liner, Hole on Top, 3.5mm x 5.0 x 95 for Shimadzu GCs, Base Deact., ea
Liner, Hole on Top, 3.5mmx5.0x95 for Shimadzu GCs, Siltek Deact., w/Deact Wor
Liner, Hole on Top, 3.5mm x 5.0 x 95 for Shimadzu GCs, Siltek Deact, ea
Liner, Hole on Top, 3.5mm x 5.0 x 95 for Shimadzu GCs, IP Deact., 5pk
Liner, Hole on Top, 3.5mm x 5.0 x 95 for Shimadzu GCs, IP Deact., w/Deact. Wor
Liner, Hole on Top, 3.5mm x 5.0 x 95 for Shimadzu GCs, Base Deact., 5pk
Liner, Hole on Top, 3.5mm x 5.0 x 95 for Shimadzu GCs, Siltek Deact, 5pk
Liner, Hole on Btm, 3.5mm x 5.0 x 95 for Shimadzu GCs, IP Deact., ea
Liner, Hole on Btm, 3.5mm x 5.0 x 95 for Shimadzu GCs, Siltek Deact., ea
Liner, Hole on Btm, 3.5mm x 5.0 x 95 for Shimadzu GCs, IP Deact., 5pk
Liner, Hole on Btm, 3.5mm x 5.0 x 95 for Shimadzu GCs, Siltek Deact., 5pk
Liner, Hole on Btm, 3.5mm x 5.0 x 95 for Shimadzu GCs, IP Deact., w/ SV Wool, 5
Uniliner Liner, Hole on Top, 3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., ea
Uniliner Liner, Hole on Top, 3.5mm x 5.0 x 95 for Shimadzu GCs Siltek Deact., ea
Uniliner Liner, Hole on Top, 3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., 5pk
Uniliner Liner, Hole on Top, 3.5mm x 5.0 x 95 for Shimadzu GCs Siltek Deact., 5p
Uniliner Liner, Hole on Bottom, 3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., ea
Uniliner Liner, Hole on Bottom, 3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., 5pk
Hole on Bottom, 4mm x 6.2 x 92.1 for PE GCs, IP Deact., ea
Hole on Bottom, 4mm x 6.2 x 92.1 for PE GCs, IP Deact., 5pk
Uniliner Liner, Hole on Top, 4mm x 6.2 x 92.1 for PE GCs IP Deact., ea
Uniliner Liner, Hole on Top, 4mm x 6.2 x 92.1 for PE GCs IP Deact., 5pk
Uniliner Liner, Hole on Bottom, 4mm x 6.2 x 92.1 for PE GCs IP Deact., ea
Uniliner Liner, Hole on Bottom, 4mm x 6.2 x 92.1 for PE GCs IP Deact., 5pk
for Thermo Trace and Focus SSL
with Flow Manifold Connection
Replacement, For Agilent ECD/FID, 2pk
For HP5890 Packed Column GC
1.2mm Gold Plated Pack of 2 For HP GCs
1.2mm Gold Plated Pack of 10 For HP GCs
1.2mm Siltek 2pk For HP GCs
1.2mm Siltek 10pk For HP GCs
Needle Guide, 26 Gauge For HP GCs
for HP Compact Ferrules for use w/HP GCs
For Standard Ferrules For HP GCs
Ring Seal 2pk

0.8mm SS Pack of 2 For HP GCs
0.8mm SS Pack of 10 For HP GCs
0.8mm Gold Plated Pack of 2 For HP GCs
0.8mm Gold Plated, Pack of 10 For HP GCs
0.8mm Siltek 2pk For HP GCs
0.8mm Siltek 10pk For HP GCs

Universal
for Agilent 5971/5972/5973 or 5975 GC/ MS

Stainless Steel CGA 580 (N2,He,Ar) Protocol Station for Single or Dual Stage Re
Wall Mounted
For Flammable Gases
Nickel Plated Brass, 1/4"NPT Inert Gas
Nickel Plated Brass, 1/4"NPT Hydrogen
Nickel Plated Brass, 1/4"NPT Air
36" Long

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



HROMalytic +61(0)3 9762 2034
ECHnology Pty Ltd
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

Australian Distributors
Importers & Manufacturers
www.chromtech.net.au

