

21402-24 Sample Cylinder Valve  
 21402-25 Sample Cylinder Valve  
 21402-26 Sample Cylinder Valve  
 21402-27 Sample Cylinder Valve  
 21402-28 Sample Cylinder Valve  
 21402-29 Sample Cylinder Valve  
 21402-3 Sample Cylinder Valve  
 21402-30 Sample Cylinder Valve  
 21402-31 Sample Cylinder Valve  
 21402-32 Sample Cylinder Valve  
 21402-33 Sample Cylinder Valve  
 21402-34 Sample Cylinder Valve  
 21402-35 Sample Cylinder Valve  
 21402-4 Sample Cylinder Valve  
 21402-5 Sample Cylinder Valve  
 21402-6 Sample Cylinder Valve  
 21402-7 Sample Cylinder Valve  
 21402-8 Sample Cylinder Valve  
 21402-9 Sample Cylinder Valve  
 21409 PTV Seal  
 21468 Drilled Uniliner Liner  
 21468-213.1 Drilled Uniliner Liner  
 21468-214.1 Drilled Uniliner Liner  
 21469 Drilled Uniliner Liner  
 21469-200.5 Drilled Uniliner Liner  
 21469-214.5 Drilled Uniliner Liner  
 21470 Drilled Uniliner Liner  
 21470-200.1 Drilled Uniliner Liner  
 21470-209.1 Drilled Uniliner Liner  
 21470-213.1 Drilled Uniliner Liner  
 21470-214.1 Drilled Uniliner Liner  
 21471 Drilled Uniliner Liner  
 21471-200.5 Drilled Uniliner Liner  
 21471-213.5 Drilled Uniliner Liner  
 21471-214.5 Drilled Uniliner Liner  
 21472 Alumaseal Ferrule  
 21473 Alumaseal Ferrule  
 21474 Alumaseal Ferrule  
 21475 O-rings, Graphite  
 21476 Graphite O-rings  
 21487 Pro ezGC Software  
 21500 Tubing, Stainless Steel  
 21501 Tubing, Stainless Steel  
 21502 Tubing, Stainless Steel  
 21503 Tubing, Stainless Steel  
 21504 Tubing, Stainless Steel  
 21505 Tubing, Stainless Steel  
 21506 Tubing, Stainless Steel  
 21507 Tubing, Stainless Steel  
 21508 Tubing, Stainless Steel  
 21509 Tubing, Stainless Steel  
 21510 Tubing, Stainless Steel  
 21511 Tubing, Stainless Steel  
 21512 Tubing, Stainless Steel  
 21512-281 Tubing, Stainless Steel  
 21513 Tubing, Stainless Steel  
 21514 Tubing, Stainless Steel  
 21515 Tubing, Stainless Steel  
 21516 Tubing, Stainless Steel  
 21517 Tubing, Stainless Steel  
 21540 Sulfinert Fitting  
 21541 Sulfinert Fitting  
 21542 Sulfinert Fitting  
 21543 Sulfinert Fitting  
 21544 Sulfinert Fitting  
 21545 Sulfinert Fitting

Page 72  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tul  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tul  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tube 3-3/8 inches  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tube 5-1/4 inches  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tube 2-1/2 inches  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tube 3.0 inches  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tube 1-1/2 inches  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tube 1.0 inches  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tube 1-1/2 inches  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tube 3-3/8 inches  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tube 3-3/8 inches  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tube 3-3/8 inches  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tube 2.0 inches  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tube 2-3/8 inches  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tube 2-1/4 inches  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tube 1-1/2 inches  
 Sulfinert, 1/4"NPTx1/4"NPT w/Dip Tube 1-3/4 inches  
 Agilent 6890 PTV Silver Seal, 5pk  
 Hole on Bottom, 4mm x 6.3 x 78.5 for Varian GCs, IP Deact., ea  
 Hole on Bottom, 4mm x 6.3 x 78.5 for Varian GCs, Siltek, Deact. Wool, Ea  
 Hole on Bottom, 4mm x 6.3 x 78.5 For Varian GCs, Siltek Deact., Ea  
 Hole on Bottom, 4mm x 6.3 x 78.5 for Varian GCs, IP Deact., 5pk  
 Hole on Bottom, 4mm x 6.3 x 78.5 for Varian GCs, IP Deact., w/Deact. Wool, 5pk  
 Hole on Bottom, 4mm x 6.3 x 78.5 for Varian GCs, Siltek Deact., 5pk  
 Hole on Top, 4mm x 6.3 x 78.5 for Varian GCs, IP Deact., ea  
 Hole On Top, 4mm x 6.3 x 78.5 For Varian GCs, IP Deact., w/Deact Wool, ea  
 Hole on Top, 4mm x 6.3 x 78.5 for Varian GCs, IP Deact., w/CarboFrit, ea  
 Hole on Top, 4mm x 6.3 x 78.5 For Varian GCs, Siltek Deact., w/Deact. Wool, ea  
 Hole on Top, 4mm x 6.3 x 78.5 for Varian GCs, Siltek Deact., ea  
 Hole on Top, 4mm x 6.3 x 78.5 for Varian GCs, IP Deact., 5pk  
 Hole on Top, 4mm x 6.3 x 78.5 for Varian GCs, IP Deact., w/Deact. Wool, 5pk  
 Hole on Top, 4mm x 6.3 x 78.5 For Varian GCs, Siltek Deact., w/ Deact. Wool, 5p  
 Hole on Top, 4mm x 6.3 x 78.5 for Varian GCs, Silket Deact., 5pk  
 0.4mm, 10pk  
 0.5mm, 10pk  
 0.8mm, 10pk  
 for PE Autosys XL PSS Inlet, 10pk  
 for PE Autosys XL PSS Inlet, 25pk  
 on CD Rom  
 1/16" OD x 0.01" ID 25ft  
 1/16" OD x 0.01" ID 26 to 100ft  
 1/16" OD x 0.01" ID >100ft  
 1/16" OD x 0.02" ID 25ft  
 1/16" OD x 0.02" ID 26 to 100ft  
 1/16" OD x 0.02" ID >100ft  
 1/16" OD x 0.03" ID 25ft  
 1/16" OD x 0.03" ID 26 to 100ft  
 1/16" OD x 0.03" ID >100ft  
 1/16" OD x 0.04" ID 25ft  
 1/16" OD x 0.04" ID 26 to 100ft  
 1/16" OD x 0.04" ID >100ft  
 1/8" OD x 0.085" ID 25ft  
 1/8" OD x 0.085" ID 25ft, without treatment  
 1/8" OD x 0.085" ID 26 to 100ft  
 1/8" OD x 0.085" ID >100ft  
 1/4" OD x 0.210" ID 25ft  
 1/4" OD x 0.210" ID 26 to 100ft  
 1/4" OD x 0.210" ID >100ft  
 1/8" Plug Sulfinert Coated  
 1/4" Plug Sulfinert Coated  
 1/8" Cross Sulfinert Coated  
 1/4" Cross Sulfinert Coated  
 1/8" to 1/16" Tube End Reducer Sulfinert Coated  
 1/4" to 1/16" Tube End Reducer Sulfinert Coated



03 9762 2034

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors



**HROMalytic** +61(0)3 9762 2034  
**ECHnology** Pty Ltd

**Australian Distributors**  
 Importers & Manufacturers  
[www.chromtech.net.au](http://www.chromtech.net.au)

Website NEW : [www.chromalytic.net.au](http://www.chromalytic.net.au) E-mail : [info@chromtech.net.au](mailto:info@chromtech.net.au) Tel: 03 9762 2034 . . . in AUSTRALIA